

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® MINI	07.11.2014

High degree of protection
 For the smallest conductor sizes
 Low height
 Gentle cable clamping
 High packing density



Automation



Space requirement

Application range

For use wherever there is limited assembly space.
 Sensors
 Measuring technology

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: cable screw gland
Material:	Body: nickel-plated brass Seal: CR/NBR
Protection rating:	IP 68 - 5 bar
Temperature range:	-20°C to +100°C


Product Management	Document: LAPP_PRO1017EN.pdf	1 / 3
--------------------	------------------------------	-------




SKINDICHT® MINI

07.11.2014

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINDICHT® MINI						
52001860	MINI 6 x 1	2 - 3	9	19,5	5.0	50
52001880	MINI 8 x 1	3,5 - 5,5	11	20,5	5.0	50
SKINDICHT® MINI counter nut						
52102998	MINI 6 x 1	-	10	11.0	2.5	50
52102997	MINI 8 x 1	-	12	13,5	2.5	50

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® MINI	07.11.2014



Product Management	Document: LAPP_PRO1017EN.pdf	3 / 3
--------------------	------------------------------	-------