



used for: DIN 41651



POS.	B ±0.2	Part-NO.
10	17.30	140X10059X
14	22.40	140X10069X
16	24.90	140X10079X
20	30.00	140X10089X
26	37.60	140X10099X
34	47.80	140X10109X
40	55.40	140X10119X
50	68.10	140X10129X
60	80.80	140X10139X
64	85.85	140X10159X



APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

**NOTES:**

- INSULATORS: PBT GV, V0, UL 94, GREY RAL 7035
- OPERATING TEMPERATURE RANGE: -55°C TO +125°C

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.  
 OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
 DO NOT ALTER CAD DRAWING BY HAND

tolerance			
2002	date	name	
drawn	11.12.	Parei	
appd.	11.12.	Kühle	
norm	DIN 41651		
d-old			
rev.	description	date	name

scale:	2:1	
material:	SEE NOTES	
title:	<b>STRAIN RELIEF</b> 10-64pos.	
dwg no:	AutoCAD 2000	DIN-A
	14K1A013	4
		sh: 1/1
part no:	SEE TABLE	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[140X10109X](#) [140X10119X](#) [140X10079X](#) [140X10069X](#) [140X10089X](#) [140X10129X](#) [140X10159X](#) [140X10139X](#)  
[140X10059X](#)