

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0500798100**
Status: **Active**
Overview: PicoBlade Connector System
Description: 1.25mm Pitch PicoBlade Crimp Terminal, 26-28 AWG, Tin (Sn) Plating, Bag

Documents:

3D Model	Product Specification PS-51021-024-001 (PDF)
Drawing (PDF)	Product Specification PS-51021-025-001 (PDF)
Product Specification PS-51021-001-001 (PDF)	Product Specification PS-51021-026-001 (PDF)
Product Specification PS-51021-002-001 (PDF)	Product Specification PS-51021-027-001 (PDF)
Product Specification PS-51021-009-001 (PDF)	Product Specification PS-51021-032-001 (PDF)
Product Specification PS-51021-010-001 (PDF)	Application Specification 510210000-AS-000 (PDF)
Product Specification PS-51021-011-001 (PDF)	Application Specification 510210001-AS-000 (PDF)
Product Specification PS-51021-022-001 (PDF)	Packaging Specification SPK-50079-001-001 (PDF)
Product Specification PS-51021-023-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	50079
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Current Derating Order No	987651-3691
Overview	<u>PicoBlade Connector System</u>
Packaging Alternative	500798000 (Reel)
Product Name	PicoBlade
UPC	800753749740

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	10.100/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max.
Wire Size AWG	26, 28
Wire Size mm ²	N/A


Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	510210000-AS-000, 510210001-AS-000
Packaging Specification	SPK-50079-001-001
Product Specification	PS-51021-001-001, PS-51021-002-001, PS-51021-009-001, PS-51021-010-001, PS-51021-011-001, PS-51021-022-001, PS-51021-023-001, PS-51021-024-001, PS-51021-025-001, PS-51021-026-001, PS-51021-027-001, PS-51021-032-001
Sales Drawing	SD-50079-001-001, SD-51021-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

50079 Series

Use With

51021 Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description **Product #**

Extraction Tool [11030043](#)

Hand Crimp Tool [638271400](#)

for 1.25mm Pitch
PicoBlade Female
Crimp Terminals,
26-32 AWG

Japan

Description **Product #**

Extraction Tool [570726000](#)

Hand Crimp Tool [571775000](#)

This document was generated on 04/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION