


Precision Metal Film Resistors



Features:

- EIA standard colour coding
- Low noise and voltage coefficient
- Low temperature coefficient range
- Wide precision range in small package
- Too low or too high ohmic value can be supplied on case to case basis
- Nichrome resistor element provides stable performance in various environment
- Multiple epoxy coating on vacuum deposited metal film provides superior moisture protection


Performance Specifications

Temperature Coefficient	: Within the maximum temperature coefficient specified
Short Time Overload	: $\pm (0.5\% + 0.05 \Omega)$ Maximum, with no evidence of mechanical damage
Insulation Resistance	: Minimum 10,000 Mega Ohms
Dielectric Withstanding Voltage	: No evidence of flashover, mechanical damage, arcing or insulation breakdown
Pulse Overload	: $\pm(1.0\% + 0.05 \Omega)$ Maximum, with no evidence of mechanical damage
Terminal Strength	: No evidence of mechanical damage
Resistance to Soldering Heat	: $\pm(1.0\% + 0.05 \Omega)$ Maximum, with no evidence of mechanical damage
Solderability	: Minimum 95% coverage
Resistance to Solvent	: No deterioration of protective coating and markings
Temperature Cycling	: $\pm (1\% + 0.05 \Omega)$ Maximum, with no evidence of mechanical damage
Humidity (Steady state)	: $\pm (2\% + 0.05 \Omega)$ Maximum, with no evidence of mechanical damage
Load Life in Humidity	: Normal type $\pm (1.5\% + 0.05 \Omega)$ Maximum
Load Life	: Normal type $\pm (1.5\% + 0.05 \Omega)$ Maximum

Part Number Explanation:

MCMF	0	W4	B	B	1002	A 5 0
Type	Feature	Wattage	Tolerance	PPM Requirement	Resistance	Internal Reference
Metal Film	0 = Standard F = Non-Flame	W8 = 1/8W W4 = 1/4W 1W = 1W 2W = 2W 3W = 3W Small Size S2 = 1/2W-S Extra Small Size 04 = 0.4W-SS	B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	B = 15 ppm C = 25 ppm F = 50 ppm G = 100 ppm J = 200 ppm	1st to 3rd digits are significant figures of the resistance and the 4th digit indicates the number of zeros. R = Decimal Point 1331 = 1.33 kohms 49R9 = 49.9 ohms	

Precision Metal Film Resistors



Dimensions : Millimetres

Part Number	Style	Power Rating at 70°C	Dimension (mm)					Standard Packing Quantity
			D Maximum	L Maximum	d ±0.05	H ±3	PT	
Normal Size								
MF0W8	MF 12	1/8 W (0.125 W)	1.85	6.8	0.45	28	52	5,000
MF0W4	MF 25	1/4 W (0.25 W)	2.5	3.5	0.54	28	52	5,000
MF0W2	MF 50	1/2 W (0.5 W)	3.6	10	0.54	28	52	1,000
MF01W	MF 100	1 W	5	12	0.7	25	52	1,000
MF02W	MF 200	2 W	5.5	16	0.7	28	64	1,000
MF034	MF 300	3 W	6.5	17.5	0.75	28	64	500
Small Size								
MF0S4	MF 25-S	1/4 W (0.25 W)	1.85	3.5	0.45	28	52	5,000
MFF04	MF 40-SS	0.4 W	1.9	3.7	0.45	28	52	5,000
MFFU2	MF 50-SS	1/2 W (0.5 W)	2.5	6.8	0.54 ⁽²⁾	28	52	5,000
MF0S2	MF50-S	1/2 W (0.5W)	3	9	0.54	28	52	2,000
MF006	MF 60-S	0.6 W	2.5	6.8	0.54 ⁽²⁾	28	52	5,000
MF0M7	MF 75-S	0.75 W	3.5	10	0.54	28	52	5,000
MF01S	MF 100-S	1 W	3.5	10	0.54	28	52	1,000
MF02S	MF 200-S	2 W	5	12	0.7	28	52	1,000
MF03S	MF 300-S	3 W	5.5	16	0.7	28	64	1,000

Notes:

- Extra small size types (-SS) are Non flame coating (Dark Green Colour)
- ⁽²⁾ Lead diameter of MF0W4, MF006 & MFFU2 can be provided in 0.5, 0.54 and 0.6 mm


Precision Metal Film Resistors




General Specifications

Part Number	Style	Maximum Working Voltage	Maximum Overload Voltage	Dielectric Withstanding Voltage	Tolerance	Resistance Range	TCR	Special Order		
								Tolerance	Resistance Range	TCR
MF12	MF12	200 V	400 V	400 V	±1%	10 Ω to 1 M Ω	±50 PPM/°C	±0.25%	51.1 Ω to 200 KΩ	±15 PPM/°C
MF0S4	MF 25-S				±2%	10 Ω to 1 M Ω	±100 PPM/°C			
MFF04	MF 40-SS	200 V	400 V	200 V	±5%	1 Ω to 1 M Ω	±200 PPM/°C	±0.5%	51.1 Ω to 511 KΩ	±50 PPM/°C
MF0W4	MF 25	250 V	500 V	500 V	±1%	10 Ω to 1 M Ω	±50 PPM/°C			±0.1%
MF006	MF 60-S				±2%	10 Ω to 1 M Ω	±100 PPM/°C	±0.25%	51.1 Ω to 330 KΩ	±25 PPM/°C
MFFU2	MF 50-SS	250 V	500 V	250 V	±5%	1 Ω to 1 M Ω	±200 PPM/°C	±0.5%	10 Ω to 1 M Ω	±50 PPM/°C
MF0W2	MF 50	350 V	700 V	700 V	±1% ±2% ±5%	10 Ω to 1 M Ω	±50 PPM/°C	±0.1% ±0.25% ±0.5%	100 Ω to 300 KΩ 51.1 Ω to 511 KΩ 10 Ω to 1 M Ω	±15 PPM/°C ±25 PPM/°C ±50 PPM/°C
MF0S2	MF 50-S					10 Ω to 1 M Ω	±100 PPM/°C			
MF0m7	MF 75-S					Ω	±200 PPM/°C			
MF01S	MF 100-S					1 Ω to 1 M Ω				
MF02S	MF 200-S	500 V	1,000 V	1,000 V	±1% ±2% ±5%	51.1 Ω to 1 MΩ	±50 PPM/°C	±0.1% ±0.25% ±0.5%	100 Ω to 300 KΩ 51.1 Ω to 511 KΩ 51.1 Ω to 1 MΩ	±15 PPM/°C ±25 PPM/°C ±50 PPM/°C
MF03S	MF 300-S					51.1 Ω to 1 MΩ	±100 PPM/°C			
MF01W	MF 100					10 Ω to 1 M Ω	±200 PPM/°C			
MF02W	MF 200									
MF03W	MF 300									

Derating Curve




Load Life



Precision Metal Film Resistors



Current Noise Level



Part Number Table

Description	Part Number
Precision Metal Film Resistor	MCMF0W4BB1002A50

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.