


MINIATURE LAMP (3175) Details

[Back](#)



Part #		3175			
Description		T3 FESTOON 12V 10W 10X31MM			
Bulb Shape	T-3 1/4	Filament	C-8	Base Style	Festoon Cap
Glass Diameter (in)	0.433	MOL† (in)	1.22	LCL†† (in)	0.00
Glass Diameter (mm)	11	MOL (mm)	31.00	LCL (mm)	0.00
Volts	12	MSCP ‡	9.55	Avg Life Hrs	400
Watts	10	Amps	0.83	RoHS Compliant	Yes
E-Marked	No	Drawing	3175.pdf	New Announcement	

Click below to see NAFTA & Packaging information



† **MOL (Maximum Overall Length):**

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ **MSCP (Mean Spherical Candlepower):**

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† **LCL (Light Center Length):**

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.

Search Miniature Lamps By:



BULB SHAPE



BASE STYLE



AUTOMOTIVE APPLICATION GUIDE



MOTORCYCLE APPLICATION GUIDE



DOWNLOADS



MINIATURE PART # INTERCHANGE



MINIATURE LAMP ITEM MATCH-UP



ALL MINIATURE LAMPS



E-MARKED MINIATURE LAMPS

54

Xe

131.29

XENON GAS FILLED MINIATURE LAMPS

36

Kr

83.80

KRYPTON GAS FILLED MINIATURE LAMPS