


# Series 11CE 12mm Rotary Encoder

- Compact 12 mm package size
- Rotational life (30,000 cycles)
- Wide temperature range (-10°C to +70°C)
- Momentary switch option
- Bushing and mounting style options

### **Applications**

- Consumer portable electronics
- Commercial appliances
- Instrument amplifiers and guitar effects
- Keyboards and synthesizers
- Communications equipment

# **Ordering Information**



\* See outline drawings for shaft length (LM) availability by configuration.

#### 2020-08-26 Rev. B

#### www.ctscorp.com

Page 1 of 7

RoH:

Sense



# **Encoder Specifications**

		Min	Typical	Max	Unit		
Voltage Rating	@ 0.5 mA	_	+5.0	_	VDC		
Output	2-bit quadrature						
Insulation Resistance	100 MΩ min. @ 250 VDC						
Dielectric Strength	300 VAC for 1 min., no arcing						
Resolution	12 or 24 PPR (pulses per revolution)						
Contact Bounce/Chatter	(See Fig. 1)						
t1, t3	≤ 3 ms						
t2	≤ 2 ms						
Phase Difference	(See Fig. 2)						
12 PPR	$\Delta T \ge 4 \text{ ms}$ (A leads B by 90° in the CW direction)						
24 PPR	$\Delta T \ge 3.5$ ms (A leads B by 90° in the CW direction)						
Total Mechanical Travel	360° continuous						
Operating Torque	50 gf-cm (non-detent option only)						
Detent Position							
12 detents	30° ± 3°						
24 detents	15° ± 3°						
Detent Torque	30 to 200 gf-cm						
Detent Position Play	4° max.						
Shaft Wobble	1.0 x L/30mm p-p max.; L = Shaft Length						
Shaft Push-Pull Strength	5 kgf for 10 sec.						
Shaft Static Side Load	2 kgf max.						
Terminal Strength	300 gf max.						
Rotational Life	30,000 cycles						

# Switch Specifications

		Min	Typical	Max	Unit	
Voltage Rating	@ 0.5 mA	_	+5.0	_	VDC	
Contact Resistance	100 mΩ max.					
Contact Arrangement	SPST Momentary					
Chatter	10 ms max.					
Switch Travel	0.5mm +0.4mm, -0.3mr	n				
Actuation Force	300 gf +150 gf/-100 gf					
Insulation Resistance	100 MΩ min. @ 250 VDC					
Dielectric Strength	300 VAC for 1 min., no arcing					
Operating Life	20,000 actuations					
IP Rating	40					
Packaging	Tray					
Weight	3.2 grams					




### **Environmental Specifications**

	Min	Typical	Max	Unit		
Operating Temperature	-10	_	+70	°C		
Storage Temperature	-40	_	+85	°C		
Soldering Conditions						
Wave Solder	Preheat: 100°C max for 2 min max; Solder temperature: 260°C ± 5°C for 5 sec max.;					
	No clean foam flux recommended					
Manual Solder	350°C ± 5°C for 3 sec max.; Sn95Ag5 no clean solder					
Wash	Not recommended					
Moisture Sensitivity Level	1					
ESD Classification (HBM)	Not applicable					


All testing is performed at room ambient conditions except as noted. Users should verify device actual performance in their specific applications This product is compliant to RoHS3 Directive 2015/863 Amendments of Annex II on 31 March 2015, and REACH SVHC Directive EC 1907/2006 Amendments of Annex XIV & Annex XVII on 15 January 2018.

Custom and value-added options available on request. Please contact your sales representative for additional information.

# **Electrical Specifications**







### Figure 2: Phase Difference




Figure 3: Suggested Filter Circuit

2020-08-26 Rev. B

#### www.ctscorp.com

Page 3 of 7




12


30

### **Mechanical Specifications**

Series 11CE Horizontal/Side Mount Sleeve Bushing (No Switch)



### Series 11CE Vertical/Rear Mount Sleeve Bushing (No Switch)



2020-08-26 Rev. B


www.ctscorp.com

Page 4 of 7




# **Mechanical Specifications**

Series 11CE Horizontal/Side Mount with Threaded Bushing (No Switch)



### Series 11CE Vertical/Rear Mount with Threaded Bushing (No Switch)



www.ctscorp.com




12


30

# **Mechanical Specifications**

### Series 11CE Horizontal/Side Mount Sleeve Bushing (With Switch)



### Series 11CE Vertical/Rear Mount Sleeve Bushing (With Switch)




2020-08-26 Rev. B

www.ctscorp.com




# **Mechanical Specifications**

Series 11CE Horizontal/Side Mount with Threaded Bushing (With Switch)



### Series 11CE Vertical/Rear Mount with Threaded Bushing (With Switch)



2020-08-26 Rev. B

www.ctscorp.com