

# GDB

## 5 mm x 20 mm Fast-acting glass tube fuses



### Product features

- Fast-acting, low breaking capacity
- 5 x 20mm physical size
- Glass tube, nickel-plated brass endcap construction
- Optional axial leads are 0.032" x 1.5" copper tinned
- Designed to IEC 60127-2 (32 mA- 10 A)

### Agency information

- UL Recognized Card: Guide JDYX2, File E19180
- VDE approval: File 40014109

### Ordering

- Specify product code: Insert packaging code prefix before part number. E.g. BK/GDB-250mA
- Ratings above 6.3 A have a 0.8 mm diameter lead
- With TR2 packaging code, lead wire length is 19.05 mm
- Specify option code if desired: For axial leads, insert "V" between catalog series and amp rating. E.g. BK/GDB-V-250mA

Electrical Characteristics							
I <sub>n</sub>	1.5 I <sub>n</sub>		2.1 I <sub>n</sub>		2.75 I <sub>n</sub>		10 I <sub>n</sub>
	min	max	min	max	min	max	
32mA-100mA	60 min	30 min	10 ms	500 ms	3 ms	100 ms	20 ms
125mA-6.3A	60 min	30 min	50 ms	2 sec	10 ms	300 ms	20 ms
8A-10A	30 min	30 min	50 ms	2 sec	10 ms	400 ms	40 ms

### Specifications

Part Number	Voltage Rating Vac	Interrupting Rating (amps) at Rated Voltage (50Hz) Vac	Typical DC Cold Resistance (Ω)*	Typical Melting I <sup>2</sup> t AC†	Maximum Voltage Drop (mV)‡	Agency Approval	
						UR	VDE
GDB-32mA	250	35	40	0.000047	3200		
GDB-40mA	250	35	25	0.00011	2500		
GDB-50mA	250	35	17	0.00020	2400		
GDB-63mA	250	35	12.5	0.00057	2000		
GDB-80mA	250	35	5.0	0.0012	1200		
GDB-100mA	250	35	3.8	0.003	1100		
GDB-125mA	250	35	2.8	0.005	1000		
GDB-160mA	250	35	9.1	0.008	2000	X	X
GDB-200mA	250	35	6.8	0.016	1700	X	X
GDB-250mA	250	35	4.3	0.28	1400	X	X
GDB-315mA	250	35	3.1	0.58	1300	X	X
GDB-400mA	250	35	2.0	0.18	1100	X	X
GDB-500mA	250	35	0.26	0.18	220	X	X
GDB-630mA	250	35	0.20	0.35	220	X	X
GDB-800mA	250	35	0.14	0.67	190	X	X
GDB-1A	250	35	0.125	0.60	200	X	X
GDB-1.25A	250	35	0.096	0.84	200	X	X
GDB-1.6A	250	35	0.066	1.6	190	X	X
GDB-2A	250	35	0.043	4.2	150	X	X
GDB-2.5A	250	35	0.034	6.1	150	X	X
GDB-3.15A	250	35	0.025	13	130	X	X
GDB-4A	250	40	0.021	22	130	X	X
GDB-5A	250	50	0.014	42	120	X	X
GDB-6.3A	250	63	0.010	69	120	X	X
GDB-8A	250	80	0.010	N/A	120	X	X
GDB-10A	250	100	0.008	N/A	120	X	X

\* DC Cold Resistance (Measured at <10% of rated current)


† Typical Melting I<sup>2</sup>t (I<sup>2</sup>t was measured at listed interrupting rating and rated voltage)

‡ Maximum Voltage Drop (Voltage drop was measured at 20°C ambient temperature at rated current)




Powering Business Worldwide

**Dimensions - mm**  
Drawing Not to Scale



**Time-Current Curve**



Packaging Code	
Packaging Prefix	Description
BK	100 fuses packed into a cardboard carton
BK1	1,000 fuses packed into a poly bag
TR2	1,500 fuses packed into tape on a reel (19.05mm lead wire length)

Option Code	
Option Code	Description
V	Axial leads - copper tinned wire with nickel plated brass endcaps

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
www.eaton.com/electronics

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 2015 BU-SB08762  
May 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Eaton:

[BK/GDB-40MA](#) [BK/GDB-V-63MA](#) [BK/GDB-V-80MA](#) [BK/GDB-250MA](#) [BK/GDB-315MA](#) [BK/GDB-8A](#) [BK/GDB-V-32MA](#) [BK/GDB-V-400MA](#) [BK/GDB-V-8A](#) [BK/GDB-V-200MA](#) [BK/GDB-63MA](#) [BK/GDB-800MA](#) [BK/GDB-200MA](#) [BK/GDB-V-40MA](#) [BK/GDB-1.25A](#) [BK/GDB-2.5A](#) [BK/GDB-1.6A](#) [BK/GDB-V-1A](#) [BK/GDB-V-500MA](#) [BK/GDB-V-1.6A](#) [BK/GDB-160MA](#) [BK/GDB-V-4A](#) [BK/GDB-80MA](#) [BK/GDB-V-3.15A](#) [GDB-10A](#) [GDB-3-15A](#) [GDB-6-3A](#) [BK-GDB-16A](#) [GDB-1-6A](#) [BK/GDB-6.3A](#) [BK/GDB-V-125MA](#) [BK/GDB-125MA](#) [BK/GDB-V-800MA](#) [BK/GDB-V-2A](#) [BK/GDB-V-1.25A](#) [BK/GDB-V-10A](#) [BK/GDB-V-630MA](#) [BK/GDB-100MA](#) [BK/GDB-V-315MA](#) [BK/GDB-32MA](#) [BK/GDB-V-100MA](#) [BK/GDB-V-6.3A](#) [BK/GDB-V-50MA](#) [BK/GDB-V-250MA](#) [BK/GDB-50MA](#) [BK/GDB-V-160MA](#) [BK/GDB-16A](#) [GDB-1.6A](#) [GDB-3.15A](#) [GDB-6.3A](#)