# GREEN POLARIZATION INSENSITIVE FIBER ISOLATOR

#### **OIXSG Series**

#### **Product Description**

Oplink's Green isolator is based on glass encapsulated micro-optic packaging technology and minimizes back reflection and back scattering in the reverse direction for any state of polarization. The Green Isolator is a low cost model with excellent performance such as low insertion loss, high isolation, high return loss, low polarization dependent loss (PDL) and low polarization mode dispersion (PMD) for dual-stage isolator.



#### **Performance Specification**

Specifications		OISSG Serie	OIDSG Serie	Unit
Operating Wavelength Range		1310 ± 15 or 1480 ± 15 or C-band: 1528 ~ 1564 or L-band: 1570 ~ 1605		nm
Insertion Loss [1]	Standard PMD	< 0.4	-	dB
	Low PMD	< 0.45	-	dB
		-	< 0.5	
Isolation (over operating wavelength range, 0~70°C, all SOP)		> 20	>35	dB
Polarization Dependent Loss		< 0.06	< 0.08	dB
Polarization Mode Dispersion	Standard PMD	< 0.25	< 0.05	ps
	Low PMD	< 0.05	-	ps
Return Loss (Input/Output Ports)		> 55/50		dB
Maximum Power Handling		< 500		mW
Fiber Type		Corning SMF-28		
Operating Temperature		0 to +70		°C
Storage Temperature		-40 to +85		°C
Package Dimensions [3]		P1: (ø) 5.5 x (L) 34.0, with boot P2: (ø) 5.5 x (L) 34.0, without boot		mm

#### Note:

- [1] The maximum IL is under all states of polarization and within the full operating temperature and wavelength ranges specified.
- [2] All the parameters are excluding connectors.
- [3] The mechanical tolerance should be +/-0.2mm on all package dimensions unless otherwise custom specified

#### **Features**

- Wide Operating Wavelength Range and Temperature Range
- ♦ Low Insertion Loss
- High Isolation
- Ultra Low PDL & Option for Ultra Low PMD
- ♦ Highly Stable & Reliable
- Epoxy-free Optical Path

#### **Applications**

- Fiberoptic Amplifiers
- ♦ CATV Fiberoptic Links
- WDM Systems
- ♦ Fiberoptic Instruments
- Transmitters and Fiber Lasers
- Laboratory R&D







#### **DIXSG SERIES**

#### **Mechanical Drawing / Package Dimensions (dimension in mm)**


P1 Package: P2 Package:





#### **Ordering Information**

Oplink can provide a remarkable range of customized optical solutions. For detail, please contact Oplink's OEM design team or account manager for your requirements and ordering information (510) 933-7200.



<sup>\*</sup>For OIDSG series, the PMD option is 'S'. For OISSG series, the PMD option is 'S' or 'L' based on customer's requirement.

<sup>\*\*</sup>The tolerance of fiber length is  $\pm$ -0.1m. 1 meter is standard. The lead-time for special fiber length will be longer.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Molex:

OIDSG1550S01111 OISSG1550L01111