








**SoftFinish® electric slimBit, slotted.**


Increases your safety:	Wiha slimBits ensure unrestricted and fully insulated access to low-lying screws. Wiha slim blades grant unhindered, fully insulated access to low-lying screws.
Protects your health:	Protects your health With patented SoftFinish® handle design for fatigue-free, manual operation. Recommended by German doctors and therapists of the AGR.
Increases your efficiency:	Saves space due to comprehensive interchangeable blade system. Unique concept of screwdriver handle sizes for an optimum balance between torque and control.
Offers you full protection:	Each piece individually tested at 10.000 V AC.
Standards:	Manufactured acc. to IEC 60900:2012.
Material:	High-quality chrome vanadium steel, through-hardened, bronzed. Protective insulation moulded directly onto the bit and completely integrated into the blade in the lower area from size 4.0.
Application:	For all work on or around electrical components up to 1,000 V AC.
Extra:	The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated. The slim form of the bit allows easy reaching of the screws below the finger and hand guards.
Note:	Tool tested at 10,000 V AC

Ord.No.						max. Nm			Gross
34578	5	2,5	75	0,4	6,0	0,4		8	5,56
34579	5	3,0	75	0,5	6,0	0,6		8,14	5,56
34580	5	4,0	75	0,8	6,0	2,5		8.4	6,49
34581	5	5,5	75	1,0	6,0	5,5		11	6,49
34582	5	6,5	75	1,2	6,0	5,5		11,22	6,49

The above-mentioned prices are in EUR.

All prices are quoted net/pc.