

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0500388000**  
**Status:** **Active**  
**Overview:** Mizu Sealed Connectors  
**Description:** 2.50mm Pitch Mizu-P25 Crimp Terminal, 50038, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-50038-001-001 (PDF)</a>
<a href="#">Product Specification PS-52048-001 (PDF)</a>	<a href="#">Packaging Specification 500380000-P00 (PDF)</a>
<a href="#">Product Specification PS-52117-008-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	50038
Application	Signal, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mizu Sealed Connectors
Packaging Alternative	500388100 (Loose)
Product Name	Mizu-P25 Waterproof
UPC	800754368643

**Physical**

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	58.900/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-1.90mm
Wire Size AWG	20, 22
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Voltage - Maximum	250V
-------------------	------


**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-50038-001-001
Packaging Specification	500380000-P00
Product Specification	PS-52048-001, PS-52117-008-001
Sales Drawing	SD-50038-001-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

50038 Series

**Use With**

Mizu-P25 2.50mm Pitch Waterproof Plug  
Housing [52116](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Hand Crimp Tool for Splash Proof Crimp Terminal	<a href="#">638233900</a>
-------------------------------------------------------	---------------------------

FineAdjust Applicator for 2.50mm Pitch Splash Proof Crimp Terminal, 20-22 AWG	<a href="#">639000100</a>
-------------------------------------------------------------------------------------------	---------------------------

T2 Terminator Tooling Die for	<a href="#">639100100</a>
----------------------------------	---------------------------

2.50mm Pitch  
Splash Proof Crimp  
Terminal, 20-22  
AWG

**Japan**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

Applicator for M211A Bench Press	<u>570843000</u>
----------------------------------	------------------

S-1 Applicator for Mizu-P25	<u>570843700</u>
-----------------------------	------------------

Standard Waterproof

Terminals

This document was generated on 01/21/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**