


CM8V-T1A

Tuning Fork Crystal 32.768 kHz



100% leadfree, RoHS - compliant

DIMENSIONS



All dimensions in mm typical

Miniature SMT ceramic package
 Ultra low profile: 0.60 mm height
 Ind. and Ext. temperature ranges
 Optimized electrical characteristics
 "Low ESR and Low Sensitivity"
 High stability
 Low aging
 Low power consumption
 High shock and vibration resistance

DESCRIPTION:

This SMD ceramic package has been specially designed for miniature telecom and portable applications. The Ultra Miniature Quartz Crystal resonator in this product is achieved by a special manufacturing process. The optimized resonator design "low-ESR and low sensitivity" provide best-of-its-class electrical performance.

For pick-and-place equipment, the parts are available in 8 mm tape:

- 7" (178 mm) reel with 1'000 crystals
- 7" (178 mm) reel with 3'000 crystals
- 13" (330 mm) reel with 14'000 crystals

ELECTRICAL CHARACTERISTICS AT 25°C:

Nominal Frequency	¹⁾ F_L	32.768	kHz
Load capacitance	²⁾ C_L	4.0 / 6.0 / 7.0 / 9.0 / 12.5	pF
Frequency tolerance	³⁾ $\Delta F/F$	+/-20	ppm
		+/-100	ppm
Series resistance typ. / max.	R_S	55 / 75	k Ω
Motional capacitance typ.	C_1	3.7	fF
Static capacitance typ.	C_0	1.1	pF
Drive level max.	P	0.5	μ W
Insulation resistance min.	R_i	500	M Ω
Aging first year max.	$\Delta F/F$	+/-3	ppm
Turnover temperature	T_0	25 +/-5	°C
Frequency vs. temperature	$\Delta F/F_0$	$-0.035 \text{ ppm}/^\circ\text{C}^2 (T - T_0)^2 \pm 10\%$	ppm

- 1) Other frequencies on request.
- 2) Other load capacitances on request.
- 3) Tighter and wider frequency tolerances on request.

STANDARD FREQUENCIES:

Frequency kHz
32.768
Other frequencies on request

**ENVIRONMENTAL
CHARACTERISTICS:**

		Conditions	Max. Dev.
Storage temp. range		-55 to +125°C	
TA Operating temperature range		-40 to +85°C	
TB Extended oper. temp. range		-40 to +125°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	+/-5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	+/-5 ppm

**TERMINATIONS AND
PROCESSING:**

Type	Termination	Processing
CM8V-T1A	For SMD mounting Au plated pads	Reflow soldering 260°C / 20 s max.

**PRODUCT DESCRIPTION AND
ORDERING INFORMATION:**

CM8V-T1A 32.768kHz 12.5pF +/-20ppm TA QC

Frequency F_0 _____

C_L Load Capacitance
7.0 pF
9.0 pF
12.5 pF

Frequency tolerance
+/- 20 ppm
+/- 100 ppm

Temperature Range
TA = -40 to 85°C (Standard)
TB = -40 to +125°C

Optional:
if not defined,
'Standard' will apply

Qualification
QC = Commercial (Standard)

A unique part number will be generated for each product specification, i.e:

20xxxx-MC01	1'000 pcs (in 8mm tape on 7" reel)
20xxxx-MC03	3'000 pcs (in 8mm tape on 7" reel)
20xxxx-PC14	14'000 pcs (in 8mm tape on 13" reel)

Please contact us.

All specifications subject to change without notice.



Micro Crystal AG
Mühlestrasse 14
CH-2540 Grenchen
Switzerland

Tel. +41 32 655 82 82
Fax +41 32 655 82 83
sales@microcrystal.com
www.microcrystal.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Crystal:

[CM8V-T1A-32.768k-12.5pF-20PPM-TA-QA](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TC-QC](#) [CM8V-T1A-32.768kHz-4pF-20PPM-TA-QC](#) [CM8V-T1A-100.000kHz-9pF-100PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-100PPM-TA-QC](#) [CM8V-T1A-32.768k-9pF-20PPM-TB-QA](#) [CM8V-T1A-32.768k-12.5pF-20PPM-TB-QA](#) [CM8V-T1A-32.768kHz-7pF-100PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-6pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-7pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-7pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-4pF-20PPM-TA-QC T1](#)