

Product Specification Confirmation

Product Model:	DL-17C-L04S060ATJ-MM00
Customer Name	:
Customer P/N:	
Product Name:	Lifeo4 4s 12V 60A Common port
Version:	
Company P/N:	
Sample send dat	te:

	Confirmation	
Verified	Approved	Operation

	Custon	ner Ackno	owledgement	
Remarks:				
		Sign:	Date:	
		Sign.	Date:	

Note:

1. After receiving the prototype confirmation, please return it in time. There is no return and problem feedback within 7 days. Our default customer test is qualified;

The picture in the book is a general-purpose model picture, which may be different from the sample delivery machine. This specification book reaches the final interpretation right of Lithium Electronics.

2. Before the customer batches, please sign and return in the specification, and explain the detailed function description.

# **1. Product Summary:**

- Adopt foreign premium IC in class A protection.
- Use professional high current trace design and process to withstand large current

surge.


• Complete overcharge, over discharge, over current, short circuit function.


# **2.Electrical Parameters:**


	Description	Specification	Unite	Remarks
Dischause	Continue discharge current	60	A	
Discharge	Sparkle current	150	A	
	Charge voltage	14.6	V	
Charge	Charge current	60 (MAX)	A	
	Over charge detect voltage	3.65±0.05	V	
Over charge protection	over charge protection delay	1	S	
	over charge release voltage	3.6±0.05	V	
	Balance detect Voltage	/	V	
Balance	Balance release voltage	/	V	
	Balance current	/	mA	
	Over discharge detect voltage	2.5±0.1	V	
Over discharge protection	Over discharge detect delay	20	mS	
protection	Over discharge release voltage	2.5±0.1	V	
Over evenent meteodiem	Over current detect voltage	/		
Over current protection	Over current detect delay	100	MS	

Model	DL-17	C-F04S060ATJ-MM00	F	P/N			
		Over current protection curren	t	150	±30	Α	as required
		Over current protection release	9	Off	load		
	~	Short Circuit protection condit	tion		ircuit of al load		
Short C		Short circuit detect delay		2	50	uS	
		Short circuit protection release condition	e	Off	load		
Temp Protec	t						No
Inner Resista	ance	Main Circuit Conduct Inner resistance		\$	20	mΩ	
		Working current		<	100	uA	
Self Consum	ption	Sleeping current(when in discharge)		\$	20	uA	
Working Ter	np	Temp range		-20	/+70	°C	

## 3. BMS wiring







#### (3). Wiring operation

- (1) First connect the B-line of the protection board to the total negative pole of the battery pack;
- (2) The cable starts from the thin black line connecting B-, the second line connects the positive

Mode1	DL-17C-F04S060ATJ-MM00	P/N	
-------	------------------------	-----	--

pole of the first string of batteries, and the next string is connected in turn.

The positive pole of the pool; then insert the cable into the protection board;

(3) After the wiring is completed, measure whether the battery B+, B-voltage and P+, P-voltage values are the same, the same, that is, the protection board works positively.otherwise please follow the above re-operation;

(4) When removing the protection board, first pull out the cable (if there are two cables, pull the high-voltage cable first, then pull the low-voltage cable), then remove Power line B-.

### 4.Warranty

All our produced Lithium battery BMS, we guarantee 3 years warranty in quality, if the damage is caused by human improper operation, we will conduct repair with charge

### 5.Attention Items

1.Lithium batery BMS with different voltage platform can not be used mutaully, eg., Life Po4 BMS

can not be used for Li-ion battery.

2.In utilization, please to make sure to Follow up the designed parameter and utilization conditions.

3. Charge and discharge current can not be higher than the quoted current value in specification.

4.Please to utilize the BMS in the the regulated working temperature range, and make sure of the

well heat dissipation environment.

5.No self taking off and change parts in BMS.

6.Our product has the function of waterproof, but still suggest avoid of long time water immersion.

7.We conduct Anode Oxidation process in BMS dissipation plate, but when the Oxidation layer

destroid, it stll may electricity conductive, it is stll suggest to avoid Dissipation plate contact with

Cell and Nickel band.

8.If the protection board is abnormal, please stop using it, and then solve the problem and use it again;

9.Do not use two protective plates in series or in parallel.

Address: Building A, 2nd District, Chengxing Industrial Park, No51 Industrial Zone, Tutang Village, Changping Town, Dongguan City TEL: 0769-82822953

DL-17C-F04S060ATJ-MM00
------------------------

### NOTE:

Our products undergo strict factory inspection tests, but because the environment used by customers is different (especially at high temperatures,

Ultra-low temperature, under the sun, etc.), it is inevitable that there will be a protection board failure, so customers need to be friends when choosing and using the protection board.

Use in a good environment, and choose a certain amount of protection board.