

KEMET Part Number: C0603C332F5GACTU
(C0603C332F5GAC7867)

SMD Comm COG, Ceramic, 3300 pF, 1%, 50 VDC, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0603



Dimensions

| | |
|----------|------------------|
| L | 1.6mm +/-0.15mm |
| W | 0.8mm +/-0.15mm |
| T | 0.8mm +/-0.07mm |
| S | 0.7mm MIN |
| B | 0.35mm +/-0.15mm |

Packaging Specifications

| | |
|----------------------------|------------------------|
| Packaging: | T&R, 180mm, Paper Tape |
| Packaging Quantity: | 4000 |

General Information

| | |
|-----------------------|---|
| Supplier: | KEMET |
| Series: | SMD Comm COG |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Note: KEMET 50V rated parts may be operated at 63 Volts |
| Chip Size: | 0603 |
| Shelf Life: | 78 Weeks |
| MSL: | 1 |

Specifications

| | |
|---|---------------------|
| Capacitance: | 3300 pF |
| Capacitance Tolerance: | 1% |
| Voltage DC: | 50 VDC |
| Dielectric Withstanding Voltage: | 125 VDC |
| Temperature Range: | -55/+125°C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.10% 1kHz 25C |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |