


FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 58V





Specifications

Housing: Out of thermoplastic (UL 94-V0, heat-resistant)
Connections: Leaf spring connector systems, soldering terminals

(4 pins each), copper alloy, tinned

Color: Black


Ordering Information

Part Number	Package Size
178.4265.0002	500

Description

PCB Fuse Holder for 42V PowerNet with coding for TAC fuses-links. For through hole soldering. Rated voltage 58V.


Recommended Assembly





Note: The locking feature at the holder center must lock holder and PCB before welding.


Dimensions

Dimensions in mm









Ratings

Part Number	Description	Contact Temperature
178.4265.0002	Complete	max. 130°C



Visit **Littelfuse.com** for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.



FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V







Description

PCB Fuse Holder for ATO / FKS size fuse-links. For through hole soldering. Rated voltage 80V.

Recommended Assembly





Note: The locking feature at the holder center must lock holder and PCB before welding.

Specifications

Housing: Out of thermoplastic (UL 94-V0, heat-resistant)
Connections: Leaf spring connector systems, soldering terminals

(4 pins each), copper alloy, silver plated


Color: Black


Ordering Information


Part Number	Package Size	
178.6165.xxx1	100	
178.6165.xxx2	500	


Dimensions

Dimensions in mm









Ratings

Part Number	Description	Contact Temperature
178.6165.000_	Complete	max. 130°C




Visit **Littelfuse.com** for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.



FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V





Specifications

Housing: Out of thermoplastic (UL 94-V0, heat-resistant)
Connections: Leaf spring connector systems, soldering terminals,

copper alloy, tin plated

Color: Black


Ordering Information

Part Number	Package Size	
178.6164.xxx1	100	
178.6164.xxx2	500	

Description


PCB Fuse Holder for ATO/FKS size fuse-links. For through hole soldering. Rated voltage 80V


Recommended Assembly



Note: The locking feature at the holder center must lock holder and PCB before welding.

Dimensions in mm







Ratings

Part Number	Description	Contact Temperature
178.6164.000_	Complete	max. 130°C



Visit **Littelfuse.com** for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

178.4265.0002 178.6165.0001 178.6165.0002 178.6164.0001 178.6164.0002