8-channel analog multiplexer/demultiplexer with injection-current effect control Rev. 3 — 24 August 2018 Pro

Product data sheet

### 1. General description

The 74HC4851; 74HCT4851 are high-speed Si-gate CMOS devices and are specified in compliance with JEDEC standard no. 7A.

The 74HC4851; 74HCT4851 are 8-channel analog multiplexers/demultiplexers with three digital select inputs (S0 to S2), an active-LOW enable input ( $\overline{E}$ ), eight independent inputs/outputs (Y0 to Y7) and a common input/output (Z). The devices feature injection-current effect control, which has excellent value in automotive applications where voltages in excess of the supply voltage are common.

With  $\overline{E}$  LOW, one of the eight switches is selected (low impedance ON-state) by S0 to S2. With  $\overline{E}$  HIGH, all switches are in the high-impedance OFF-state, independent of S0 to S2.

The injection-current effect control allows signals at disabled analog input channels to exceed the supply voltage without affecting the signal of the enabled analog channel. This eliminates the need for external diode/resistor networks typically used to keep the analog channel signals within the supply-voltage range.

### 2. Features and benefits

- Injection-current cross coupling < 1 mV/mA
- Wide supply voltage range from 2.0 V to 6.0 V for 74HC4851
- ESD protection:
  - HBM JESD22-A114E exceeds 2000 V
  - CDM JESD22-C101C exceeds 1000 V
- Latch-up performance exceeds 100 mA per JESD 78 Class II level A
- Low ON-state resistance:
  - 400  $\Omega$  (typical) at V<sub>CC</sub> = 2.0 V
  - 215  $\Omega$  (typical) at V<sub>CC</sub> = 3.0 V
  - 120 Ω (typical) at V<sub>CC</sub> = 3.3 V
  - 76 Ω (typical) at V<sub>CC</sub> = 4.5 V
  - 59  $\Omega$  (typical) at V<sub>CC</sub> = 6.0 V

### 3. Applications


- · Analog multiplexing and demultiplexing
- Digital multiplexing and demultiplexing
- Signal gating




# 4. Ordering information

Type number	Package									
	Temperature range	Name	Description	Version						
74HC4851D	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads;	SOT109-1						
74HCT4851D			body width 3.9 mm							
74HC4851PW	-40 °C to +125 °C	TSSOP16 plastic thin shrink small outline package;		SOT403-1						
74HCT4851PW			16 leads; body width 4.4 mm							
74HC4851BQ	-40 °C to +125 °C	DHVQFN16	plastic dual in-line compatible thermal	SOT763-1						
74HCT4851BQ			enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 × 3.5 × 0.85 mm							

# 5. Functional diagram




### 8-channel analog multiplexer/demultiplexer with injection-current effect control



**Product data sheet** 


© Nexperia B.V. 2018. All rights reserved

# 6. Pinning information



### 6.1. Pinning

### 6.2. Pin description



be connected to GND.

Pin configuration SOT763-1 (DHVQFN16) Fig. 5.

Symbol	Pin	Description	
Y4	1	independent input/output	
Y6	2	independent input/output	
Z	3	common input/output	
Y7	4	independent input/output	
Y5	5	independent input/output	
Ē	6	enable input (active LOW)	
n.c.	7	not connected	
GND	8	ground (0 V)	
S2	9	select input	
S1	10	select input	
S0	11	select input	
Y3	12	independent input/output	
Y0	13	independent input/output	
Y1	14	independent input/output	
Y2	15	independent input/output	
V <sub>CC</sub>	16	supply voltage	

# 7. Functional description

#### Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care.

Input				Channel ON
E	S2	S1	S0	
L	L	L	L	Y0 to Z
L	L	L	Н	Y1 to Z
L	L	Н	L	Y2 to Z
L	L	Н	Н	Y3 to Z
L	Н	L	L	Y4 to Z
L	Н	L	Н	Y5 to Z
L	Н	Н	L	Y6 to Z
L	Н	Н	Н	Y7 to Z
Н	Х	Х	Х	-

### 8. Limiting values

#### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage		-0.5	+7.0	V
VI	input voltage	[1]	-0.5	V <sub>CC</sub> + 0.5	V
V <sub>SW</sub>	switch voltage	[2]	-0.5	V <sub>CC</sub> + 0.5	V
I <sub>IK</sub>	input clamping current	$V_{\rm I}$ < -0.5 V or $V_{\rm I}$ > $V_{\rm CC}$ + 0.5 V	-	±20	mA
I <sub>SK</sub>	switch clamping current	$V_{SW}$ < -0.5 V or $V_{SW}$ > $V_{CC}$ + 0.5 V	-	±20	mA
I <sub>SW</sub>	switch current	$V_{SW}$ > -0.5 V or $V_{SW}$ < $V_{CC}$ + 0.5 V	-	±25	mA
I <sub>CC</sub>	supply current		-	50	mA
I <sub>GND</sub>	ground current		-50	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb} = -40 \ ^{\circ}C \ to +125 \ ^{\circ}C$ [3]	-	500	mW

[1] The minimum and maximum input voltage rating may be exceeded if the input clamping current rating is observed.

[2] The minimum and maximum switch voltage rating may be exceeded if the switch clamping current rating is observed.

For SO16 package: P<sub>tot</sub> derates linearly with 8 mW/K above 70 °C.
 For TSSOP16 package: P<sub>tot</sub> derates linearly with 5.5 mW/K above 60 °C.

For DHVQFN16 packages:  $\mathsf{P}_{tot}$  derates linearly with 4.5 mW/K above 60 °C.

# 9. Recommended operating conditions

Symbol	Parameter	Conditions	7	74HC4851			74HCT4851		
			Min	Тур	Мах	Min	Тур	Max	
V <sub>CC</sub>	supply voltage		2.0	-	6.0	4.5	5.0	5.5	V
VI	input voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
V <sub>SW</sub>	switch voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature		-40	-	+125	-40	-	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 2.0 V	-	6.0	1000	-	-	-	ns/V
		V <sub>CC</sub> = 3.0 V	-	6.0	800	-	-	-	ns/V
		V <sub>CC</sub> = 3.3 V	-	6.0	800	-	-	-	ns/V
		V <sub>CC</sub> = 4.5 V	-	6.0	500	-	6.0	500	ns/V
		V <sub>CC</sub> = 6.0 V	-	6.0	400	-	-	-	ns/V

#### Table 5. Recommended operating conditions

# **10. Static characteristics**

### Table 6. R<sub>ON</sub> resistance

At recommended operating conditions; voltages are referenced to GND (ground 0 V); For test circuit see Fig. 8.

Symbol	Parameter	eter Conditions		25 °C			-40 °C to +85 °C		-40 °C to +125 °C	
			Min	Тур	Мах	Min	Max	Min	Мах	
74HC485	51					1	1		•	
R <sub>ON(peak)</sub>		$V_I = V_{CC}$ to GND; $\overline{E} = V_{IL}$								
	(peak)	V <sub>CC</sub> = 2.0 V; I <sub>SW</sub> = 2 mA	-	400	650	-	670	-	700	Ω
		V <sub>CC</sub> = 3.0 V; I <sub>SW</sub> ≤ 2 mA	-	215	330	-	360	-	380	Ω
		V <sub>CC</sub> = 3.3 V; I <sub>SW</sub> ≤ 2 mA	-	120	270	-	305	-	345	Ω
		V <sub>CC</sub> = 4.5 V; I <sub>SW</sub> ≤ 2 mA	-	76	210	-	240	-	270	Ω
		V <sub>CC</sub> = 6.0 V; I <sub>SW</sub> ≤ 2 mA	-	59	195	-	220	-	250	Ω
$\Delta R_{ON}$	ON resistance mismatch between	$V_{I} = 0.5 \times V_{CC}; \overline{E} = V_{IL}$								
		V <sub>CC</sub> = 2.0 V; I <sub>SW</sub> = 2 mA	-	4	10	-	15	-	20	Ω
	channels	V <sub>CC</sub> = 3.0 V; I <sub>SW</sub> ≤ 2 mA	-	2	8	-	12	-	16	Ω
		V <sub>CC</sub> = 3.3 V; I <sub>SW</sub> ≤ 2 mA	-	2	8	-	12	-	16	Ω
		V <sub>CC</sub> = 4.5 V; I <sub>SW</sub> ≤ 2 mA	-	2	8	-	12	-	16	Ω
		V <sub>CC</sub> = 6.0 V; I <sub>SW</sub> ≤ 2 mA	-	3	9	-	13	-	18	Ω
74HCT48	351	·								
R <sub>ON(peak)</sub>	ON resistance	$V_I = V_{CC}$ to GND; $\overline{E} = V_{IL}$								
	(peak)	V <sub>CC</sub> = 4.5 V; I <sub>SW</sub> ≤ 2 mA	-	76	210	-	240	-	270	Ω
ΔR <sub>ON</sub>	ON resistance	$V_{I} = 0.5 \times V_{CC}; \overline{E} = V_{IL}$								
	mismatch between channels	V <sub>CC</sub> = 4.5 V; I <sub>SW</sub> ≤ 2 mA	-	2	8	-	12	-	16	Ω

### Table 7. Injection current coupling

At recommended operating conditions; voltages are referenced to GND (ground 0 V); For test circuit see Fig. 9.

Symbol	Parameter	Conditions		74HC4851	l	7	74HCT485	1	Unit
		-	Min	Typ [1]	Мах	Min	Тур [1]	Max	
T <sub>amb</sub> = -4	40 °C to +125 °C	>					•		
$\Delta V_O$	output voltage	$ I_{SW}  \le 1 \text{ mA}; R_S \le 3.9 \text{ k}\Omega$ [2][3]							
	variation	V <sub>CC</sub> = 3.3 V	-	0.05	1	-	-	-	mV
		V <sub>CC</sub> = 5.0 V	-	0.03	1	-	0.03	1	mV
		$ I_{SW}  \le 10 \text{ mA}; \text{ R}_{S} \le 3.9 \text{ k}\Omega$							
		V <sub>CC</sub> = 3.3 V	-	0.55	5	-	-	-	mV
		V <sub>CC</sub> = 5.0 V	-	0.27	5	-	0.27	5	mV
		$ I_{SW}  \le 1 \text{ mA}; R_S \le 20 \text{ k}\Omega$							
		V <sub>CC</sub> = 3.3 V	-	0.04	2	-	-	-	mV
		V <sub>CC</sub> = 5.0 V	-	0.03	2	-	0.03	2	mV
	I <sub>S</sub>	$ I_{SW}  \le 10 \text{ mA}; \text{ R}_{S} \le 20 \text{ k}\Omega$							
		V <sub>CC</sub> = 3.3 V	-	0.56	20	-	-	-	mV
		V <sub>CC</sub> = 5.0 V	-	0.48	20	-	0.48	20	mV

Typical values are measured at T<sub>amb</sub> = 25 °C. [1]

 $\Delta V_O$  here is the maximum variation of output voltage of an enabled analog channel when current is injected into any disabled channel. I<sub>SW</sub> = total current injected into all disabled channels. [2]

[3]

### **Table 8. Static characteristics**


At recommended operating conditions; voltages are referenced to GND (ground 0 V);

Symbol	Parameter	Conditions		25 °C			-40 °C to +85 °C		-40 °C to +125 °C	
			Min	Тур	Max	Min	Max	Min	Max	1
74HC48	51									
V <sub>IH</sub>	HIGH-level	control inputs								
	input voltage	V <sub>CC</sub> = 2.0 V	1.5	-	-	1.5	-	1.5	-	V
		V <sub>CC</sub> = 3.0 V	2.1	-	-	2.1	-	2.1	-	V
		V <sub>CC</sub> = 3.3 V	2.3	-	-	2.3	-	2.3	-	V
		V <sub>CC</sub> = 4.5 V	3.15	-	-	3.15	-	3.15	-	V
		V <sub>CC</sub> = 6.0 V	4.2	-	-	4.2	-	4.2	-	V
V <sub>IL</sub>	LOW-level	control inputs								
	input voltage	V <sub>CC</sub> = 2.0 V	-	-	0.5	-	0.5	-	0.5	V
		V <sub>CC</sub> = 3.0 V	-	-	0.9	-	0.9	-	0.9	V
		V <sub>CC</sub> = 3.3 V	-	-	1.0	-	1.0	-	1.0	V
		V <sub>CC</sub> = 4.5 V	-	-	1.35	-	1.35	-	1.35	V
		V <sub>CC</sub> = 6.0 V	-	-	1.8	-	1.8	-	1.8	V

### 8-channel analog multiplexer/demultiplexer with injection-current effect control

Symbol	Parameter	Conditions		25 °C			°C to 5 °C	-40 °C to +125 °C		Unit
			Min	Тур	Max	Min	Max	Min	Max	1
lı	input leakage current	control inputs; $V_I$ = GND or $V_{CC}$ ; $V_{CC}$ = 6.0 V	-	-	±0.1	-	±0.1	-	±1.0	μA
I <sub>S(OFF)</sub>	OFF-state leakage current	$\overline{E} = V_{IH}; V_I = GND \text{ or } V_{CC};$ $V_O = V_{CC} \text{ or } GND; V_{CC} = 6.0 \text{ V};$ see <u>Fig. 6</u>								
		per channel	-	-	±0.1	-	±0.5	-	±1.0	μA
		all channels	-	-	±0.2	-	±2.0	-	±4.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	$E = V_{IL}; V_I = GND \text{ or } V_{CC};$ $V_O = V_{CC} \text{ or } GND; V_{CC} = 6.0 \text{ V};$ see Fig. 7	-	-	±0.1	-	±0.5	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_{I}$ = GND or $V_{CC}$ ; $V_{CC}$ = 6.0 V	-	-	2.0	-	5.0	-	20.0	μA
Cı	input capacitance	S0, S1, S2 and $\overline{E}$	-	2	10	-	10	-	10	pF
C <sub>sw</sub>	switch	Z; OFF-state	-	15	40	-	40	-	40	pF
	capacitance	Yn; OFF-state	-	3	15	-	15	-	15	pF
74HCT4	851									
V <sub>IH</sub>	HIGH-level input voltage	control inputs; $V_{CC}$ = 4.5 V to 5.5 V	2.0	-	-	2.0	-	2.0	-	V
V <sub>IL</sub>	LOW-level input voltage	control inputs; $V_{CC}$ = 4.5 V to 5.5 V	-	-	0.8	-	0.8	-	0.8	V
I <sub>I</sub>	input leakage current	control inputs; V <sub>I</sub> = GND or V <sub>CC</sub> ; V <sub>CC</sub> = 5.5 V	-	-	±0.1	-	±0.1	-	±1.0	μA
I <sub>S(OFF)</sub>	OFF-state leakage current	$\overline{E} = V_{IH}; V_I = GND \text{ or } V_{CC};$ $V_O = V_{CC} \text{ or } GND; V_{CC} = 5.5 \text{ V};$ see Fig. 6								
		per channel	-	-	±0.1	-	±0.5	-	±1.0	μA
		all channels	-	-	±0.2	-	±2.0	-	±4.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	$      E = V_{IL}; V_I = GND \text{ or } V_{CC};        V_O = V_{CC} \text{ or } GND; V_{CC} = 5.5 \text{ V};        see Fig. 7                                   $	-	-	±0.1	-	±0.5	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_{I}$ = GND or $V_{CC}$ ; $V_{CC}$ = 5.5 V	-	-	2.0	-	5.0	-	20.0	μA
∆I <sub>CC</sub>	additional supply current	control inputs; $V_I = V_{CC} - 2.1 V$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 V$ to 5.5 V; $I_0 = 0 A$	-	-	300	-	370	-	370	μA
CI	input capacitance	S0, S1, S2 and $\overline{E}$	-	2	10	-	10	-	10	pF
C <sub>sw</sub>	switch	Z; OFF-state	-	15	40	-	40	-	40	pF
	capacitance	Yn; OFF-state	-	3	15	-	15	-	15	pF

### 8-channel analog multiplexer/demultiplexer with injection-current effect control



# **11. Dynamic characteristics**

### Table 9. Dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground 0 V); for test circuit see Fig. 14.

Symbol	Parameter	Conditions		25 °C			°C to 5 °C		°C to 5 °C	Unit
			Min	Тур	Max	Min	Max	Min	Max	
74HC48	51	·								
t <sub>pd</sub>	propagation	Z to Yn, Yn to Z; see Fig. 10 [1]								
	delay	V <sub>CC</sub> = 2.0 V	-	10.0	25	-	29	-	32	ns
		V <sub>CC</sub> = 3.0 V	-	6.0	15.5	-	17.5	-	19.5	ns
		V <sub>CC</sub> = 3.3 V	-	5.0	14.5	-	16.5	-	18.5	ns
		V <sub>CC</sub> = 4.5 V	-	4.0	11.5	-	12.5	-	13.5	ns
		V <sub>CC</sub> = 6.0 V	-	3.0	10	-	11	-	12	ns
		Sn to Z, Sn to Yn; see Fig. 11 [1]								
		V <sub>CC</sub> = 2.0 V	-	18.0	32	-	35	-	40	ns
		V <sub>CC</sub> = 3.0 V	-	9.5	17.5	-	20	-	23	ns
		V <sub>CC</sub> = 3.3 V	-	8.5	16.5	-	19	-	22	ns
		V <sub>CC</sub> = 4.5 V	-	6.5	13	-	15	-	17	ns
		V <sub>CC</sub> = 6.0 V	-	5.0	12.5	-	14.5	-	16.5	ns
t <sub>en</sub>	enable time	$\overline{E}$ to Z, $\overline{E}$ to Yn; see <u>Fig. 12</u> [2]								
		V <sub>CC</sub> = 2.0 V	-	-	95	-	105	-	115	ns
		V <sub>CC</sub> = 3.0 V	-	-	90	-	100	-	110	ns
		V <sub>CC</sub> = 3.3 V	-	-	85	-	95	-	105	ns
		$V_{\rm CC}$ = 4.5 V	-	-	80	-	90	-	100	ns
		V <sub>CC</sub> = 6.0 V	-	-	78	-	80	-	80	ns
t <sub>dis</sub>	disable time	$\overline{E}$ to Z, $\overline{E}$ to Yn; see <u>Fig. 12</u> [3]								
		V <sub>CC</sub> = 2.0 V	-	-	99	-	105	-	115	ns
		V <sub>CC</sub> = 3.0 V	-	-	90	-	100	-	110	ns
		V <sub>CC</sub> = 3.3 V	-	-	85	-	95	-	105	ns
		$V_{CC} = 4.5 V$	-	-	80	-	90	-	100	ns
		V <sub>CC</sub> = 6.0 V	-	-	78	-	80	-	80	ns
C <sub>PD</sub>	power	per channel; see <u>Fig. 13</u> [4]								
	dissipation	V <sub>CC</sub> = 3.3 V	-	28	-	-	-	-	-	pF
	capacitance	V <sub>CC</sub> = 5.0 V	-	33	-	-	-	-	-	pF

### 8-channel analog multiplexer/demultiplexer with injection-current effect control

Symbol	Parameter	Conditions	25 °C			-40 °C to +85 °C		-40 °C to +125 °C		Unit
			Min	Тур	Мах	Min	Мах	Min	Max	1
74HCT4	851									
t <sub>pd</sub>	propagation	Z to Yn, Yn to Z; see Fig. 10 [1]								
	delay	V <sub>CC</sub> = 4.5 V	1.6	3.7	11.5	1.1	12.5	1.1	13.5	ns
		Sn to Z, Sn to Yn; see Fig. 11 [1]								
		V <sub>CC</sub> = 4.5 V	3.2	8.0	13	2.3	15	2.3	17	ns
t <sub>en</sub>	enable time	$\overline{E}$ to Z, $\overline{E}$ to Yn; see <u>Fig. 12</u> [2]								
		V <sub>CC</sub> = 4.5 V	4.2	8.6	25	3.0	30	3.0	35	ns
t <sub>dis</sub>	disable time	$\overline{E}$ to Z, $\overline{E}$ to Yn; see <u>Fig. 12</u> [3]								
		$V_{CC} = 4.5 V$	28.5	64.7	80	28.2	90	28	100	ns
C <sub>PD</sub>	power	per channel; see Fig. 13 [4]								
	dissipation capacitance	V <sub>CC</sub> = 5.0 V	-	30	-	-	-	-	-	pF

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .

[3]  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

[4]  $C_{PD}$  is used to determine the dynamic power dissipation (P<sub>D</sub> in  $\mu$ W):

 $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} + \sum \{(C_{L} + C_{sw}) \times V_{CC}^{2} \times f_{o}\} \text{ where:}$ 

f<sub>i</sub> = input frequency in MHz;

 $f_o$  = output frequency in MHz;


 $\sum \{ (C_{L} + C_{sw}) \times V_{CC}^{2} \times f_{o} \} = sum of outputs;$ 


 $C_L$  = output load capacitance in pF;

 $C_{sw}$  = switch capacitance in pF;


 $V_{CC}$  = supply voltage in V.

### 11.1. Waveforms and test circuit






### 8-channel analog multiplexer/demultiplexer with injection-current effect control




Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.


### Fig. 12. Enable and disable times

Туре	Input		Output		
	V <sub>M</sub>	VI	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>
74HC4851	0.5V <sub>CC</sub>	V <sub>CC</sub>	0.5V <sub>CC</sub>	V <sub>OL</sub> + 0.1(V <sub>CC</sub> - V <sub>OL</sub> )	0.9V <sub>OH</sub>
74HCT4851	1.3 V	3.0 V	0.5V <sub>CC</sub>	V <sub>OL</sub> + 0.1(V <sub>CC</sub> - V <sub>OL</sub> )	0.9V <sub>OH</sub>



### 8-channel analog multiplexer/demultiplexer with injection-current effect control





Definitions for test circuit:

 $R_{I}$  = load resistance.

 $C_{L}$  = load capacitance including jig and probe capacitance.

 $R_T$  = termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.

a. Input pulse definition

#### Fig. 14. Test circuit for measuring switching times


### Table 11. Test data

Test	Input			Output		S1 position
	Control E, Sn	Switch Yn (Z)	t <sub>r</sub> , t <sub>f</sub>	Switch Z (Yr	ו)	
	V <sub>I</sub> [1]	VI		CL	RL	
t <sub>PHL,</sub> t <sub>PLH</sub>	V <sub>CC</sub>	V <sub>CC</sub>	6 ns	50 pF	-	open
t <sub>PHZ</sub> , t <sub>PZH</sub>	V <sub>CC</sub>	V <sub>CC</sub>	6 ns	50 pF	10 kΩ	GND
t <sub>PLZ</sub> , t <sub>PZL</sub>	V <sub>CC</sub>	V <sub>CC</sub>	6 ns	50 pF	10 kΩ	V <sub>CC</sub>
C <sub>PD</sub>	V <sub>CC</sub>	V <sub>CC</sub>	6 ns	0 pF	-	open

b. Test circuit

[1] For 74HCT4851: input voltage  $V_I = 3.0 V$ .

# 12. Package outline



### Fig. 15. Package outline SOT109-1 (SO16)




Fig. 16. Package outline SOT403-1 (TSSOP16)

<sup>74</sup>HC\_HCT4851




Fig. 17. Package outline SOT763-1 (DHVQFN16)

# 13. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model

### 14. Revision history

#### Table 13. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74HC_HCT4851 v.3	20180824	Product data sheet	-	74HC_HCT4851_2
Modifications:	of Nexperia.	f this data sheet has been i ave been adapted to the ne	C C	nply with the identity guidelines e where appropriate.
74HC_HCT4851_2	20080902	Product data sheet	-	74HC4851_1
Modifications:	• 74HCT4851	device added.		
74HC4851_1	20070309	Product data sheet	-	-

# 15. Legal information

#### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# **Contents**

1. General description	1
2. Features and benefits	1
3. Applications	1
4. Ordering information	2
5. Functional diagram	2
6. Pinning information	4
6.1. Pinning	4
6.2. Pin description	4
7. Functional description	5
8. Limiting values	5
<ol> <li>8. Limiting values</li> <li>9. Recommended operating condition</li> </ol>	
	ons6
9. Recommended operating condition	ons6
9. Recommended operating condition 10. Static characteristics	ons6 6 10
9. Recommended operating condition 10. Static characteristics 11. Dynamic characteristics	ons6 6 10 11
<ol> <li>Recommended operating condition</li> <li>Static characteristics</li> <li>Dynamic characteristics</li> <li>11.1. Waveforms and test circuit</li> </ol>	ons6 6 10 11
<ol> <li>Recommended operating condition</li> <li>Static characteristics</li></ol>	ons6 10 11 14 17

© Nexperia B.V. 2018. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 24 August 2018

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

 74HC4851BQ,115
 74HC4851D,112
 74HC4851D,118
 74HC4851PW,112
 74HC4851PW,118
 74HCT4851BQ,115

 74HCT4851D,112
 74HCT4851D,118
 74HCT4851PW,112
 74HCT4851PW,118
 74HCT4851PW