

A758, Polymer Aluminum, 220 uF, 20%, 16 VDC, -55/+105°C, Lead Spacing = 3.5mm



Dimensions	
D	8mm +/-0.5mm
L	8mm +/-1mm
S	3.5mm +/-0.5mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Ammo
Packaging Quantity:	1000

General Information	
Supplier:	KEMET
Series:	A758
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications	
Capacitance:	220 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC, 18.4 VDC (Surge)
Temperature Range:	-55/+105°C
Rated Temperature:	105°C
Life:	5000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	10.00% 120Hz 20c
Resistance:	14 mOhms (100kHz 20C)
Ripple Current:	4800 mAmps (100kHz 105C)
Leakage Current:	528 uA (2min 20°C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25