


Features

- Complementary Pair
- Epitaxial Planar Die Construction
- One 2222A Type (NPN),
One 2907A Type (PNP)
- Ideal for Low Power Amplification and Switching
- Lead Free By Design/RoHS Compliant (Note 2)**
- "Green Device" (Note 3)**


Mechanical Data

- Case: SOT-26
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020C
- Terminals: Finish - Matte Tin annealed over Copper leadframe. Solderable per MIL-STD-202, Method 208
- Terminal Connections: See Diagram
- Ordering & Date Code Information: See Page 3
- Marking (See Page 3): K27
- Weight: 0.006 grams (approximate)



SOT-26			
Dim	Min	Max	Typ
A	0.35	0.50	0.38
B	1.50	1.70	1.60
C	2.70	3.00	2.80
D			0.95
F			0.55
H	2.90	3.10	3.00
J	0.013	0.10	0.05
K	1.00	1.30	1.10
L	0.35	0.55	0.40
M	0.10	0.20	0.15
	0	8	
All Dimensions in mm			

Note: E1, B1, and C1 = 2907A Type (PNP),
E2, B2, and C2 = 2222A Type (NPN).
Type marking indicates orientation.



Maximum Ratings, 2222A Type (NPN)

@ T_A = 25 C unless otherwise specified

Characteristic	Symbol	2222A (NPN)	Unit
Collector-Base Voltage	V _{CBO}	75	V
Collector-Emitter Voltage	V _{CEO}	40	V
Emitter-Base Voltage	V _{EBO}	6.0	V
Collector Current - Continuous	I _C	600	mA

Maximum Ratings, 2907A Type (PNP)

@ T_A = 25 C unless otherwise specified

Characteristic	Symbol	2907A (PNP)	Unit
Collector-Base Voltage	V _{CBO}	-60	V
Collector-Emitter Voltage	V _{CEO}	-60	V
Emitter-Base Voltage	V _{EBO}	-5.0	V
Collector Current - Continuous	I _C	-600	mA

Maximum Ratings, Total

@ T_A = 25 C unless otherwise specified

Characteristic	Symbol	Value	Unit
Total Power Dissipation (Note 1)	P _d	300	mW
Thermal Resistance, Junction to Ambient (Note 1)	R _{JA}	417	C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	C

- Note:
- Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch; pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at <http://www.diodes.com/datasheets/ap02001.pdf>.
 - No purposefully added lead.
 - Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.

Electrical Characteristics, 2222A Type (NPN)

 @ $T_A = 25\text{ C}$ unless otherwise specified

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 4)					
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	75		V	$I_C = 10\text{ A}, I_E = 0$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	40		V	$I_C = 10\text{ mA}, I_B = 0$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	6.0		V	$I_E = 10\text{ A}, I_C = 0$
Collector Cutoff Current	I_{CBO}		10	nA A	$V_{CB} = 60\text{ V}, I_E = 0$ $V_{CB} = 60\text{ V}, I_E = 0, T_A = 150\text{ C}$
Collector Cutoff Current	I_{CEX}		10	nA	$V_{CE} = 60\text{ V}, V_{EB(OFF)} = 3.0\text{ V}$
Emitter Cutoff Current	I_{EBO}		10	nA	$V_{EB} = 3.0\text{ V}, I_C = 0$
Base Cutoff Current	I_{BL}		20	nA	$V_{CE} = 60\text{ V}, V_{EB(OFF)} = 3.0\text{ V}$
ON CHARACTERISTICS (Note 4)					
DC Current Gain	h_{FE}	35 50 75 100 40 50 35	300		$I_C = 100\text{ A}, V_{CE} = 10\text{ V}$ $I_C = 1.0\text{ mA}, V_{CE} = 10\text{ V}$ $I_C = 10\text{ mA}, V_{CE} = 10\text{ V}$ $I_C = 150\text{ mA}, V_{CE} = 10\text{ V}$ $I_C = 500\text{ mA}, V_{CE} = 10\text{ V}$ $I_C = 10\text{ mA}, V_{CE} = 10\text{ V}, T_A = -55\text{ C}$ $I_C = 150\text{ mA}, V_{CE} = 1.0\text{ V}$
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$		0.3 1.0	V	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$ $I_C = 500\text{ mA}, I_B = 50\text{ mA}$
Base-Emitter Saturation Voltage	$V_{BE(SAT)}$	0.6	1.2 2.0	V	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$ $I_C = 500\text{ mA}, I_B = 50\text{ mA}$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C_{obo}		8	pF	$V_{CB} = 10\text{ V}, f = 1.0\text{ MHz}, I_E = 0$
Input Capacitance	C_{ibo}	—	25	pF	$V_{EB} = 0.5\text{ V}, f = 1.0\text{ MHz}, I_C = 0$
Current Gain-Bandwidth Product	f_T	300		MHz	$V_{CE} = 20\text{ V}, I_C = 20\text{ mA},$ $f = 100\text{ MHz}$
SWITCHING CHARACTERISTICS					
Delay Time	t_d		10	ns	$V_{CC} = 30\text{ V}, I_C = 150\text{ mA},$ $V_{BE(off)} = -0.5\text{ V}, I_{B1} = 15\text{ mA}$
Rise Time	t_r		25	ns	
Storage Time	t_s		225	ns	$V_{CC} = 30\text{ V}, I_C = 150\text{ mA},$ $I_{B1} = I_{B2} = 15\text{ mA}$
Fall Time	t_f		60	ns	

 Note: 4. Pulse test: Pulse width 300 μ s, duty cycle 2%.

Electrical Characteristics, 2907A Type (PNP) @ $T_A = 25\text{ C}$ unless otherwise specified

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 5)					
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-60		V	$I_C = -10\text{ A}, I_E = 0$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-60		V	$I_C = -10\text{mA}, I_B = 0$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5.0		V	$I_E = -10\text{ A}, I_C = 0$
Collector Cutoff Current	I_{CBO}		-10	nA A	$V_{CB} = -50\text{V}, I_E = 0$ $V_{CB} = -50\text{V}, I_E = 0, T_A = 125\text{ C}$
Collector Cutoff Current	I_{CEX}		-50	nA	$V_{CE} = -30\text{V}, V_{EB(OFF)} = -0.5\text{V}$
Base Cutoff Current	I_{BL}		-50	nA	$V_{CE} = -30\text{V}, V_{EB(OFF)} = -0.5\text{V}$
ON CHARACTERISTICS (Note 5)					
DC Current Gain	h_{FE}	75 100 100 100 50	300		$I_C = -100\mu\text{A}, V_{CE} = -10\text{V}$ $I_C = -1.0\text{mA}, V_{CE} = -10\text{V}$ $I_C = -10\text{mA}, V_{CE} = -10\text{V}$ $I_C = -150\text{mA}, V_{CE} = -10\text{V}$ $I_C = -500\text{mA}, V_{CE} = -10\text{V}$
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$		-0.4 -1.6	V	$I_C = -150\text{mA}, I_B = -15\text{mA}$ $I_C = -500\text{mA}, I_B = -50\text{mA}$
Base-Emitter Saturation Voltage	$V_{BE(SAT)}$		-1.3 -2.6	V	$I_C = 150\text{mA}, I_B = 15\text{mA}$ $I_C = 500\text{mA}, I_B = 50\text{mA}$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C_{obo}		8.0	pF	$V_{CB} = -10\text{V}, f = 1.0\text{MHz}, I_E = 0$
Input Capacitance	C_{ibo}	—	30	pF	$V_{EB} = -2.0\text{V}, f = 1.0\text{MHz}, I_C = 0$
Current Gain-Bandwidth Product	f_T	200		MHz	$V_{CE} = -20\text{V}, I_C = -50\text{mA}, f = 100\text{MHz}$
SWITCHING CHARACTERISTICS					
Turn-On Time	t_{on}		45	ns	$V_{CC} = -30\text{V}, I_C = -150\text{mA}, I_{B1} = -15\text{mA}$
Delay Time	t_d		10	ns	
Rise Time	t_r		40	ns	
Turn-Off Time	t_{off}		100	ns	$V_{CC} = -6.0\text{V}, I_C = -150\text{mA}, I_{B1} = I_{B2} = -15\text{mA}$
Storage Time	t_s		80	ns	
Fall Time	t_f		30	ns	


Note: 5. Short duration pulse test used to minimize self-heating effect.

Ordering Information (Note 6)

Device	Packaging	Shipping
MMDT2227M-7	SOT-26	3000/Tape & Reel

Note: 6. For Packaging Details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

Marking Information



K27 = Product Type Marking Code
 YM = Date Code Marking
 Y = Year ex: S = 2005
 M = Month ex: 9 = September

Date Code Key

Year	2005	2006	2007	2008	2009	2010	2011	2012
Code	S	T	U	V	W	X	Y	Z

Month	Jan	Feb	March	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D




Fig. 1 (2222A) Typical Capacitance




Fig. 2 (2222A) Typical Collector Saturation Region




Fig. 3 (2907A) Typical Capacitance




Fig. 4 (2907A) Typical Collector Saturation Region

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.