

Specification Sheet

Part Number: 596-00868

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.

Aggressive adhesive ensures strong bond, even on powder coated surfaces.

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

Optional Paint Shields provide additional protection for pre-printed and variable data placards.



Metal Solar Placard, Blank Plate For Engraving, 3.75" x 2.0", AA, Orange/Black, 5/pkg

Article Number 596-00868

Type BLANK375X2

Color Black (BK)

Quantity Per pack

Product Description Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, engravable placards are designed to meet industry codes. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description	Metal Solar Placard, Blank Plate For Engraving, 3.75" x 2.0", AA, Orange/Black, 5/pkg
Global Part Name	BLANK375X2-AA-BK
Technical Description	3.75" X 2.00" Black text on an Orange/black sign for engraving custom metal placards - 5 per pack.
Length L (Imperial)	3.75
Length L (Metric)	95.25
Width W (Imperial)	3.75
Width W (Metric)	95.25
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)

Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 NEC2014
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	3919905060
Labels per Column	1
Labels per Row	1