




Molded, SOT-23 Thin Film Resistor, Surface Mount Divider Network



Vishay Dale Thin Film MPM Series Dividers provide ± 2 ppm/ $^{\circ}$ C tracking and a ratio tolerance as tight as 0.01 %, small size, and exceptional stability for all surface mount applications. The standard SOT-23 package format with unity and common standard resistance divider ratios provide easy selection for most applications requiring matched pair resistor elements. The ratios listed are available for off the shelf delivery. If you require a non-standard ratio, consult the applications engineering group as we may be able to meet your requirements.

SCHEMATIC



FEATURES

- Excellent long term ratio stability ($\Delta R \pm 0.015$ %, 2000 h, +70 $^{\circ}$ C)
- Ratio tolerances to ± 0.01 %
- Low TCR tracking ± 2 ppm
- Standard JEDEC TO-236 package variation AB
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available
HALOGEN FREE

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

TYPICAL PERFORMANCE

	ABSOLUTE	TRACKING
TCR	25	2
	ABSOLUTE	RATIO
TOL.	0.1	0.05

STANDARD DIVIDER RATIO (R₂/R₁)


RATIO	R ₂ (Ω)	R ₁ (Ω)	RATIO	R ₂ (Ω)	R ₁ (Ω)
100:1	100K	1K	2:1	10K	5K
50:1	50K	1K	2:1	2K	1K
25:1	25K	1K	1:1	100K	100K
20:1	20K	1K	1:1	50K	50K
10:1	20K	2K	1:1	25K	25K
10:1	10K	1K	1:1	10K	10K
9:1	9K	1K	1:1	5K	5K
9:1	900	100	1:1	2.5K	2.5K
6:1	6K	1K	1:1	2K	2K
5:1	10K	2K	1:1	1K	1K
5:1	5K	1K	1:1	500	500
4:1	8K	2K	1:1	250	250
4:1	4K	1K	1:2	5K	10K
3:1	7.5K	2.5K	1:2.5	10K	25K
2:1	50K	25K	1:4	7.5K	30K
2:1	12K	6K	1:9	10K	90K

STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin/Lead Number	3	-
Resistance Range	250 Ω to 100 kΩ per resistor	-
TCR: Absolute	± 25 ppm/ $^{\circ}$ C	-55 $^{\circ}$ C to +125 $^{\circ}$ C
TCR: Tracking	± 2 ppm/ $^{\circ}$ C (typical)	-55 $^{\circ}$ C to +125 $^{\circ}$ C
Tolerance: Absolute	± 0.05 % to ± 1.0 %	+25 $^{\circ}$ C
Tolerance: Ratio	± 0.01 % to 0.5 %	+25 $^{\circ}$ C
Power Rating: Resistor	100 mW	Maximum at +70 $^{\circ}$ C
Power Rating: Package	200 mW	Maximum at +70 $^{\circ}$ C
Stability: Absolute	$\Delta R \pm 0.05$ %	2000 h at +70 $^{\circ}$ C
Stability: Ratio	$\Delta R \pm 0.015$ %	2000 h at +70 $^{\circ}$ C
Voltage Coefficient	0.1 ppm/V	-
Working Voltage	100 V max. not to exceed $\sqrt{P \times R}$	-
Operating Temperature Range	-55 $^{\circ}$ C to +125 $^{\circ}$ C	-
Storage Temperature Range	-55 $^{\circ}$ C to +150 $^{\circ}$ C	-
Noise	< -30 dB	-
Thermal EMF	0.2 μ V/ $^{\circ}$ C	-
Shelf Life Stability: Absolute	$\Delta R \pm 0.01$ %	1 year at +25 $^{\circ}$ C
Shelf Life Stability: Ratio	$\Delta R \pm 0.002$ %	1 year at +25 $^{\circ}$ C

DIMENSIONS AND IMPRINTING in inches and millimeters				
DIMENSION	INCHES		MILLIMETERS	
	MIN.	MAX.	MIN.	MAX.
A	0.031	0.040	0.79	1.02
A1	0.001	0.004	0.02	0.10
B	0.105	0.120	2.67	3.05
S	0.071	0.079	1.80	2.00
W	0.015	0.021	0.38	0.54
L	0.083	0.098	2.10	2.50
H	0.047	0.055	1.20	1.40
T	0.005	0.010	0.13	0.25
J	0.0035	0.0059	0.089	0.15
K	0.017	0.022	0.44	0.55
Ø	0	8°	0	8°

MECHANICAL SPECIFICATIONS	
Resistive Element	Passivated nichrome
Substrate Material	Silicon
Body	Molded epoxy
Terminals	Copper alloy
Lead (Pb)-free Option	100 % matte tin
Tin Lead Option	Sn85
Tin Lead and Lead (Pb)-free Finish	Plated



GLOBAL PART NUMBER INFORMATION																								
New Global Part Numbering: MPM1003AWS																								
M	P	M	1	0	0	3	A	W	S	M	P	M	T	1	0	0	1	5	0	0	1	A	T	1
GLOBAL MODEL (3 or 4 digits)			RESISTANCE (4 or 8 digits)				TOLERANCE AND RATIO TOLERANCE			PACKAGING														
MPM (Tin lead) MPMT (Lead (Pb)-free) (e3)			First 3 digits are significant figures and the last digit specifies the number of zeros to follow. When like values are required use total resistance. When dual values are required list both values. Example: (List R ₁ first in part number with dual values) 1002 = 10K (5K/5K) 1003 = 100K (50K/50K) 10011002 = 1K/10K divider				Abs. Tol. Ratio A = 0.1 % 0.05 % B = 0.1 % 0.1 % C = 0.25 % 0.1 % D = 0.5 % 0.1 % F = 1 % 0.5 % Z = 0.1 % ⁽¹⁾ 0.025 % Q = 0.05 % ⁽¹⁾ 0.01 %			BS = BULK 100 min., 1 mult WS = WAFFLE 100 min., 1 mult TAPE AND REEL T0 = 100 min., 100 mult T1 = 1000 min., 1000 mult ⁽²⁾ T3 = 300 min., 300 mult T5 = 500 min., 500 mult TF = Full reel 4000 TS = 100 min., 1 mult														
Historical Part Number example: MPM1002BW (for reference purposes only)																								
MPM			1002				B			W														
SERIES			RESISTANCE				TOLERANCE AND RATIO TOLERANCE			PACKAGING														

Notes

- ⁽¹⁾ Tol. available 1K and up equal values only
⁽²⁾ Preferred packaging code



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[MPMT1001AT1](#) [MPMT1002AT5](#) [MPMT2002DT5](#) [MPMT2002AT5](#) [MPMT1003AT5](#) [MPMT10012002AWS](#)
[MPMT1002BTS](#) [MPMT50011002BT5](#) [MPMT20011002BT1](#) [MPMT10011003FT0](#) [MPMT50011002AWS](#)
[MPMT20011001ATF](#) [MPMT50011002FWS](#) [MPMT10011003AWS](#) [MPMT10011002DTS](#) [MPMT5000AT1](#)
[MPMT50027502DBS](#) [MPMT50011002DWS](#) [MPMT10011002AWS](#) [MPMT1001/1002A](#) [MPM1002AT1](#) [MPM1003AT1](#)
[MPM20011002AT1](#) [MPM2001AT1](#) [MPM2002AT1](#) [MPM5001AT1](#) [MPMT50011002BT1](#) [MPMT50011002DT1](#)
[MPMT5002BT1](#) [MPMT2002FT1](#) [MPMT10011002AT1](#) [MPMT10014001AT1](#) [MPMT10019001AT1](#) [MPMT1002AT1](#)
[MPMT1003AT1](#) [MPMT20011002AT1](#) [MPMT20018001AT5](#) [MPMT2001AT1](#) [MPMT2002AT1](#) [MPMT5001AT1](#)
[MPMT5002AT1](#) [MPMT20018001DT0](#) [MPM1001AT5](#) [MPM2002AT5](#) [MPM5000FT5](#) [MPM2002/6002AT5](#)
[MPM5002DT5](#) [MPM50011002BT5](#) [MPM2002FT5](#) [MPM2002CT5](#) [MPM5001AWS](#) [MPM5001DT5](#) [MPM1001AWS](#)
[MPM50011002BWS](#) [MPM2001BWS](#) [MPM1002AT5](#) [MPM2002AWS](#) [MPM1001BWS](#) [MPM2001AWS](#) [MPM5001AT5](#)
[MPM1003AT5](#) [MPM1003AWS](#) [MPM2001AT5](#) [MPMT20011002AWS](#) [MPM1002QT5](#) [MPM5002AWS](#) [MPM5002AT5](#)
[MPM1001BT5](#) [MPMT2001AT5](#) [MPM5002AT1](#) [MPM10019001AT1](#) [MPMT50011002AT5](#) [MPM10014001ATS](#)
[MPM1001BTS](#) [MPM10027002AWS](#) [MPM1002QT1](#) [MPM20018001DT3](#) [MPM2002CT1](#) [MPM2002FT1](#)
[MPM50011002BT1](#) [MPM50011002DT1](#) [MPM5002BT1](#) [MPMT1002QT1](#) [MPMT20018001BTS](#) [MPMT5000FTS](#)
[MPMT5001DTS](#) [MPMT20018001AT1](#) [MPMT10016001AT1](#) [MPMT10011003AT1](#) [MPMT2001ATS](#)
[MPMT10015002ATS](#) [MPMT50011002AT1](#) [MPMT10012002AT5](#) [MPMT10012502AT1](#) [MPMT2003AT5](#)
[MPMT10011002ATS](#) [MPMT2003AT1](#) [MPMT10012001AT1](#) [MPM2002AT0](#) [MPMT10012001AT5](#)