

## Service MANOSKOP® torque wrench

### 730 Quick



Art.No. **50184040**  
 GTIN **4018754268887**  
 Model **730/40 QUICK**

#### Label.

Service MANOSKOP torque wrench No. 730 Quick Values only for in-lb 80-400Nm  
 Inside square stitch size 14x18 mm L. 590mm

#### Description.

- click-type
- the measuring element is only under load while force is being applied, no need for manual reset to zero
- mount for interchangeable insert/shell tools
- QuickRelease safety lock (sizes 5–65)
- rapid setting thanks to easy-action locking lever in the handle (sizes 5–65)
- ergonomically designed, non-slip adjuster with a thumb recess
- magnifying glass integrated in the display window
- optimised convex handle for strain-free working
- dual stop signal
- twin scales N·m/ft·lb and N·m/in·lb (sizes 5–80)
- on request also available as an N·m-only version without twin scale (sizes 5–65)
- can be applied for either clockwise or anticlockwise tightening by turning the inserts over
- any force applied to the tool after the 'click' or applied in the opposite direction to the current function – e.g. forcible loosening of a jammed screw - does not act on the trigger mechanism and cannot cause damage to it
- calibration using perfectControl® calibrating unit No 7794 or calibration system No 7706. Readjustment does not require disassembly.
- certificate in accordance with DIN EN ISO 6789-2:2017
- **display deviation value  $\pm 4\%$**

## Advantages.

Fast setting with easy-to-operate clamping lever in the handle, integrated lens for better readability of the set value

Ergonomically shaped, non-slip adjustment element with thumb recess and optimised ball handle for fatigue-free work


Efficient. No reset to "0" necessary, as measuring element is only strained during the tightening process

Releasing torque wrench with receptacle for exchangeable plug-in tools, double stop signal (tactile

and audible), left-hand tightening by turning over the plug-in tools



## Technical Drawing.



## Technical Attributes.

Breite mm (b)	28 mm
Size	40
Size hexagon socket [internal square]	14x18 mm
Height mm (h)	23 mm
Länge mm (l)	590 mm
LF	570 mm
Measuring range ft-lb	60-300 ft·lb
Measuring range N·m	80-400 N·m
SF	25 mm
Scale division [E1]	10 N·m
Scale division [E2]	10 ft·lb

## Logistics data.

Length (IFS)	592
Width (IFS)	40
Height (IFS)	35
Length (packed, mm)	620
Width (packed, mm)	55
Höhe (verpackt, mm)	55
Code	50184040
Weight	1540 g
Weight (gross, kg)	1,720
Weight PAP (kg)	0,000
Weight PVC (kg)	0,110
GTIN	4018754268887
Numbers of content units per order units	1
Country of origin	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82041100

## Varianten.

Code	Article number (ERP)	Article description (Autom.)	GTIN
50184005	730/5 QUICK	Service MANOSKOP torque wrench No. 730 Quick Values only for in-lb 6-50Nm Inside square stitch size 9x12 mm L. 315mm	4018754268856
50184010	730/10 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 20-100Nm Inside square stitch size 9x12 mm L. 370mm	4018754266203
50184012	730/12 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 25-130Nm Inside square stitch size 14x18 mm L. 410mm	4018754268863
50184020	730/20 QUICK	Service MANOSKOP torque wrench No. 730 Quick Values only for in-lb 40-200Nm Inside square stitch size 14x18 mm L. 455mm	4018754268870
50184030	730/30 QUICK	Service-MANOSKOP torque wrench w.mount f. insert tools No. 730 Quick Values only for in-lb 60-300Nm Inside square stitch size 14x18 mm L. 520mm	4018754324071
50184040	730/40 QUICK	Service MANOSKOP torque wrench No. 730 Quick Values only for in-lb 80-400Nm Inside square stitch size 14x18 mm L. 590mm	4018754268887
50184065	730/65 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 130-650Nm Inside square stitch size 14x18 mm L. 875mm	4018754268894
50184565	730II/65 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 130-650Nm Inside square stitch size 22x28 mm L. 897mm	4018754268900
50584005	730A/5 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 50-440in lb Inside square stitch size 9x12 mm L. 315mm	4018754268979
50584010	730A/10 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 180-880in lb Inside square stitch size 9x12 mm L. 370mm	4018754268986
50584012	730A/12 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-lb 225-1150in lb Inside square stitch size 14x18 mm L. 410mm	4018754268993
50584020	730A/20 QUICK	Basic wrench w.tool carrier for insert tools No. 730 Quick Values only for in-	4018754269006

lb 350-1750in lb Inside square stitch  
size 14x18 mm L. 455mm

## GTIN-Code.



## Accessories.



58240040  
Square drive insert tool

## Images.



**STAHLWILLE Eduard Wille GmbH & Co. KG**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-200  
info@stahlwille.de · www.stahlwille.de · Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal  
Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal