




30 SIGNAL/POWER COMBO CABLE ASSEMBLY/COMPONENTS

MPCC	2	SIGNAL PINS	2	PLATING OPTION	LEAD STYLE	LENGTH	END 1 OPTION	END 2 OPTION
		-16 = Total Signal Pins		-L = 10 μm (0.25 μm) Gold on contact, Tin on tail (Power & Signal)	Specify LEAD STYLE from chart	-"XX.XX" = Assembled Length in Inches (101.60 mm) 04.00" min.	-S = Single End	(Available with -D only)
		-24 = Total Signal Pins		-T = Tin on contact and tail (Power), Gold on contact, Tin on tail (Signal)			-D = Double End	-NUS = Notch up, straight (Pin A1 to Pin AX)

MPCC
Board Mates:
MPTC

SPECIFICATIONS

Insulator Material:
Black LCP
Contact Material:
Signal: BeCu
Power: Copper Alloy
Plating:
Sn or Au over 50 μm (1.27 μm) Ni
Current Rating:
Signal Pin (24 AWG):
3.4 A per pin
(4 adjacent pins powered)
Power Pin (14 AWG):
23.2 A per pin
(1 pin powered)
Operating Temp Range:
-10 °C to +105 °C
Voltage Rating:
300 VAC





SIGNAL PINS	A
16	(44.55) 1.754
24	(48.55) 1.911

LEAD STYLE	PWR/SIG	AWG
-44	PWR	14
	SIG	24
-46	PWR	14
	SIG	26
-48	PWR	14
	SIG	28
-40	PWR	14
	SIG	30
-64	PWR	16
	SIG	24
-66	PWR	16
	SIG	26
-68	PWR	16
	SIG	28
-60	PWR	16
	SIG	30

View complete specifications at: samtec.com?MPCC

IMSC5	POWER PINS	SIGNAL PINS	POWER PINS	L	SERIES	WIRE GAUGE	01	PLATING OPTION
	-02 = Power Pins Per End	-16 = Total Signal Pins	-02 = Power Pins Per End	-L = Latch	CC81L = Contact, Loose	-2426 = 24 to 26 AWG		-L = 10 μm (0.25 μm) Gold on contact
		-24 = Total Signal Pins			CC81R = Contact, Full Reel (17,000 Parts per Reel)	-2830 = 28 to 30 AWG		



Note: Power contact (CC46 Series) information on page 203.

TOOLING

Hand Tool: CAT-HT-281-2430-13 (Signal: 24-30 AWG)
CAT-HT-246-1416-13 (Power: 14-16 AWG)

Extraction Tool: CAT-EX-169-01 (Signal)
CAT-EX-MPSS-01 (Power)

Mini Applicator: CAT-MC-246-1416-XX-01 (Power 14-16 AWG)
CAT-MC-281-2426-XX-01 (Signal: 24-26 AWG)
CAT-MC-281-2830-XX-01 (Signal: 28-30 AWG)

Note: Some lengths, styles and options are non-standard, non-returnable

View complete specifications at: samtec.com?IMSC5, samtec.com?CC81R & samtec.com?CC81L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[MPCC-2-16-2-L-44-15.00-D-NUS](#) [MPCC-2-16-2-L-44-16.00-S](#) [MPCC-2-16-2-L-44-18.00-D-NUS](#) [MPCC-2-16-2-L-44-24.00-S](#) [MPCC-2-16-2-L-48-12.00-S](#) [MPCC-2-16-2-L-48-12.15-S](#) [MPCC-2-16-2-T-60-10.00-D-NUS](#) [MPCC-2-16-2-T-64-04.00-S](#) [MPCC-2-24-2-L-48-11.00-D-NUS](#) [MPCC-2-24-2-L-68-24.00-S](#) [MPCC-2-24-2-T-44-22.00-D-NUS](#) [MPCC-2-24-2-T-44-60.00-D-NUS](#) [MPCC-2-16-2-L-46-36.00-D-NUS](#) [MPCC-2-16-2-L-66-20.00-D-NUS](#) [MPCC-2-24-2-L-40-05.00-D-NUS](#) [MPCC-2-24-2-L-44-08.00-S](#) [MPCC-2-24-2-L-60-14.00-D-NUS](#) [MPCC-2-16-2-T-46-24.00-D-NUS](#) [MPCC-2-16-2-T-64-11.81-S](#) [MPCC-2-16-2-T-68-72.00-D-NUS](#) [MPCC-2-16-2-L-44-07.00-D-NUS](#) [MPCC-2-16-2-L-44-90.00-S](#) [MPCC-2-16-2-L-44-96.00-D-NUS](#) [MPCC-2-16-2-L-46-11.81-D-NUS](#) [MPCC-2-16-2-L-60-10.00-S](#) [MPCC-2-16-2-L-64-04.00-D-NUS](#) [MPCC-2-16-2-L-64-04.00-S](#) [MPCC-2-16-2-L-64-10.00-D-NUS](#) [MPCC-2-16-2-T-44-09.00-D-NUS](#) [MPCC-2-16-2-T-44-10.00-D-NUS](#) [MPCC-2-16-2-T-44-15.00-D-NUS](#) [MPCC-2-24-2-L-44-11.00-S](#) [MPCC-2-24-2-L-44-39.37-S](#) [MPCC-2-24-2-T-64-10.00-D-NUS](#) [MPCC-2-16-2-L-44-07.87-S](#) [MPCC-2-24-2-L-44-05.20-D-NUS](#) [MPCC-2-24-2-L-44-60.00-S](#) [MPCC-2-24-2-L-44-67.00-D-NUS](#) [MPCC-2-24-2-L-44-78.00-S](#) [MPCC-2-24-2-L-64-18.00-S](#) [MPCC-2-24-2-L-64-24.00-D-NUS](#) [MPCC-2-24-2-L-66-05.00-S](#) [MPCC-2-24-2-T-60-08.00-D-NUS](#) [MPCC-2-16-2-L-44-36.00-S](#) [MPCC-2-16-2-L-44-40.00-S](#) [MPCC-2-16-2-L-60-04.00-S](#) [MPCC-2-16-2-L-68-16.00-D-NUS](#) [MPCC-2-16-2-T-44-24.00-D-NUS](#) [MPCC-2-16-2-T-44-40.00-D-NUS](#) [MPCC-2-24-2-L-44-12.00-D-NUS](#) [MPCC-2-24-2-L-64-05.00-D-NUS](#) [MPCC-2-24-2-T-44-04.00-S](#) [MPCC-2-24-2-T-44-08.00-D-NUS](#) [MPCC-2-24-2-T-44-80.00-S](#) [MPCC-2-16-2-L-40-11.81-S](#) [MPCC-2-16-2-L-44-20.00-D-NUS](#) [MPCC-2-16-2-L-48-15.00-S](#) [MPCC-2-16-2-T-64-08.00-D-NUS](#) [MPCC-2-24-2-L-44-14.00-S](#) [MPCC-2-24-2-L-44-18.00-D-NUS](#) [MPCC-2-24-2-L-60-16.00-D-NUS](#) [MPCC-2-24-2-T-44-118.1-D-NUS](#) [MPCC-2-16-2-L-44-05.00-S](#) [MPCC-2-16-2-L-44-10.00-D-NUS](#) [MPCC-2-16-2-L-44-30.00-S](#) [MPCC-2-16-2-L-48-40.00-D-NUS](#) [MPCC-2-16-2-T-44-05.00-S](#) [MPCC-2-16-2-T-44-16.00-S](#) [MPCC-2-24-2-L-48-05.00-D-NUS](#) [MPCC-2-24-2-L-64-17.70-D-NUS](#) [MPCC-2-24-2-T-44-10.00-D-NUS](#) [MPCC-2-16-2-L-68-05.90-D-NUS](#) [MPCC-2-16-2-L-68-10.00-S](#) [MPCC-2-16-2-L-68-12.00-D-NUS](#) [MPCC-2-16-2-L-68-12.00-S](#) [MPCC-2-24-2-L-48-13.00-D-NUS](#) [MPCC-2-24-2-L-60-18.00-D-NUS](#) [MPCC-2-24-2-T-44-11.00-D-NUS](#) [MPCC-2-24-2-T-44-120.0-D-NUS](#) [MPCC-2-16-2-L-44-40.00-D-NUS](#) [MPCC-2-16-2-L-46-12.00-S](#) [MPCC-2-16-2-L-60-08.00-S](#) [MPCC-2-16-2-L-64-15.00-S](#) [MPCC-2-16-2-L-64-36.00-S](#) [MPCC-2-16-2-T-44-04.00-D-NUS](#) [MPCC-2-16-2-T-44-30.00-D-NUS](#) [MPCC-2-16-2-T-64-12.00-S](#) [MPCC-2-24-2-L-40-04.00-S](#) [MPCC-2-24-2-L-44-12.00-S](#) [MPCC-2-24-2-L-44-20.00-S](#) [MPCC-2-24-2-L-44-25.00-D-NUS](#) [MPCC-2-24-2-L-64-08.00-D-NUS](#) [MPCC-2-24-2-T-44-04.01-S](#) [MPCC-2-16-2-L-48-11.81-S](#) [MPCC-2-24-2-L-44-11.81-S](#) [MPCC-2-24-2-L-44-36.00-S](#) [MPCC-2-16-2-L-44-04.01-S](#) [MPCC-2-16-2-L-44-10.00-S](#) [MPCC-2-16-2-L-44-12.00-S](#) [MPCC-2-16-2-L-66-05.00-D-NUS](#)