


## ► Release-type torque drivers

### Micro-Tech® bit drivers

▷ ISO 6789.

- Reduced weight and size specifically designed for low torques.
- Clockwise operation.
- Hexagon socket drive for  $\varnothing$  4 mm bits (optional  $\square$  1/4" drive with adapter ECR.0).
- Supplied with calibration certificate and adjusting key.



	Capacity cN.m	Drive	1 graduation cN.m	Adjusting key	Suitable bits series	L mm	l mm	$\Delta\Delta$ g
<b>A.300MT</b>	4 - 20	4 mm	0,05	82.4	0	96,5	21	75
<b>A.301MT</b>	15 - 75	1/4"	0,5	82.4	1	130,0	23	130

### A.400 Driver with Vernier adjustment

▷ Exceeds ISO 6789 requirements.

- Class II type D (A.400 maintenance).
- One-way drivers, clockwise operation.
- Hexagon socket drive for  $\varnothing$  1/4".
- ECR  $\varnothing$  1/4" -  $\square$  1/4" adaptor for optional sockets and accessories.
- Drive  $\square$  1/4" on the handle for ratchet handle A.300PA.
- Supplied with calibration certificate, adjusting key and individual identification number.




	Torque	Graduation N.m	L mm	$\Delta\Delta$ g
<b>A.402</b>	0.5 to 2.5 Nm	0,1	147	280
<b>A.404</b>	2 to 10 Nm	0,5	147	400

### Drive socket adaptor

#### ECR.0

- adaptor for using  $\square$  1/4" "radio" sockets with the A.300MT and A.340MT series screwdrivers.
- 4 mm hexagonal drive.
- Length 22 mm.
- $\Delta\Delta$  : 7 g.



### Socket adaptor - $\square$ 1/4" - $\varnothing$ 1/4"

#### ECR

- For using 1/4" sockets with drivers A.400, A.440, A.301MT and A.341MT.
- Length 25 mm.
- $\Delta\Delta$  : 15 g.



### Attachable ratchet handle

#### A.300PA

- Ratchet handle gives more tightening power for repetitive work and high torques.
- Fits drivers with 0.50 to 10 N.m torque capacity.
- Max. torque : 30 N.m
- $\Delta\Delta$  : 85 g.




# Release-type torque drivers

## Micro-Tech® tool set

▷ ISO 6789.

- Case-set includes bits and adjusting key.
- Supplied with inspection report.



E	Capacity		Adjusting key	Contents			Dimensions mm	ΔΔ g
	N.m	Screwdriver		Bits⊖	Bits⊕	Bits○		
<b>A.300MTJ1</b>	4-20	A.300MT	82.4	1,8 - 2,5 mm	0,9 - 1,3 - 1,5 - 2 mm	PZ 0 - 1 - 2 mm	185X109X40	300
<b>A.301MTJ1</b>	15-75	A.301MT	82.4	4 - 4,5 - 5,5 mm	1,5 - 2,5 - 3 mm	PZ 0 - 1 mm	185x109x40	370

## Driver bit set $\square$ 1/4"

▷ Exceeds ISO 6789 requirements.

- Class II type D (A.400 maintenance).
- One-way drivers, clockwise operation.
- Hexagon socket drive for  $\square$  1/4".
- Drive  $\square$  1/4" on the handle for ratchet handle A.300PA.
- Supplied with inspection report, adjusting key and individual identification number.
- Case BP.102 and tray PL.436.



E	Screwdriver	Bit holder	Handle	Contents Adjusting key	Contents		
					Bits⊖	Bits○	Bits⊕
<b>A.402J2</b>	A.402	EF.1P4	A.300PA	A.402-20	4,5 - 6,5 - 8 mm	3 - 4 - 5 mm	PZ 1 - 2 - 3 mm
<b>A.404J2</b>	A.404	EF.1PA	A.300PA	A.404-20	4,5 - 6,5 - 8 mm	3 - 4 - 5 mm	PZ 1 - 2 - 3 mm

## Socket set $\square$ 1/4"

▷ Exceeds ISO 6789 requirements.

- Class II type D (A.400 maintenance).
- One-way drivers, clockwise operation.
- Hexagon socket drive for  $\square$  1/4".
- ECR  $\square$  1/4" -  $\square$  1/4" adaptor for sockets and accessories.
- Drive  $\square$  1/4" on the handle for ratchet handle A.300PA.
- Supplied with inspection report, adjusting key and individual identification number.
- Supplied with adaptor ECR, extensions R.210 and R.215.
- Case BP.115 and tray PL.434.



E	Screwdriver	Handle	Adjusting key	Contents
				Socket
<b>A.402J1</b>	A.402	A.300PA	A402-20	R.3,2-4-5-5,5-6-7-8-9-10 mm
<b>A.404J1</b>	A.404	A.300PA	A404-20	R.3,2-4-5-5,5-6-7-8-9-10 mm

