

## Coaxial Cable Connector 16\_MMBX-50-2-2/111\_N

### Description

Right angle cable plug

Interface standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0011 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing	DOU-00006252
Catalogue drawing	DOU-00006254
Assembly instruction	DOC-0000178673

### Ordering Information

Single package	16_MMBX-50-2-2/111_NE
Bulk 100 pcs package	16_MMBX-50-2-2/111_NH

### Additional Information

Suitable cables	ENVIROFLEX_316_D, K_02252_D, G_02232_D
-----------------	--

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[16\\_MMBX-50-2-2/111\\_NE](#)