## KEMET Part Number: C0603C224K9RACTU

(C0603C224K9RAC7867)



SMD Comm X7R, Ceramic, 0.22 uF, 10%, 6.3 VDC, X7R, SMD, MLCC, Temperature Stable, Class II, 0603



Dimensions	
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
Т	0.8mm +/-0.07mm
S	0.7mm MIN
В	0.35mm +/-0.15mm

Packaging Specifications		
Packaging:	T&R, 180mm, Paper Tape	
Packaging Quantity:	4000	

General Information		
Supplier:	KEMET	
Series:	SMD Comm X7R	
Style:	SMD Chip	
Description:	SMD, MLCC, Temperature Stable, Class II	
Features:	Temperature Stable, Class II	
RoHS:	Yes	
Termination:	Tin	
Marking:	No	
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 48 hours	
Chip Size:	0603	
Shelf Life:	78 Weeks	
MSL:	1	

Specifications		
Capacitance:	0.22 uF	
Capacitance Tolerance:	10%	
Voltage DC:	6.3 VDC	
Dielectric Withstanding Voltage:	15.75 V	
Temperature Range:	-55/+125C	
Temperature Coefficient:	X7R	
Dissipation Factor:	5.00% 1kHz 25C	
Aging Rate:	3% Loss/Decade Hour	
Insulation Resistance:	2.273 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

