

## Mini free-standing Beacons / EvoSIGNAL

### Mini TwinLIGHT 12VAC/DC GN



Part No.:	260.210.74
Series:	EvoSIGNAL Mini



#### MECHANICAL DATA

Height	85 mm
Diameter	62 mm
Materials	PC PC/ABS
Dome colour	Green
Housing colour	Grey
Protection category	IP66
Connection	Push-in terminal
cross-sectional area minimum	0,25mm <sup>2</sup> / 24AWG
cross-sectional area maximum	1,50mm <sup>2</sup> / 16AWG
Service life optical	50,000 h minimum
Working temperature minimum	-30°C
Working temperature maximum	+60°C
UL Type Rating	Type 12
Weight with packaging	92 g
Product weight	71 g

#### ELECTRICAL DATA

Operating voltage	12V
Operating voltage type	AC/DC
Operating voltage type	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	12 VDC
Rated operational current	86 mA
Rated inrush current	1000 mA
Protection class	Protection class 2
Pollution degree	3
Overvoltage category	I

#### OPTICAL DATA


Light source	LED
Light colour	Green
Optical signal image	TwinLight
Blink frequency (Hz)	1 Hz



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.

Mini free-standing Beacons / EvoSIGNAL  
**Mini TwinLIGHT 12VAC/DC GN**

**DRAWING**



**!** For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.