

## HMC390LP4 / 390LP4E

v02.0505



MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz

#### Typical Applications

Low noise MMIC VCO w/Buffer Amplifier for:

- Wireless Local Loop (WLL)
- VSAT & Microwave Radio
- Test Equipment & Industrial Controls
- Military

#### **Features**


Pout: +4.7 dBm

Phase Noise: -112 dBc/Hz @100 KHz
No External Resonator Needed

Single Supply: 3V @ 42 mA

QFN Leadless SMT Package, 16 mm<sup>2</sup>

#### **Functional Diagram**



## **General Description**

The HMC390LP4 & HMC390LP4E are GaAs InGaP Heterojunction Bipolar Transistor (HBT) MMIC VCOs with integrated resonators, negative resistance devices, varactor diodes, and buffer amplifiers. Covering 3.55 to 3.9 GHz, the VCO's phase noise performance is excellent over temperature, shock, vibration and process due to the oscillator's monolithic structure. Power output is 4.7 dBm typical from a single supply of 3V @ 42 mA. The voltage controlled oscillator is packaged in a low cost leadless QFN 4 x 4 mm surface mount package.

## Electrical Specifications, $T_A = +25^{\circ}$ C, Vcc = +3V


Parameter	Min.	Тур.	Max.	Units
Frequency Range	3.55 - 3.9			GHz
Power Output	1.5	4.7		dBm
SSB Phase Noise @ 100 kHz Offset, Vtune= +5V @ RF Output		-112		dBc/Hz
Tune Voltage (Vtune)	0		10	V
Supply Current (Icc) (Vcc = +3.0V)		42		mA
Tune Port Leakage Current			10	μΑ
Output Return Loss		6		dB
Harmonics 2nd 3rd		5 16		dBc dBc
Pulling (into a 2.0:1 VSWR)		3.3		MHz pp
Pushing @ Vtune= +5V		-5		MHz/V
Frequency Drift Rate		0.4		MHz/°C






# MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz


#### Frequency vs. Tuning Voltage, T= 25°C




#### Frequency vs. Tuning Voltage, Vcc= +3V




#### Sensitivity vs. Tuning Voltage, Vcc= +3V




## Output Power vs. Tuning Voltage, Vcc= +3V



#### Phase Noise vs. Tuning Voltage



#### Typical SSB Phase Noise @ Vtune= +5V





## MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz

#### Absolute Maximum Ratings

Vcc	+3.5 Vdc	
Vtune	0 to +11V	
Channel Temperature	135 °C	
Continuous Pdiss (T = 85°C) (derate 6.28 mW/°C above 85°C)	565 W	
Storage Temperature	-65 to +150 °C	
Operating Temperature	-40 to +85 °C	

#### Typical Supply Current vs. Vcc


Vcc (V)	Icc (mA)	
2.75	35	
3.0	42	
3.25	47	

Note: VCO will operate over full voltage range shown above.



**ELECTROSTATIC SENSITIVE DEVICE OBSERVE HANDLING PRECAUTIONS** 

### **Outline Drawing**



PLANE

-C-

- 2. DIMENSIONS ARE IN INCHES [MILLIMETERS].
- 3. LEAD SPACING TOLERANCE IS NON-CUMULATIVE
- 4. PAD BURR LENGTH SHALL BE 0.15mm MAXIMUM. PAD BURR HEIGHT SHALL BE 0.05mm MAXIMUM.
- 5. PACKAGE WARP SHALL NOT EXCEED 0.05mm.
- 6. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLERED TO PCB RF GROUND.
- 7. REFER TO HITTITE APPLICATION NOTE FOR SUGGESTED PCB LAND PATTERN

#### Package Information

△ .003[0.08] C

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking [3]
HMC390LP4	Low Stress Injection Molded Plastic	Sn/Pb Solder	MSL1 [1]	H390 XXXX
HMC390LP4E	RoHS-compliant Low Stress Injection Molded Plastic	100% matte Sn	MSL1 [2]	H390 XXXX

- [1] Max peak reflow temperature of 235  $^{\circ}\text{C}$
- [2] Max peak reflow temperature of 260 °C
- [3] 4-Digit lot number XXXX





## MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz

### **Pin Descriptions**


Pin Number	Function	Description	Interface Schematic
1- 14, 17 - 19, 21, 23, 24	N/C	No Connection	
15	GND	This pin must be connected to RF & DC ground.	○ GND — —
16	RFOUT	RF output (AC coupled)	—  ├──○ RFOUT
20	Vcc	Supply Voltage Vcc= 3V	Vcc O26pF
22	VTUNE	Control Voltage Input. Modulation port bandwidth dependent on drive source impedance.	7.5nH 1500 VTUNEO 1500 2.4pF C;= 7.2pF
	GND	Package bottom has an exposed metal paddle that must be RF & DC grounded.	GND =





## MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz

#### **Evaluation PCB**



#### List of Materials for Evaluation PCB 105706 [1]

Item	Description	
J1 - J2	PCB Mount SMA RF Connector	
J3 - J4	DC Pin	
C1	4.7 μF Tantalum Capacitor	
C2	10,000 pF Capacitor, 0603 Pkg.	
U1	HMC390LP4 / HMC390LP4E VCO	
PCB*	105667 Eval Board	

<sup>[1]</sup> Reference this number when ordering complete evaluation PCB

The circuit board used in the final application should use RF circuit design techniques. Signal lines should have 50 ohm impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.

<sup>[2]</sup> Circuit Board Material: Rogers 4350





Notes:

MMIC VCO w/ BUFFER AMPLIFIER, 3.55 - 3.9 GHz