

Axial Vitreous Leaded Wirewound Resistors



The G200 series, with completely welded construction, is the perfect choice for high continuous power dissipation up to 17 W. The components of this series are well suited for harsh environments and exhibit a long lifetime. With their high pulse power capability, they are the ideal choice for inrush limiters. Typical applications include but are not limited to power supplies, voltage dividers, AC filters, and snubber resistors. Particular requirements can be submitted to a Vishay Draloric application engineer specifying peak voltage, pulse shape, pulse duration, and environmental conditions for review.

FEATURES

- High power dissipation in a small design
- Excellent pulse load capability
- Completely welded construction
- Vitreous coating
- Non-flammable and enhanced humidity protection
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Inrush current limiter
- Power supplies
- Snubber resistor
- Filter resistor

| TECHNICAL SPECIFICATION | | | | | | |
|-------------------------|----------|----------------------------|----------------------------------|--|------------------------------|-----------------------------|
| TYPE | DIN SIZE | RATED DISSIPATION P_{40} | RESISTANCE RANGE ⁽¹⁾ | RESISTANCE TOLERANCE | OPERATING VOLTAGE $U_{max.}$ | TEMPERATURE COEFFICIENT |
| G202 | 0414 | 4 W | 0.10 Ω to 10.0 k Ω | $\pm 2\%$, $\pm 5\%$, $\pm 10\%$ | 200 V | +100 ppm/K to +180 ppm/K |
| G204 | 0719 | 7 W | 0.10 Ω to 39.0 k Ω | | 350 V | |
| G206 | 0933 | 13 W | 0.15 Ω to 68.0 k Ω | | 500 V | |
| G207 | 0947 | 17 W | 0.20 Ω to 120 k Ω | | 650 V | |

Notes

- The operating temperature range for these resistors is from -55 °C up to 350 °C
- ⁽¹⁾ Resistance values are to be selected for $\pm 10\%$ from the E12 series, and for $\pm 5\%$ and $\pm 2\%$ from the E24 series



| PACKAGING | | | | | | | |
|-----------|------|-------------|----------|---|-------|-------|-------------------------|
| TYPE | CODE | DESCRIPTION | QUANTITY | PACKAGING STYLE | WIDTH | PITCH | PACKAGING DIMENSIONS |
| G202 | 2C | AC G53 | 500 | Taped acc. IEC 60286-1, fan-folded in a box | 53 mm | 10 mm | 324 mm x 82 mm x 49 mm |
| | 4C | AC G73 | 500 | | 73 mm | 10 mm | 324 mm x 101 mm x 49 mm |
| | D1 | R1 R53 | 1000 | Taped acc. IEC 60286-1, on a reel | 53 mm | 10 mm | Ø 271 mm x 88 mm |
| | F1 | R1 R73 | 1000 | | 73 mm | 10 mm | Ø 271 mm x 108 mm |
| G204 | 4B | AB G73 | 250 | Taped acc. IEC 60286-1, fan-folded in a box | 73 mm | 10 mm | 324 mm x 101 mm x 49 mm |
| | 7B | AB G88 | 250 | | 88 mm | 10 mm | 324 mm x 111 mm x 75 mm |
| | FC | RC R73 | 500 | Taped acc. IEC 60286-1, on a reel | 73 mm | 10 mm | Ø 271 mm x 108 mm |
| | IC | RC R88 | 500 | | 88 mm | 10 mm | Ø 271 mm x 118 mm |
| G206 | LA | LA | 100 | Bulk | - | - | 225 mm x 140 mm x 70 mm |
| G207 | LA | LA | 100 | | - | - | 225 mm x 140 mm x 70 mm |

Notes

- Width is the nominal spacing between tapes, with the nominal tape width on both sides being 6 mm, and pitch is the nominal standard spacing between components; tolerances apply according to IEC 60286-1
- On reels, the flanges are regular octagons with a span of 250 mm, and the arbor hole is Ø 20 mm

| PART NUMBER AND PRODUCT DESCRIPTION | | | | | | | | | | | | | | | | | |
|--|----------|---|----------|--|---|----------|----------|--------------------------|---|----------|---|---|----------|---|----------|----------|----------|
| PART NUMBER: G24071933902J4B000 | | | | | | | | | | | | | | | | | |
| G | 2 | 4 | 0 | 7 | 1 | 9 | 3 | 3 | 9 | 0 | 2 | J | 4 | B | 0 | 0 | 0 |
| TYPE | | VARIANT | | | RESISTANCE | | | | TOLERANCE | | PACKAGING | | | SPECIAL | | | |
| G220414 = G202 G240719 = G204 G260933 = G206 G270947 = G207 | | 3 = +100 ppm/K to +180 ppm/K | | | 3 digit value 1 digit multiplier MULTIPLIER 7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ | | | | G = ± 2 % J = ± 5 % K = ± 10 % | | 2C 4C D1 F1 4B 7B FC IC LA | | | 000 = standard 3 digit code = customized version | | | |
| PRODUCT DESCRIPTION: G204 39K 5 % AB G73 | | | | | | | | | | | | | | | | | |
| G204 | | | | 39K | | | | 5 % | | | | AB G73 | | | | | |
| TYPE | | | | RESISTANCE | | | | TOLERANCE | | | | PACKAGING | | | | | |
| G202 G204 G206 G207 | | | | 1R2 = 1.2 Ω 12K = 12 kΩ | | | | ± 2 % ± 5 % ± 10 % | | | | AC G.. R1 R.. AB G.. RC R.. LA | | | | | |

Note

- The products can be ordered using either the PRODUCT DESCRIPTION or the PART NUMBER



DESCRIPTION

Vitreous wirewound resistors are best suited for the use in demanding environmental conditions. Their rugged design and durable coating enable these resistors to withstand extreme environmental stress. The vitreous coating is designed for high stability and a long lifetime in humid environments. The coating is resistant to all cleaning chemicals commonly used in the electronic industry.

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. The winding is done with specific materials on a specially developed fine ceramic body (Al_2O_3). The ceramic meets the highest requirements against mechanical resistance, thermal shocks, dielectric strength, and insulation resistance at high temperatures. With different diameters and turn spacings, a large ohmic value range can be offered. The glaze is fired layer by layer, several times, at a high temperature ($> 600\text{ }^\circ\text{C}$). The resistors are marked with resistance and tolerance. Product quality is verified by testing procedures, performed on all individual resistors.

Resistance is measured on the lead wires at a distance of 6 mm from the resistor body. If a greater length of lead wire is used in the application, the user may need to consider the additional wire resistance, particularly with low resistance products.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽¹⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽²⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽³⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

ASSEMBLY

The resistors are axial leaded for soldering. The terminals of the resistors are completely lead (Pb)-free. The special tin plating used, provides compatibility with lead (Pb)-free and lead-containing soldering processes.

Special lead forms may be available on request, please inquire at ww1resistors@vishay.com.

These components are high dissipation power resistors, customers are advised to use a high melting point solder.

APPLICATION INFORMATION

The power dissipation of the resistor generates a temperature rise with respect to the ambient. The permissible dissipation is derated for temperatures above $40\text{ }^\circ\text{C}$, as shown in the derating diagram, in order to avoid overheating of the resistor. The heat dissipated from the resistor may affect adjacent components, hence proper clearance will be required in order to avoid overheating.

The resistive wire is hermetically encapsulated. All materials used are non-flammable and inorganic.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

RELATED PRODUCTS

For products approved to CECC 40201-801: FDG, FDK, FDP with established reliability and failure rate level E7, see the datasheet:

- “FDG, FDK, FDP - Axial Vitreous Leaded Wirewound Resistors with CECC Approval, Available with Established Reliability”
www.vishay.com/doc?21046

In lower continuous power applications and less demanding environmental conditions the cement coated alternatives, like the AC series or the Z300 series, might be suitable, see the datasheets:

- “AC Series - Cemented Leaded Wirewound Resistors”
www.vishay.com/doc?28730
- “Z300 - Industrial Axial Cemented Leaded Wirewound Resistors”
www.vishay.com/doc?21007

For precision applications, there is the cement coated PAC series, see the datasheet:


- “PAC Series - Cemented Leaded Wirewound Precision Resistors”
www.vishay.com/doc?28731

Notes





- ⁽¹⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- ⁽²⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council, and available at www.gadsl.org
- ⁽³⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>



DERATING



TEMPERATURE RISE





The requirements stated in the Test Procedures And Requirements table are based on the required and permitted limits of CECC 40201-801. However, a number of improvements against those minimum requirements have been included. The testing temperatures LCT = -55 °C and UCT = 200 °C are established with the climatic category -55 / 200 / 56 as defined in CECC 40201-801.

| TEST PROCEDURES AND REQUIREMENTS | | | | | |
|----------------------------------|--------------------------------|------------------------------|---|-----------------------------|--|
| EN 60115-1 CLAUSE | IEC 60068-2 TEST METHOD (1) | TEST | PROCEDURE | | REQUIREMENTS PERMISSIBLE CHANGE (ΔR) STABILITY CLASS 5 OR BETTER |
| 4.5 | - | Resistance | - | | $\pm 2\%$; $\pm 5\%$; $\pm 10\%$ |
| 4.7 | - | Voltage proof | V-block-method; $U_{RMS} = U_{ins}$; 60 s | | No flashover or breakdown |
| | | | Type | U_{ins} | |
| | | | G202 | 300 V | |
| | | | G204 | 400 V | |
| | | | G206 | 500 V | |
| | | | G207 | 650 V | |
| 4.8 | - | Temperature coefficient | At (20 / -55 / 20) °C and (20 / 200 / 20) °C | | +100 ppm/K to +180 ppm/K |
| 4.13 | - | Short time overload | Overload voltage = $\sqrt{10}$ x rated voltage | | $\pm (0.5\% R + 0.05 \Omega)$ no visible damage |
| | | | Type | Duration | |
| | | | G202 | 5 s | |
| | | | G204 | 6 s | |
| | | | G206 | 10 s | |
| | | | G207 | 10 s | |
| 4.16 | 21 (Ua1) 21 (Ub) 21 (Uc) | Robustness of terminations | Tensile, bending and torsion | | $\pm (0.25\% R + 0.05 \Omega)$ no visible damage |
| 4.17 | 20 (Ta) | Solderability | Solder bath method; SnPb40; non-activated flux (235 \pm 5) °C; (2 \pm 0.2) s | | Good tinning ($\geq 95\%$ covered) no visible damage |
| | | | Solder bath method; SnAg3Cu0.5; non-activated flux; (245 \pm 5) °C; (3 \pm 0.3) s | | |
| 4.18 | 20 (Tb, Method 1A) | Resistance to soldering heat | Unmounted components; (260 \pm 3) °C; (10 \pm 1) s | | $\pm (0.25\% R + 0.05 \Omega)$ no visible damage |
| 4.19 | 14 (Na) | Rapid change of temperature | 30 min at LCT = -55 °C 30 min at UCT = 200 °C 5 cycles | | $\pm (0.25\% R + 0.05 \Omega)$ no visible damage |
| 4.21 | 27 (Ea) | Shock | Acceleration: 981 m/s ² Pulse duration: 11 ms Wave form: half sine 3 successive shocks to be applied in each perpendicular direction | | $\pm (0.25\% R + 0.05 \Omega)$ no visible damage |
| 4.22 | 6 (Fc) | Vibration | Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 6 h | | $\pm (0.25\% R + 0.05 \Omega)$ no visible damage |

| TEST PROCEDURES AND REQUIREMENTS | | | | |
|----------------------------------|---|--|--|--|
| EN 60115-1 CLAUSE | IEC 60068-2 TEST METHOD ⁽¹⁾ | TEST | PROCEDURE | REQUIREMENTS PERMISSIBLE CHANGE (ΔR) STABILITY CLASS 5 OR BETTER |
| 4.23 | | | | |
| 4.23.2 | 2 (Bb) | Climatic sequence | Dry heat 200 °C; 16 h | $\pm (0.5 \% R + 0.05 \Omega)$ |
| 4.23.3 | 30 (Db) | | Damp heat, cyclic 55 °C; 24 h; 90 % to 100 % RH; 1 cycle | |
| 4.23.4 | 1 (Ab) | | Cold -55 °C; 2 h | |
| 4.23.5 | 13 (M) | | Low air pressure; 1.0 kPa; 2 h; 15 °C to 35 °C | |
| 4.23.6 | 30 (Db) | | Damp heat, cyclic 55 °C; 24 h; 95 % to 100 % RH; 5 cycles | |
| 4.25.2 | - | Endurance at room temperature | $P_{\text{test}} = 1.16 \times P_{40}$ $U_{\text{test}} = \sqrt{1.16 \times P_{40} \times R} \leq U_{\text{max.}}$ $t_{\text{on}} = 1.5 \text{ h}; t_{\text{off}} = 0.5 \text{ h}$ 25 °C; 1000 h 25 °C; 8000 h | $\pm (3.0 \% R + 0.05 \Omega)$ $\pm (6.0 \% R + 0.05 \Omega)$ |
| 4.25.3 | - | Endurance at upper category temperature | $P_{\text{test}} = P_{\text{cat}} = 0.54 \times P_{40}$ $U_{\text{test}} = \sqrt{0.54 \times P_{40} \times R} \leq U_{\text{max.}}$ 200 °C; 1000 h | $\pm (3.0 \% R + 0.05 \Omega)$ |
| 4.24 | 78 (Cab) | Damp heat, steady state | (40 ± 2) °C; 56 days; (93 ± 3) % RH | $\pm (0.5 \% R + 0.05 \Omega)$ |

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents

| DIMENSION AND MASS | | | | | | | |
|--------------------|---------------------------|---------------------------------|-----------|------------|-------------|---------------------------------|-------------|
| | | | | | | | |
| TYPE | $L_{\text{max.}}$ (mm) | $D_{\text{max.}}^{(1)}$ (mm) | d (mm) | B (mm) | A (mm) | $S_{\text{min.}}^{(2)}$ (mm) | MASS (g) |
| G202 | 13.0 | 5.7 | 0.8 | 53.0 ± 1.0 | 63.0 ± 0.3 | 17.5 | 1.0 |
| | | | | 73.0 ± 1.0 | 83.0 ± 0.3 | | |
| G204 | 20.5 | 8.5 | 0.8 | 73.0 ± 1.0 | 63.0 ± 0.3 | 25.0 | 2.2 |
| | | | | 88.0 ± 1.0 | 98.0 ± 0.3 | | |
| G206 | 32.3 | 9.8 | 0.8 | - | 107.0 ± 2.0 | 40.0 | 6.5 |
| G207 | 50.0 | 10.5 | 0.8 | - | 120.0 ± 2.0 | 55.0 | 10.0 |

Notes

⁽¹⁾ The body diameter is 1 mm larger for resistance values $\leq 10 \Omega$

⁽²⁾ Minimum pitch



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.