



**SLIDE POTENTIOMETER**

**Q-4515**

**F-101G**

5mm, Mini Type, Dual Unit



**SPECIFICATIONS**

**Electrical Characteristics**

- Total Resistance ..... 500Ω~ 1MΩ
- Total Resistance Tolerance ..... ±20%
- Resistance Taper ..... A,B,C,D, See P109
- Sliding Noise..... Les than 100 mV
- Insulation Resistance ..... 5 mm~15mm: More than 50 MΩ at DC 100V  
20 mm: More than 50 MΩ at DC 250V
- Withstand Voltage..... 5mm~15mm: 1 minute at AC 100V  
20 mm: 1 minute at AC 250V
- Residual Resistance ..... Term: 1-2: Less than 10Ω  
Term: 2-3: Less than 10Ω
- Gang Error (Dual Unit)..... -40 dB~0dB±3dB
- Rated Voltage
- Linear Taper B..... 4mm,5mm: AC 50V,  
10mm,15mm: AC 100V, 20mm: AC 200V
- Other Tapers ..... 5mm: AC 25V, 10mm, 15mm: AC 50V,  
20mm: AC 150V
- Rated Power (Single Unit/Dual Unit)
- Linear Taper B ..... 4mm,5mm: 0.01W/0.005W  
10mm: 0.03W/0.015W, 15mm: 0.05W/0.025W, 20mm: 0.1W/-  
Other Tapers ..... 5mm: 0.025W/0.012W, 10mm: 0.015W/0.01W  
15mm: 0.025W/0.01W, 20mm: 0.05W/-

**Mechanical Characteristics**

- Operating Force ..... 20 gf.cm~200 gf.cm
- Click Slip-Out Force (only Center Click)  
Operating Force ..... 30 gf.cm~300 gf.cm
  - Stopper Strength ..... 2.50 Kg/cm Min  
(from the base level to a point of 2 mm)
- Level Wobble ..... 2(2xL)/25mm Max. (L:Level length both sides)
- Level Push-Pull Strength ..... 1.0Kgf Min.at 10 sec.
- Rotational Life..... 5,000 Cycles

**Durability**