


KEMET, FLLD4-TH, EMI/RFI Filters, Noise Suppression, 530 VAC, 64 A, 160x125x125mm



General Information	
Series:	FLLD4-TH
Style:	Chassis Mount
Description:	EMI Filter, Classis Mount, Compact
Features:	Three Phase + Neutral, High Performance
Phase:	Three-phase
RoHS:	Yes
Qualifications:	IEC/EN 60939
Terminal Type:	Threaded Studs M10

Dimensions	
L	160mm NOM
W	125mm NOM
H	125mm NOM
L1	100mm NOM
W1	137.5mm NOM
W2	153mm NOM
J	35mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M10

Specifications	
Voltage AC:	530 VAC, 305 VAC
Voltage DC:	2250 VDC
Rated Frequency:	50-60 Hz
Rated Current:	64 A (50°C)
Rated Temperature:	50°C
Temperature Range:	-25/+100°C
Climate Category:	25/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	18 W (25°C 50 Hz)
Leakage Current:	11 mA

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Component Weight:	2.3 kg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.