

COAXIAL ADAPTER, BNC, 75 Ohm, Bulkhead, jack / jack (female / female)

34_BNC-75-0-2/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	75 Ω
Interface frequency	1 GHz

COAXIAL ADAPTER, BNC, 75 Ohm, Bulkhead, jack / jack (female / female)

34_BNC-75-0-2/133_N

Mechanical data

Weight	0.0174 kg
Mating cycles	500

Environmental data

Operation temperature	-65 °C ... 165°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22541042	34_BNC-75-0-2/133_NE	Single

Additional Information

Remarks	For insulated mounting
---------	------------------------

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2122 / Date of publication: 26.11.2023 / uncontrolled copy