


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL (COLOR)	NAIL PART NO.	"A" NAIL LENGTH FROM FLANGE (REF)	"B" NAIL DIA. (REF)	"C" HOL DIA. (REF)	"D" OVERALL HEIGHT (REF)
QB-FN1-Q	ABS (WHITE)	HBN1-T	1.0 [25.4]	.074 [1.880]	.079 [2.007]	2.17 [55.12]
QB-FN2-Q	ABS (BLACK)	HBN2-T	2.0 [50.8]	.094 [2.388]	.094 [2.388]	3.17 [80.52]
QB-FN3-Q	ABS (GRAY)	HBN3-T	3.0 [76.2]	.121 [3.073]	.128 [3.251]	4.17 [105.92]

NOTES:

1. DIMENSIONS IN BRACKETS [ ] ARE METRIC [ mm ]
2. PRODUCT DESIGNED TO BE INSERTED INTO PANDUIT PART: QB-MOUNT
3. PRODUCT DESIGNED TO SUPPORT A MAXIMUM STATIC LOAD OF 5 LBS WITH COMPATIBLE PARTS.
4. PRODUCT IS RATED FOR ENVIRONMENTAL CONDITIONS OF 40-100°F IN ALL HUMIDITY RANGES.
5. PRODUCT DESIGNED TO SUPPORT ANY COMBINATION OR ARRANGEMENT OF 1 TO 5 NAILS.
6. NAILS SOLD SEPARATELY.

TITLE  
**QUICK-BUILD FIVE NAIL BASE FOR USE WITH HBN1-T, HBN2-T, HBN3-T; 25 PER PACKAGE. (QB-FN1-Q, QB-FN2-Q, QB-FN3-Q)**

CUSTOMER DRAWING

ITEM REVISION NAME <b>14L203AP/01</b>	<b>PANDUIT</b>
DATASET FILE NAME <b>14L203AP_DC/00</b>	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]	
.x ± .1 [ 2.54 ]	.xxx ± .005 [ .127 ]
.xx ± .01 [ .25 ]	ANGLES ± 5 °
DRAWING NUMBER: <b>14L203AP-DC</b>	
DRAWN BY <b>ANF</b>	DATE <b>06-15-15</b>
CHK <b>DJW</b>	SCALE <b>1:2</b>
SHT 1 OF 1	
SIZE <b>A</b>	

00	06-15-15	ANF	DJW	MSAD	DRAWING RELEASE	GAECN03013
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[QB-FN1-Q](#) [QB-FN3-Q](#) [QB-FN2-Q](#)