




ELECTRICAL CHARACTERISTICS

VOLTAGE: 250 VAC (RMS) Max.
 CURRENT RATING: 2 AMPS
 CONTACT RESISTANCE: 20 mΩ Max.
 INSULATION RESISTANCE: 5000 MΩ Min.
 DIELECTRIC WITHSTANDING: 500 VAC
 OPERATING TEMPERATURE: -40°C TO +105°C
 PROCESSING TEMPERATURE: 260°C FOR 10 SECONDS



MATERIAL CHARACTERISTICS



HOUSING: PA9T, UL94V-0, BLACK
 CONTACTS: COPPER ALLOY
 PLATING: GOLD FLASH ENTIRE CONTACT



2763YY02RP2

SERIES _____
 2763 = SINGLE ROW
 POSITIONS _____
 SINGLE-INCREMENTS OF 1
 (01 TO 36)
 TYPE _____
 02 = RIGHT ANGLE
 PLATING _____
 P2 = GOLD FLASH

Recommended P.C. Board
 Hole Layout



RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS
 DATE:
 01/27/2006

NorComp

SCALE: NTS	SHEET 1	OF 1	REV 4
DWG NO.		2763YY02RP2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[27630102RP2](#) [27630202RP2](#) [27630302RP2](#) [27630402RP2](#) [27630502RP2](#) [27630602RP2](#) [27630702RP2](#)
[27630802RP2](#) [27631002RP2](#) [27631502RP2](#) [27631602RP2](#) [27632002RP2](#) [27632402RP2](#) [27632502RP2](#)
[27633602RP2](#)