

Description

The TL431 and TL432 are three terminal adjustable shunt regulators offering excellent temperature stability and output current handling capability up to 100mA. The output voltage may be set to any chosen voltage between 2.5 and 36 volts by selection of two external divider resistors.

The devices can be used as a replacement for zener diodes in many applications requiring an improvement in zener performance. Diodes' TL431 has the same electrical specifications as the industry standard '431 and is available in 2 grades with initial tolerances of 1% and 0.5% for the A and B grades respectively.


Features


- Temperature range -40 to +125°C
- Reference Voltage Tolerance at 25°C
 - TL431A: 2.495V ± 1.0%
 - TL431B: 2.495V ± 0.5%
- Low Output Noise
- 0.2Ω Typical Output Impedance
- Sink Current Capability: 1mA to 100mA
- Adjustable Output Voltage: V_{REF} to 36V
- All devices are:
 - Totally Lead-Free & Fully RoHS compliant (Notes 1 & 2)
 - Halogen and Antimony Free. "Green" Device (Note 3)


Applications

- Opto-Coupler Linearisers
- · Shunt Regulators
- Improved Zener
- Variable Reference


Pin Assignments







TL432



Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen and Antimony free, "Green" and Lead-Free.
- 3. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Absolute Maximum Ratings (Note 4)

Symbol	Paramet	Rating	Unit	
V_{KA}	Cathode Voltage		40	٧
I _{KA}	Continuous Cathode Current	150	mA	
I _{REF}	Reference Input Current	-0.050 to +10	mA	
T_J	Operating Junction Temperature	+150	°C	
T _{ST}	Storage Temperature	-55 to +150	٦°	
		SOT23	330	
P_{D}	Power Dissipation (Notes 5, 6)	SOT25	500	mW
		SO-8*	700	

Notes:

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{KA}	Cathode Voltage	V_{REF}	36	V
I _{KA}	Cathode Current	1	100	mA
T _A	Operating Ambient Temperature	-40	+125	°C

^{4.} Operation above the absolute maximum rating may cause device failure. Operation at the absolute maximum ratings, for extended periods, may reduce device reliability. Unless otherwise stated voltages specified are relative to the ANODE pin.

^{5.} TJ, MAX =150°C

^{6.} Ratings apply to ambient temperature at 25°C.



Electrical Characteristics (T_A = +25°C, unless_otherwise noted)

Symbol	Parameter	Test C	onditions	Min	Тур.	Max	Unit
V	Poforonos voltago	$V_{KA} = V_{REF}$	TL431A	2.470	2.495	2.520	V
V _{REF}	Reference voltage	$I_{KA} = 10mA$	TL431B	2.482	2.495	2.507	V
			$T_A = 0 \text{ to } 70^{\circ}\text{C}$		6	16	mV
V_{DEV}	Deviation of reference voltage over full temperature range (Note 5)	$V_{KA} = V_{REF},$ $I_{KA} = 10mA$	$T_A = -40 \text{ to } +85^{\circ}\text{C}$		14	34	
	Tuil temperature range (Note 3)	IKA = TOTTIA	$T_A = -40 \text{ to } +125^{\circ}\text{C}$		14	34	
ΔV_{REF}	Ratio of the change in reference		$V_{KA} = 10V \text{ to } V_{REF}$		-1.4	-2.7	
ΔV_{KA}	voltage to the change in cathode voltage	$I_{KA} = 10mA$	V _{KA} = 36V to 10V		-1	-2	mV/V
I _{REF}	Reference input current	I _{KA} = 10mA, R1 = 10KΩ, R2 = ∞			1	4	μΑ
	I _{REF} deviation over full temperature range (Note 7)	$R1 = 10K\Omega$, T_A	$T_A = 0 \text{ to } 70^{\circ}\text{C}$		0.8	1.2	μА
ΔI_{REF}			$T_A = -40 \text{ to } +85^{\circ}\text{C}$		0.8	2.5	
			$T_A = -40 \text{ to } +125^{\circ}\text{C}$		0.8	2.5	
I _{KA(MIN)}	Minimum cathode current for regulation	V _{KA} = V _{REF}			0.4	0.7	mA
I _{KA(OFF)}	Off-state current	$V_{KA} = 36V, V_{REF} = 0V$			0.05	0.5	μΑ
Z _{KA}	Dynamic output impedance (Note 8)	V _{KA} = V _{REF,} f = 0Hz			0.2	0.5	Ω
	Thermal Resistance Junction to Ambient	SOT23			380		
θ_{JA}		SOT25			250		°C/W
	Allibient	SO-8*			70		

Notes: 7. Deviation of VDEV, and ΔIREF are defined as the maximum variation of the values over the full temperature range.


The average temperature coefficient of the reference input voltage αV_{REF} is defined as:

$$\left| \alpha V_{REF} \right| = \frac{\left(\frac{V_{DEV}}{V_{REF} @ 25^{\circ}C} \right) X \cdot 10^{6}}{T2 - T1} \text{ ppm/°C}$$


Where:

T2 - T1 = full temperature change.

 $\alpha V_{\text{REF}} \, \text{can}$ be positive or negative depending on whether the slope is positive or negative.



$$\left| Z_{KA} \right| = \frac{\Delta V_{KA}}{\Delta I_{KA}}$$



When the device is programmed with two external resistors R1 and R2, the dynamic output impedance of the overall circuit, is defined as:

$$|Z'| = \frac{\Delta V}{\Delta I} \approx |Z_{KA}| \left(1 + \frac{R1}{R2}\right)$$

Test Circuits




Figure 1. Test circuit for $V_{KA} = V_{REF}$




Figure 2. Test circuit for $V_{KA} > V_{REF}$








Figure 3. Test circuit for I_{OFF}

















Ratio of Delta Reference Voltage to Delta Cathode Voltage vs. Free Air Temperature



Typical Performance Characteristics (cont.)





Figure 4. Test circuit for noise input voltage

 $A_V = 2$


 $A_V = 10k$




Typical Performance Characteristics (cont.)




Small-Signal Voltage Amplification vs. Frequency






Test circuit for voltage amplification




Test circuit for reference impedance




Typical Performance Characteristics (cont.)




01 0.001 0.01 0.1 $\rm C_L$ -Load Capacitance - $\rm uF$ Stability Boundary Conditions



Test Circuit for Pulse Response



Test Circuit for Curve A



Test Circuit for Curves B, C, D

The device is stable under all conditions with a load capacitance not exceeding 50pF. The device is stable under all conditions with a load capacitance between 5nF and 20nF. The device is stable under all conditions with a load capacitance exceeding 300nF. With a cathode current not exceeding 5mA, the device is stable with any load capacitance.


0.00001 0.0001 0.001

 V_{OUT}




ADJUSTABLE PRECISION SHUNT REGULATOR


Applications Information



Shunt Regulator




Higher Current Shunt Regulator




Rb - Optional to provide minimum cathode current


Output Control of a Three Terminal Fixed Regulator



Series Regulator




Single Supply Comparator with Temperature **Compensated Threshold**



Over Voltage / Under **Voltage Protection Circuit**



Ordering Information



		Package	Packaging	7" Tape and Reel		Ammo Box	
	Device	Code	(Note 9)	Quantity	Part Number Suffix	Quantity	Part Number Suffix
Pb ,	TL431A(B)SA-7	SA	SOT23	3000/Tape & Reel	-7	NA	NA
Pb ,	TL431A(B)W5-7	W5	SOT25	3000/Tape & Reel	-7	NA	NA
Pb ,	TL431A(B)S-13*	S	SO-8*	2500/Tape & Reel	-13	NA	NA
Pb,	TL432A(B)SA-7	SA	SOT23	3000/Tape & Reel	-7	NA	NA

^{*} Suffix "B" denotes TL431B device.

Notes: 9. Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.



Marking Information

(1) SOT23

(Top View)

3 XX YWX

2

1

XX: Identification code

Y: Year 0~9

W: Week: A~Z: 1~26 week;

a~z:27~52 week; z represents


52 and 53 week

X: A~Z: Green

Device	Package	Identification Code
TL431ASA	SOT23	AA
TL431BSA	SOT23	AB
TL432ASA	SOT23	ВА
TL432BSA	SOT23	BB

(2) SOT25

(Top View)



XX: Identification code

₹ : Year 0~9


W: Week: A~Z: 1~26 week; a~z: 27~52 week; z represents

52 and 53 week

X: A~Z: Green

Device	Package	Identification Code
TL431AW5	SOT25	AA
TL431BW5	SOT25	AB


(3) SO-8*






Package Outline Dimensions (All Dimensions in mm)

(1) Package type: SOT25



	SOT25					
Dim	Min	Max	Тур			
Α	0.35	0.50	0.38			
В	1.50	1.70	1.60			
С	2.70	3.00	2.80			
D	_		0.95			
Н	2.90	3.10	3.00			
J	0.013	0.10	0.05			
K	1.00	1.30	1.10			
L	0.35	0.55	0.40			
М	0.10	0.20	0.15			
N	0.70	0.80	0.75			
α	0°	8°				
All Dimensions in mm						

(2) Package Types: SOT23




SOT23					
Dim	Min	Max	Тур		
Α	0.37	0.51	0.40		
В	1.20	1.40	1.30		
С	2.30	2.50	2.40		
D	0.89	1.03	0.915		
F	0.45	0.60	0.535		
G	1.78	2.05	1.83		
Η	2.80	3.00	2.90		
7	0.013	0.10	0.05		
K	0.903	1.10	1.00		
K1	-	-	0.400		
L	0.45	0.61	0.55		
М	0.085	0.18	0.11		
α	0°	8°	-		
All Dimensions in mm					



Package Outline Dimensions (All Dimensions in mm)

(3) Package Types: SO-8*



SO-8*				
Dim	Min	Max		
Α	-	1.75		
A1	0.10	0.20		
A2	1.30	1.50		
А3	0.15	0.25		
b	0.3	0.5		
D	4.85	4.95		
Е	5.90	6.10		
E1	3.85	3.95		
е	1.27	Тур		
h	-	0.35		
L	0.62	0.82		
θ	0°	8°		
All Dimensions in mm				



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

TL431ASA-7 TL431AW5-7 TL431BSA-7 TL431BW5-7 TL432ASA-7 TL432BSA-7