

917764-1 ✓ ACTIVE

AMP Signal Double Lock


TE Internal #: 917764-1

Connector Contact, Tab, Wire-to-Wire, 22 – 20 AWG Wire Size, .3 – .53 mm² Wire Size, Tin, Reel, Wire & Cable, 3 A, Signal, AMP Signal Double Lock

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts > Signal Double Lock Tab



Contact Type: **Tab**

Connector System: **Wire-to-Wire**

Wire Size: **.3 – .53 mm²**

Contact Mating Area Plating Material: **Tin**

[All Signal Double Lock Tab \(2\)](#)

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Contact Retention Within Housing	With
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material Thickness	.2 μm[7.87 μin]
Contact Base Material	Phosphor Bronze
Contact Type	Tab



Contact Mating Area Plating Material	Tin
--------------------------------------	-----

Contact Current Rating (Max)	3 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
---------------------------------------	---------------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Dimensions

Compatible Insulation Diameter Range	1.4 – 1.8 mm [.055 – .071 in]
--------------------------------------	-------------------------------

Wire Size	.3 – .53 mm ²
-----------	--------------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	8000
--------------------	------

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
----------------------------------------	---------------------------------------------------------------------------------------------------------------------------------

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	-------------------------------------------------------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	----------------------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-SI261-C1701A
Glow Wire Signal Double Lock Cap



TE Part # CAT-SI261-C1701
STD Temp Signal Double Lock Cap




TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 2151081-1
OCEAN_2.0_APPLICATOR-S-050F070F



TE Part # 2151081-2
OCEAN_2.0_APPLICATOR-S-050F070F



TE Part # 234605-1
EXT-TOOL



TE Part # 7-2151081-1
OCEAN_2.0_APPLICATOR-S-050F070F



TE Part # 7-2151081-2
OCEAN_2.0_APPLICATOR-S-050F070F




TE Part # 7-2151081-7
OCEAN_2.0_SPARE_PART_KIT-050F070F




TE Part # 2-2151081-1
OCEAN_2.0_APPLICATOR-S-050F070F


Also in the Series | **AMP Signal Double Lock**




Connector Caps & Covers(1)



Connector Contacts(8)




Connector Seals & Cavity Plugs(10)




Insertion & Extraction Tools(1)




PCB Headers & Receptacles(144)



PCB Latches, Locks & Retainers(17)




Rectangular Connector Housings(23)




Rectangular Connector Locking(2)




Rectangular Power Connectors(3)



Standard Rectangular Connectors(1)



Wire-to-Board Connector Assemblies & Housings(76)



Wire-to-Board Connector Contacts(6)

Customers Also Bought



TE Part #1376392-1
5MM POWER KEY 4P PLUG 2ROW NUT



TE Part #917895-1
2.5 S.D.L STD V 3P HDR ON/TAPE



TE Part #316087-1
2.5 SIGNAL D/LOCK CAP HSG 3P



TE Part #1-1473059-3
EP CONN POST HDR 3/4P




TE Part #1-1565033-2
EP CONN HDR ASSY 2/4P SPECIAL



TE Part #1-1747066-6
GRACE INERTIA CONN 2.5 PLUG HSG 6P RED



TE Part #1-1565035-4
EP CONN HDR ASSY 4/6P SPECIAL



TE Part #1871571-1
GIC 3.3 HDR ASSY 12POS KINK



Documents

Product Drawings

2.5 SIGNAL D/LOCK TAB CONT. L

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_917764-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_917764-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_917764-1_E.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_917764-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_917764-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_917764-1_A.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

[1773458-3_2.5MM_SIGNAL_DOUBLE_LOCK_CONNECTORS](#)

English



Product Specifications

Product Specification

English

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English