

1027-003-1200 ✓ ACTIVE

enetSEAL+ | DEUTSCH DT

TE Internal #: 1027-003-1200

DEUTSCH DT, Other Automotive Connector Accessories,
Mounting Clip, Wire-to-Wire, Stainless Steel, Wire & Cable

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories > DEUTSCH DT MOUNTING CLIPS



Automotive Connector Accessory Type: **Mounting Clip**

Connector System: **Wire-to-Wire**

Primary Product Material: **Stainless Steel**

Connector & Contact Terminates To: **Wire & Cable**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All DEUTSCH DT MOUNTING CLIPS \(10\)](#)

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-------------------------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUN 2020 (209)
Candidate List Declared Against: JUN 2020 (209)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Model / Part # CAT-D485-CH8172
DEUTSCH DTM HOUSINGS



TE Model / Part # CAT-D487-CH8172
DEUTSCH DT HOUSINGS



TE Model / Part # CAT-D486-CH8172
DEUTSCH DTP HOUSINGS



TE Model / Part # CAT-D48-PCH8172
DEUTSCH DTHD HOUSINGS



TE Model / Part # DTCE04-1-4P-E003
DTCE RECP ASM



TE Model / Part # 2350891-1
20POS, HYBRID, PIN HSG ASSY, SLD, COD A



TE Model / Part # 2350890-1
20POS, HYBRID, SOC HSG ASSY, SLD, COD A



TE Model / Part # 2350890-2
20POS, HYBRID, SOC HSG ASSY, SLD, COD B




TE Model / Part # 2350890-3
20POS, HYBRID, SOC HSG ASSY, SLD, COD C



TE Model / Part # 2350891-4
20POS, HYBRID, PIN HSG ASSY, SLD, COD D



TE Model / Part # 2350890-4
20POS, HYBRID, SOC HSG ASSY, SLD, COD D



TE Model / Part # 2350891-3
20POS, HYBRID, PIN HSG, SLD, COD C



TE Model / Part # 2350891-2
20POS, HYBRID, PIN HSG ASSY, SLD, COD B



TE Model / Part # 1-2350890-2
20POS, HYBRID, SOC HSG ASSY, SLD, COD B



TE Model / Part # 1-2350890-3
20POS, HYBRID, SOC HSG ASSY, SLD, COD C



TE Model / Part # 1-2350890-4
20POS, HYBRID, SOC HSG ASSY, SLD, COD D



TE Model / Part # 2318967-1
24POS, AMP MCP 2.8, REC HSG ASSY, SLD



TE Model / Part # 2319023-1
8POS, AMP MCP 2.8, REC HSG ASSY, SLD




TE Model / Part # 2319023-2
8POS, AMP MCP 2.8, REC HSG ASSY, SLD




TE Model / Part # 2319826-2
2POS, MCON 8.0, REC HSG ASSY, SLD


Also in the Series | DEUTSCH DT




Automotive Connector Caps & Covers (71)




Automotive Connector Locks & Position Assurance (62)




Automotive Headers (83)




Automotive Housings (563)



Automotive Seals & Cavity Plugs (4)



Insertion & Extraction Tools (7)



Other Automotive Connector Accessories (13)

Customers Also Bought



Documents

Product Drawings

CLIP, SS, 11MM HOLE, ST

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1027-003-1200_99_c-1027-003-1200-99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1027-003-1200_99_c-1027-003-1200-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1027-003-1200_99_c-1027-003-1200-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)



English