


Thick Film Surface Mount Chip Resistors, Wraparound, Extremely Low Value (0.01 Ω to 0.976 Ω)




DESIGN SUPPORT TOOLS


click logo to get started



FEATURES

- Extremely low resistance values $(0.01 \Omega \text{ to } 0.976 \Omega)$
- Sulfur resistant (per ASTM B809-95 humid vapor





- Metal glaze on high quality ceramic
- Protective overglaze
- Lead (Pb)-free solder contacts on Ni barrier laver
- please see www.vishay.com/doc?99912



COMPLIANT
HALOGEN
FREE


	_044 (. 5	,	···	5 011 1 ti Daiii	O	ay 0.
•	AEC-Q20	00 qualified				
•	Material	categorization:	for	definitions	of	compliance
		the second secon	,			

GLOBAL MODEL	CASE SIZE	POWER RATING P _{70°C} W	TEMPERATURE COEFFICIENT ± ppm/°C	RESISTANCE RANGE Ω	TOLERANCE ± %	E-SERIES (2)
			400	0.033 to 0.05	5.0	24
RCWE0402	0402	0.125	200	0.051 to 0.196	1.0, 5.0	24; 96
			100	0.2 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	24, 90
			700	0.010 to 0.018	5.0	24
DCME0603	0603	0.2	400	0.02 to 0.0324	1.0, 5.0	
RCWE0603	0003	0.2	200	0.033 to 0.105	1.0, 5.0	24; 96
			100	0.11 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
			400	0.010 to 0.018	5.0	24
DOWEDOOF	0805	0.25	300	0.02 to 0.0324	1.0, 5.0	
RCWE0805	0805	0.25	200	0.033 to 0.05	1.0, 5.0	24; 96
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE0612	0612		300	0.010 to 0.016	2.0, 5.0	24
		1.0	200	0.018 to 0.2	2.0, 5.0	24
		-	100	0.205 to 0.976	1.0, 5.0	24; 96
D011/2/22	1206		600	0.010 to 0.018	5.0	24
		0.5	300	0.02 to 0.0324	1.0, 5.0	24; 96
RCWE1206		0.5	200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
			500	0.010 to 0.018	5.0	24
DCW/E1010	1210	1.0	300	0.02 to 0.0324	1.0, 5.0	
RCWE1210	1210	1.0	200	0.033 to 0.05	1.0, 5.0	24; 96
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	1
DCW/E1000	1000	0.0	200	0.010 to 0.016	2.0, 5.0	24
RCWE1020	1020	2.0	100	0.0162 to 0.976	1.0, 5.0	24; 96
			600	0.010 to 0.018	5.0	24
DOM/E0040	0010	1.0	300	0.02 to 0.0324	1.0, 5.0	
RCWE2010	2010	1.0	200	0.033 to 0.05	1.0, 5.0	24; 96
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	7
			600	0.010 to 0.018	5.0	24
	0540		300	0.02 to 0.0324	1.0, 5.0	24; 96
RCWE2512	2512	2.0	200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	1

Notes

- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material
- Part marking: Reference "Surface Mount Resistor Marking" (www.vishav.com/doc?20020) Tight tolerance of 0.5 % is available for resistance values above 0.300 Ω (0402 size) and above 0.200 Ω (0603 to 2512 sizes)
- Use E24 decades only for 5.0 % tolerance. E24 or E96 decades are available for 0.5 % and 1.0 % tolerance. Refer to standard decade table (www.vishay.com/doc?31001)





TECHNICAL SPECIFICATIONS										
PARAMETER	UNIT	0402	0603	0805	0612	1206	1210	1020	2010	2512
Operating temperature range	°C	-55 to +155								
Maximum operating voltage	V					$(P \times R)^{1/2}$				
Insulation voltage Uins (1 min)	V	> 75	> 100	> 200	> 100	> 300	> 300	> 300	> 300	> 300
Insulation resistance	Ω	> 10 ⁹								
Weight/1000 pieces (typical)	g	0.7	3	5.5	11.5	10.5	17.5	27.5	26	40.5

RCWE0402 to RCWE2512 RCWE0612, RCWE1020

- 3D models available: www.vishay.com/doc?31106
- Surface mount solder profile recommendations: www.vishay.com/doc?31052

	DIMENSIONS in millimeters							DIMENSIONS	in millimeters		
SIZE	$\begin{array}{c} \textbf{RESISTANCE} \\ \textbf{RANGE} \\ \Omega \end{array}$	L	w	н	T1	T2	а	b	I		
0402	0.033 to 0.976	1.05 ± 0.05	0.55 ± 0.05	0.35 ± 0.1	0.3 ± 0.15	0.25 ± 0.1	0.7	0.7	0.3		
0603	0.01 to 0.03	1.6 ± 0.1	0.85 ± 0.1	0.5 ± 0.1	0.5 ± 0.2	0.3 ± 0.2	0.9	1.0	0.4		
0003	0.033 to 0.976	1.0 ± 0.1	0.65 ± 0.1	0.5 ± 0.1	0.3 ± 0.2	0.3 ± 0.2	0.7	1.0	0.8		
0805	0.01 to 0.03	2.0 ± 0.15	1.3 ± 0.1	0.55 ± 0.1	0.6 ± 0.2	0.35 ± 0.2	1.0	1.4	0.6		
0803	0.033 to 0.976	2.0 ± 0.15	1.3 ± 0.1	0.55 ± 0.1	0.4 ± 0.2		0.8	1.4	1.0		
0612	0.01 to 0.976	1.6 ± 0.2	3.2 ± 0.2	0.6 ± 0.1	0.4 ± 0.15	0.25 ± 0.15	0.9	3.5	0.8		
	0.01 to 0.03	3.1 ± 0.15	1.6 ± 0.15	0.6 ± 0.1	0.9 ± 0.2	0.45 ± 0.2	1.3	1.8	1.0		
1206	0.033 to 0.05				0.8 ± 0.2		1.2	1.8	1.2		
	0.051 to 0.976				0.45 ± 0.2		1.0	1.8	1.6		
1210	0.01 to 0.03	21.02	2.5 ± 0.2	05.00	0.0 0.4	06.01	0.8 ± 0.2	0.4 ± 0.2	1.3	2.6	1.1
1210	0.033 to 0.976	3.1 ± 0.2		0.6 ± 0.1	0.4 ± 0.2	0.4 ± 0.2	0.9	2.6	2.0		
1020	0.01 to 0.976	2.5 ± 0.2	5.0 ± 0.2	0.6 ± 0.1	0.55 ± 0.15	0.30 ± 0.15	1.2	5.5	1.4		
	0.01 to 0.03		2.5 ± 0.15	0.6 ± 0.1	1.6 ± 0.3	0.6 ± 0.2	2.3	3.0	1.4		
2010	0.033 to 0.05	5.0 ± 0.2			0.7 ± 0.3		1.4	3.0	3.2		
	0.051 to 0.976				0.7 ± 0.3		1.4	3.0	3.2		




www.vishay.com

RCWE0402 to RCWE2512 RCWE0612, RCWE1020


- 3D models available: www.vishay.com/doc?31106
- Surface mount solder profile recommendations: www.vishay.com/doc?31052

	DIMENSIONS in millimeters						SOLDER PAD DIMENSIONS in millimeters		
SIZE	$\begin{array}{c} \textbf{RESISTANCE} \\ \textbf{RANGE} \\ \Omega \end{array}$	L	w	H	T1	T2	а	b	I
	0.01 to 0.03				2.0 ± 0.3		2.8	3.6	1.4
2512	0.033 to 0.05	6.3 ± 0.2	3.15 ± 0.15	0.6 ± 0.1	0.8 ± 0.3	0.6 ± 0.2	1.6	3.6	3.8
	0.051 to 0.976				0.8 ± 0.3		1.6	3.6	3.8

DERATING




SINGLE PULSE





SINGLE PULSE



PERFORMANCE							
TEST	CONDITIONS OF TEST	TEST LIMITS					
Thermal shock	MIL-STD-202, method 107, -55 °C to +125 °C, 300 cycles at each extreme	\pm 1.0 % + 0.0005 Ω					
Short time overload	2x rated power; size and duration - 0402: 0.5 s, 0603 and 0805: 1 s, 1206 and larger: 2 s	\pm 0.5 % + 0.0005 Ω					
High temperature exposure	MIL-STD-202, method 108, 1000 h at T = 125 °C, 0 % power	\pm 2.0 % + 0.0005 Ω					
Temperature cycling	JESD 22, method JA-104, 1000 cycles (-55 °C to +125 °C)	\pm 2.0 % + 0.0005 Ω					
Biased humidity	MIL-STD-202, method 103, 1000 h 85 °C/85 % RH, 10 % x (P x R) ^{1/2}	\pm 2.0 % + 0.0005 Ω					
Mechanical shock	MIL-STD-202, method 213, condition C, 10 g's, 6 ms (half sine), 3 directions	\pm 1.0 % + 0.0005 Ω					
Vibration	MIL-STD-202, method 204, 5 g 's, 20 min, 12 cycles, 3 directions, 10 Hz to 2000 Hz	\pm 1.0 % + 0.0005 Ω					
Operational life	MIL-STD-202, method 108, 1000 h at T = 125 °C at rated power	\pm 2.0 % + 0.0005 Ω					
Resistance to solder heat	MIL-STD-202, method 210, +260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 1.0 % + 0.0005 Ω					
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	\pm 2.0 % + 0.0005 Ω					

PACKAGING										
MODEL		REEL								
MODEL	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	CODE					
RCWE0402	8 mm/punched paper	180 mm/7"	2 mm	10 000	EA					
RCWE0603	8 mm/punched paper	180 mm/7"	4 mm	5000	EA					
RCWE0805	8 mm/punched paper	180 mm/7"	4 mm	5000	EA					
RCWE0612	8 mm/punched paper	180 mm/7"	4 mm	5000	EA					
RCWE1206	8 mm/punched paper	180 mm/7"	4 mm	5000	EA					
RCWE1210	8 mm/punched paper	180 mm/7"	4 mm	5000	EA					
RCWE1020	12 mm/embossed plastic	180 mm/7"	4 mm	4000	EA					
RCWE2010	12 mm/embossed plastic	180 mm/7"	4 mm	4000	EA					
RCWE2512	12 mm/embossed plastic	180 mm/7"	8 mm	2000	EA					

Notes

- Embossed carrier tape per EIA-481-1A
- Additional packaging details at: www.vishay.com/doc?31543



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

RCWE0805R750FKE	A RCWE0805R390EKE	A RCWE0402R110ENE	A RCWE0402R120FNEA
RCWE0402R130FNEA	RCWE0402R150FNEA	RCWE0402R160FNEA	RCWE0402R180FNEA
RCWE0402R200FKEA	RCWE0402R220FKEA	RCWE0402R240FKEA	RCWE0402R270FKEA
RCWE0402R300FKEA	RCWE0402R330FKEA	RCWE0402R360FKEA	RCWE0402R390FKEA
RCWE0402R430FKEA	RCWE0402R470FKEA	RCWE0402R510FKEA	RCWE0402R560FKEA
RCWE0402R620FKEA	RCWE0402R680FKEA	RCWE0402R750FKEA	RCWE0402R820FKEA
RCWE0402R910FKEA	RCWE0603R110FKEA	RCWE0603R120FKEA	RCWE0603R130FKEA
RCWE0603R150FKEA	RCWE0603R160FKEA	RCWE0603R180FKEA	RCWE0603R200FKEA
RCWE0603R240FKEA	RCWE0603R270FKEA	RCWE0603R300FKEA	RCWE0603R330FKEA
RCWE0603R360FKEA	RCWE0603R390FKEA	RCWE0603R430FKEA	RCWE0603R470FKEA
RCWE0603R510FKEA	RCWE0603R560FKEA	RCWE0603R620FKEA	RCWE0603R680FKEA
RCWE0603R750FKEA	RCWE0603R820FKEA	RCWE0603R910FKEA	RCWE0805R220FKEA
RCWE0805R240FKEA	RCWE0805R270FKEA	RCWE0805R300FKEA	RCWE0805R330FKEA
RCWE0805R360FKEA	RCWE0805R430FKEA	RCWE0805R470FKEA	RCWE0805R510FKEA
RCWE0805R560FKEA	RCWE0805R620FKEA	RCWE0805R680FKEA	RCWE0805R820FKEA
RCWE0805R910FKEA	RCWE1206R220FKEA	RCWE1206R240FKEA	RCWE1206R270FKEA
RCWE1206R300FKEA	RCWE1206R360FKEA	RCWE1206R390FKEA	RCWE1206R430FKEA
RCWE1206R470FKEA	RCWE1206R510FKEA	RCWE1206R560FKEA	RCWE1206R620FKEA
RCWE1206R680FKEA	RCWE1206R750FKEA	RCWE1206R820FKEA	RCWE1206R910FKEA
RCWE1210R220FKEA	RCWE1210R240FKEA	RCWE1210R270FKEA	RCWE1210R300FKEA
RCWE1210R330FKEA	RCWE1210R360FKEA	RCWE1210R390FKEA	RCWE1210R430FKEA
RCWE1210R470FKEA	RCWE1210R510FKEA	RCWE1210R560FKEA	RCWE1210R620FKEA
RCWE1210R680FKEA	RCWE1210R750FKEA	RCWE1210R820FKEA	RCWE1210R910FKEA
RCWE2010R510FKEA	RCWE2010R560FKEA	RCWE2010R620FKEA	RCWE2010R680FKEA
RCWE2010R750FKEA	RCWE2010R820FKEA	RCWE2010R910FKEA	RCWE2512R510FKEA