

## Schottky Rectifier, 3.0 A


**SMC**

**FEATURES**

- Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability
- Halogen-free according to IEC 61249-2-21 definition
- Small foot print, surface mountable
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Compliant to RoHS directive 2002/95/EC


**RoHS**  
 COMPLIANT  
 HALOGEN  
**FREE**
**PRODUCT SUMMARY**

|                 |                 |
|-----------------|-----------------|
| Package         | SMC             |
| $I_{F(AV)}$     | 3.0 A           |
| $V_R$           | 60 V            |
| $V_F$ at $I_F$  | 0.52 V          |
| $I_{RM}$        | 20 mA at 125 °C |
| $T_J$ max.      | 150 °C          |
| Diode variation | Single die      |
| $E_{AS}$        | 5.0 mJ          |

**DESCRIPTION**

The VS-30BQ060-M3 surface mount Schottky rectifier has been designed for applications requiring low forward drop and small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

**MAJOR RATINGS AND CHARACTERISTICS**

| SYMBOL      | CHARACTERISTICS                             | VALUES      | UNITS |
|-------------|---|-------------|-------|
| $I_{F(AV)}$ | Rectangular waveform                        | 3.0         | A     |
| $V_{RRM}$   |   | 60          | V     |
| $I_{FSM}$   | $t_p = 5 \mu s$ sine                        | 1200        | A     |
| $V_F$       | 3.0 Apk, $T_J = 125 \text{ }^\circ\text{C}$ | 0.52        | V     |
| $T_J$       | Range                                       | - 55 to 150 | °C    |

**VOLTAGE RATINGS**

| PARAMETER                            | SYMBOL    | VS-30BQ060-M3 | UNITS |
|--------------------------------------|-----------|---------------|-------|
| Maximum DC reverse voltage           | $V_R$     | 60            | V     |
| Maximum working peak reverse voltage | $V_{RWM}$ |               |       |

**ABSOLUTE MAXIMUM RATINGS**

| PARAMETER  | SYMBOL      | TEST CONDITIONS   | VALUES | UNITS |
|--|-------------|---|--------|-------|
| Maximum average forward current  | $I_{F(AV)}$ | 50 % duty cycle at $T_L = 123 \text{ }^\circ\text{C}$ , rectangular waveform  | 3.0    | A     |
|  |             | 50 % duty cycle at $T_L = 113 \text{ }^\circ\text{C}$ , rectangular waveform  | 4.0    |       |
| Maximum peak one cycle non-repetitive surge current at $T_C = 25 \text{ }^\circ\text{C}$ | $I_{FSM}$   | 5 $\mu s$ sine or 3 $\mu s$ rect. pulse   | 1200   | A     |
|  |             | 10 ms sine or 6 ms rect. pulse  |        |       |
| Non-repetitive avalanche energy  | $E_{AS}$    | $T_J = 25 \text{ }^\circ\text{C}$ , $I_{AS} = 1.0 \text{ A}$ , $L = 10 \text{ mH}$                                  | 5.0    | mJ    |
| Repetitive avalanche current   | $I_{AR}$    | Current decaying linearly to zero in 1 $\mu s$<br>Frequency limited by $T_J$ maximum $V_A = 1.5 \times V_R$ typical | 1.0    | A     |

| ELECTRICAL SPECIFICATIONS       |                |   |                                   |        |            |
|---------------------------------|----------------|---|-----------------------------------|--------|------------|
| PARAMETER                       | SYMBOL         | TEST CONDITIONS   |                                   | VALUES | UNITS      |
| Maximum forward voltage drop    | $V_{FM}^{(1)}$ | 3 A   | $T_J = 25\text{ }^\circ\text{C}$  | 0.58   | V          |
|                                 |                | 6 A   |                                   | 0.76   |            |
|                                 |                | 3 A   | $T_J = 125\text{ }^\circ\text{C}$ | 0.52   |            |
|                                 |                | 6 A   |                                   | 0.66   |            |
| Maximum reverse leakage current | $I_{RM}$       | $T_J = 25\text{ }^\circ\text{C}$  | $V_R = \text{Rated } V_R$         | 0.5    | mA         |
|                                 |                | $T_J = 125\text{ }^\circ\text{C}$   |                                   | 20     |            |
| Maximum junction capacitance    | $C_T$          | $V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz), $25\text{ }^\circ\text{C}$ |                                   | 180    | pF         |
| Typical series inductance       | $L_S$          | Measured lead to lead 5 mm from package body                                      |                                   | 3.0    | nH         |
| Maximum voltage rate of change  | $dV/dt$        | Rated $V_R$   |                                   | 10 000 | V/ $\mu$ s |

**Note**

(1) Pulse width = 300  $\mu$ s, duty cycle = 2 %

| THERMAL - MECHANICAL SPECIFICATIONS             |                  |                                      |  |             |                    |
|---|------------------|--------------------------------------|--|-------------|--------------------|
| PARAMETER                                       | SYMBOL           | TEST CONDITIONS                      |  | VALUES      | UNITS              |
| Maximum junction temperature range              | $T_J^{(1)}$      |                                      |  | - 55 to 150 | $^\circ\text{C}$   |
| Maximum storage temperature range               | $T_{Stg}$        |                                      |  |             |                    |
| Maximum thermal resistance, junction to lead    | $R_{thJL}^{(2)}$ | DC operation                         |  | 12          | $^\circ\text{C/W}$ |
| Maximum thermal resistance, junction to ambient | $R_{thJA}$       |                                      |  | 46          |                    |
| Approximate weight                              |                  |                                      |  | 0.24        | g                  |
|   |                  |                                      |  | 0.008       | oz.                |
| Marking device                                  |                  | Case style SMC (similar to DO-214AB) |  | 3H          |                    |

**Notes**

(1)  $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$  thermal runaway condition for a diode on its own heatsink

(2) Mounted 1" square PCB




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)




Fig. 5 - Maximum Average Forward Current vs. Allowable Lead Temperature




Fig. 6 - Maximum Average Forward Dissipation vs. Average Forward Current





Fig. 7 - Maximum Peak Surge Forward Current vs. Pulse Duration

**Note**

- (1) Formula used:  $T_C = T_J - (P_d + P_{d_{REV}}) \times R_{thJC}$ ;
- $P_d$  = Forward power loss =  $I_{F(AV)} \times V_{FM}$  at  $(I_{F(AV)}/D)$  (see fig. 6);
- $P_{d_{REV}}$  = Inverse power loss =  $V_{R1} \times I_R (1 - D)$ ;  $I_R$  at  $V_{R1} = 80\%$  rated  $V_R$



**ORDERING INFORMATION TABLE**



- 1** - Vishay Semiconductors product suffix
- 2** - Current rating
- 3** - B = SMC
- 4** - Q = Schottky "Q" series
- 5** - Voltage rating (060 = 60 V)
- 6** - Environmental digit:  
-M3 = Halogen-free, RoHS compliant and terminations lead (Pb)-free

| <b>ORDERING INFORMATION</b> (Example) |                        |                        |                                    |
|---------------------------------------|------------------------|------------------------|------------------------------------|
| PREFERRED P/N                         | PREFERRED PACKAGE CODE | MINIMUM ORDER QUANTITY | PACKAGING DESCRIPTION              |
| VS-30BQ060-M3/9AT                     | 9AT                    | 3500                   | 13" diameter plastic tape and reel |

| <b>LINKS TO RELATED DOCUMENTS</b> |  |
|-----------------------------------|--|
| Dimensions                        | <a href="http://www.vishay.com/doc?95402">www.vishay.com/doc?95402</a> |
| Part marking information          | <a href="http://www.vishay.com/doc?95403">www.vishay.com/doc?95403</a> |
| Packaging information             | <a href="http://www.vishay.com/doc?95404">www.vishay.com/doc?95404</a> |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**