



T62 Natural Graphite Sheet

REACH Compliant RoHS Compliant

Features

- · Ultra high thermal conductivity
- · Easy to assemble
- · Low mass decreases space
- · EMI reduction

Applications

Suitable for products requiring flat temperature

Electronic components - Electric Vehicles, 5G, Autopilot System, Mobile Phone, AIOT, HPC (High Performance Computing), Server, IC, CPU, MOS, LED, Mother Board, Power Supply, Heat Sink, LCD-TV, Notebook, PC, Telecom Device, Wireless Hub, DDR II Module, etc.

Properties

Properties	T62	T62-1	T62-2	Unit	Tolerance	Test Method
Thermal Conductivity (XY axis)	400			W/mK	-	AC calorimeter
Thermal Conductivity (Z axis)	20	15	5	W/mK	±10%	Laser flash
Thickness	0.13	0.16	0.2	mm	±0.03	Micrometer
	0.0051	0.0063	0.0079	inch	-	-
Colour	Black			-	-	Visual
Structure	Graphite	Graphite Adhesive	PET Graphite Adhesive	-	-	-
Density	1.5~1.8			g/cm³	±0.05	ASTM D792
Graphite Contained	>98			%	-	-
Working Temperature	-30~+100			°C	-	-

Pre-cut for different shapes

T +44 (0)1455 553 510

Available to apply adhesive

Other thickness is available, please contact product consultant

T-Global Technology (Europe & North America) Limited

Units 1-2 Cosford Business Park, Central Park, Lutterworth, Leicestershire, LE17 4QU, United Kingdom **E** sales@tglobaltechnology.com **W** www.tglobaltechnology.com



T-Global Technology are proud to announce the launch of a new company logo and mission statement as part of the ongoing growth and evolution of our company's brand.

NOTICE: The information contained herein is to the best of our knowledge true and accurate. Values stated in this technical data sheet represent typical values as not all tests are run on each lot of material produced. All specifications are subject to change without notice. The protective film does not affect the function of the product. If there is no special requirement, the default depends on T-Global. Since the varied conditions of potential use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part and users should make their own test to determine the suitability of our products in any specific situation. This product is sold without warranty either expressed or implied, of fitness for a particular purpose or otherwise, except that this product shall be of standard quality, and except to the extent otherwise stated in T-Global Technology's invoice, quotation, or order acknowledgment.