

NUP4060AXV6

ESD Protection Diode Array, 4-Line

This 4-line surge protection array is designed for application requiring transient voltage protection capability. It is intended for use in over-transient voltage and ESD sensitive equipment such as cell phones, portables, computers, printers and other applications. This device features a common cathode design which protects four independent lines in a single SOT-563 package.

Features

- Protects up to 4 Lines in a Single SOT-563 Package
- ESD Rating: IEC61000-4-2: Level 4
Contact (8 kV), Air (15 kV)
- V_{CC} Pin = 16 V Protection
D1, D2, and D3 Pins = 6.8 V Protection
- Low Capacitance (< 7 pF @ 3 V) for D1, D2, and D3
- This is a Pb-Free Device

Applications

- Hand Held Portable Applications
- USB Interface
- Notebooks, Desktops, Servers
- SIM Card Protection

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Rating | Value | Unit |
|------------|---|---------------|------------------|
| P_{PK} 1 | Peak Power Dissipation | 200 | W |
| | V_{CC} Diode 8x20 μsec double exponential waveform, (Note 1) D1, D2, and D3 | 20 | W |
| T_J | Operating Junction Temperature Range | -40 to 125 | $^\circ\text{C}$ |
| T_{STG} | Storage Temperature Range | -55 to 150 | $^\circ\text{C}$ |
| T_L | Lead Solder Temperature – Maximum (10 seconds) | 260 | $^\circ\text{C}$ |
| ESD | IEC 61000-4-2 Air IEC 61000-4-2 Contact | 15000 8000 | V |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Nonrepetitive current pulse per Figure 1.




ON Semiconductor[®]


www.onsemi.com

SOT-563 4-LINE SURGE PROTECTION


PIN ASSIGNMENT



MARKING DIAGRAM



SOT-563
CASE 463A
STYLE 6



MT = Specific Device Code
M = Date Code
▪ = Pb-Free Package
(Note: Microdot may be in either location)

ORDERING INFORMATION

| Device | Package | Shipping [†] |
|----------------|----------------------|-----------------------|
| NUP4060AXV6T1G | SOT-563 (Pb-Free) | 4000/Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

NUP4060AXV6

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$, unless otherwise specified)

| Parameter | Conditions | Symbol | Min | Typ | Max | Unit |
|---|---|-----------|------|------|------|---------------|
| Reverse Working Voltage (D_1 , D_2 , and D_3) | (Note 2) | V_{RWM} | - | - | 5.0 | V |
| Breakdown Voltage (D_1 , D_2 , and D_3) | $I_T = 1 \text{ mA}$, (Note 3) | V_{BR} | 6.2 | 6.8 | 7.2 | V |
| Breakdown Voltage (V_{CC}) | $I_T = 5 \text{ mA}$, (Note 3) | V_{BR2} | 15.3 | 16 | 17.1 | V |
| Reverse Leakage Current (D_1 , D_2 , and D_3) | $V_{RWM} = 3 \text{ V}$ | I_R | - | 0.01 | 0.5 | μA |
| Reverse Leakage Current (V_{CC}) | $V_{BR} = 11 \text{ V}$ | I_R | - | - | 0.05 | μA |
| Capacitance (D_1 , D_2 , and D_3) | $V_R = 3 \text{ V}$, $f = 1 \text{ MHz}$ (Line to GND) | C_J | - | 7 | 10 | pF |

- Surge protection devices are normally selected according to the working peak reverse voltage (V_{RWM}), which should be equal or greater than the DC or continuous peak operating voltage level.
- V_{BR} is measured at pulse test current I_T .

NUP4060AXV6

TYPICAL ELECTRICAL CHARACTERISTICS

(Diode D₁, D₂, and D₃ only)




Figure 1. Pulse Width




Figure 2. Power Derating Curve




Figure 3. Reverse Leakage versus Temperature




Figure 4. Capacitance




Figure 5. $8 \times 20 \mu\text{s}$ Pulse Waveform





Figure 6. Forward Voltage

NUP4060AXV6

PACKAGE DIMENSIONS

SOT-563, 6 LEAD
CASE 463A
ISSUE G




NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

| DIM | MILLIMETERS | | | INCHES | | |
|----------------|-------------|------|------|----------|-------|-------|
| | MIN | NOM | MAX | MIN | NOM | MAX |
| A | 0.50 | 0.55 | 0.60 | 0.020 | 0.021 | 0.023 |
| b | 0.17 | 0.22 | 0.27 | 0.007 | 0.009 | 0.011 |
| C | 0.08 | 0.12 | 0.18 | 0.003 | 0.005 | 0.007 |
| D | 1.50 | 1.60 | 1.70 | 0.059 | 0.062 | 0.066 |
| E | 1.10 | 1.20 | 1.30 | 0.043 | 0.047 | 0.051 |
| e | 0.5 BSC | | | 0.02 BSC | | |
| L | 0.10 | 0.20 | 0.30 | 0.004 | 0.008 | 0.012 |
| H _E | 1.50 | 1.60 | 1.70 | 0.059 | 0.062 | 0.066 |

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com
Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor:](#)

[NUP4060AXV6T1G](#)