

Is Now Part of



# **ON Semiconductor**®

# To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="https://www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="https://www.onsemi.com">Fairchild\_questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese



## HCPL0600, HCPL0601, HCPL0611, HCPL0637, HCPL0638, HCPL0639 High Speed-10 MBit/s Logic Gate Optocouplers

#### Single Channel: HCPL0600, HCPL0601, HCPL0611 Dual Channel: HCPL0637, HCPL0638, HCPL0639

#### Features


- Compact SO8 package
- Very high speed-10 MBit/s
- Superior CMR
- Logic gate output
- Strobable output (single channel devices)
- Wired OR-open collector
- U.L. recognized (File # E90700)
- IEC60747-5-2 approved (VDE option)
   HCPL0600, HCPL0601, HCPL0611 only

### Applications


- Ground loop elimination
- LSTTL to TTL, LSTTL or 5-volt CMOS
- Line receiver, data transmission
- Data multiplexing
- Switching power supplies
- Pulse transformer replacement
- Computer-peripheral interface

#### Description


The HCPL06XX optocouplers consist of an AlGaAS LED, optically coupled to a very high speed integrated photo-detector logic gate with a strobable output (single channel devices). The devices are housed in a compact small-outline package. This output features an open collector, thereby permitting wired OR outputs. The HCPL0600, HCPL0601 and HCPL0611 output consists of bipolar transistors on a bipolar process while the HCPL0637, HCPL0638, and HCPL0639 output consists of bipolar transistors on a CMOS process for reduced power consumption. The coupled parameters are guaranteed over the temperature range of -40°C to +85°C. An internal noise shield provides superior common mode rejection.



August 2013



Single-channel circuit drawing (HCPL0600, HCPL0601 and HCPL0611)



Dual-channel circuit drawing (HCPL0637, HCPL0638 and HCPL0639)

#### Truth Table (Positive Logic)

Input	Enable	Output
Н	Н	L
L	Н	Н
Н	L	Н
L	L	Н
H*	NC*	L*
L*	NC*	H*

\*Dual channel devices or single channel devices with pin 7 not connected. A  $0.1\mu$ F bypass capacitor must be connected between pins 8 and 5. (See note 1)

#### Absolute Maximum Ratings (No derating required up to 85°C)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter		Value	Units
T <sub>STG</sub>	Storage Temperature		-40 to +125	°C
T <sub>OPR</sub>	Operating Temperature		-40 to +85	°C
EMITTER				
١ <sub>F</sub>	DC/Average Forward Input Current	Single Channel	50	mA
	(each channel)	Dual Channel		
V <sub>E</sub>	Enable Input Voltage Not to exceed VCC by more than 500mV	Single Channel	5.5	V
V <sub>R</sub>	Reverse Input Voltage (each channel)		5.0	V
PI	Power Dissipation	Single Channel	45	mW
		Dual Channel		
DETECTOR			· · ·	
V <sub>CC</sub> (1 minute max)	Supply Voltage		7.0	V
Ι <sub>Ο</sub>	Output Current (each channel)	Single Channel	50	mA
		Dual Channel	15	
Vo	Output Voltage (each channel)		7.0	V
Po	Collector Output Power Dissipation	Single Channel	85	mW
		Dual Channel	85	

### **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter		Min.	Max.	Units
I <sub>FL</sub>	Input Current, Low Level		0	250	μΑ
I <sub>FH</sub>	Input Current, High Level		*6.3	15	mA
V <sub>CC</sub>	Supply Voltage, Output		4.5	5.5	V
V <sub>EL</sub>	Enable Voltage, Low Level	Single Channel only	0	0.8	V
V <sub>EH</sub>	Enable Voltage, High Level	Single Channel only	2.0	V <sub>CC</sub>	V
T <sub>A</sub>	Operating Temperature	ł	-40	+85	°C
Ν	Fan Out (TTL load)	Single Channel		8	TTL Loads
		Dual Channel		5	
RL	Output Pull-up		330	4K	Ω

\*6.3mA is a guard banded value which allows for at least 20% CTR degradation. Initial input current threshold value is 5.0mA or less

#### **Electrical Characteristics** ( $T_A = -40^{\circ}C$ to $+85^{\circ}C$ unless otherwise specified.) Individual Component Characteristics

Symbol	Parameter	Test Conditions		Min.	Тур.*	Max.	Unit	
EMITTER							1	
V <sub>F</sub>	Input Forward Voltage	I <sub>F</sub> = 10mA					1.8	V
				$T_A = 25^{\circ}C$			1.75	1
B <sub>VR</sub>	Input Reverse Breakdown Voltage	I <sub>R</sub> = 10μΑ		•	5.0			V
$\Delta VF/\Delta TA$	Input Diode Temperature Coefficient	I <sub>F</sub> = 10mA			-1.5		mV/°C	
DETECTOR	3							
I <sub>CCH</sub>	High Level Supply Current	I <sub>F</sub> = 0mA,	V <sub>E</sub> = 0.5 V	Single Channel			10	mA
		$V_{CC} = 5.5V$		Dual Channel			15	]
I <sub>CCL</sub>	Low Level Supply Current	I <sub>F</sub> = 10mA,	V <sub>E</sub> = 0.5 V	Single Channel			13	mA
		$V_{CC} = 5.5V$		Dual Channel			21	1
I <sub>EL</sub>	Low Level Enable Current	V <sub>CC</sub> = 5.5V, V	<sub>E</sub> = 0.5V	Single Channel			-1.6	mA
I <sub>EH</sub>	High Level Enable Current	V <sub>CC</sub> = 5.5V, V	<sub>E</sub> = 2.0V	Single Channel			-1.6	mA
V <sub>EH</sub>	High Level Enable Voltage	$V_{CC} = 5.5 V, I_{F}$	= 10mA	Single Channel	2.0			V
V <sub>EL</sub>	Low Level Enable Voltage	$V_{CC} = 5.5 V, I_{F}$	= 10mA <sup>(2)</sup>	Single Channel			0.8	V

Symbol	AC Characteristics	Test Conditi	ons	Device	Min.	Тур.	Max.	Unit
T <sub>PLH</sub>	Propagation Delay Time	$R_L = 350\Omega, C_L = 15pF^{(3)}$	$T_A = 25^{\circ}C$	All	20		75	ns
	to Output High Level	(Fig. 20)					100	1
T <sub>PHL</sub>	Propagation Delay Time	$R_L = 350\Omega, C_L = 15pF^{(4)}$	$T_A = 25^{\circ}C$	All	25		75	ns
	to Output Low Level	(Fig. 20)					100	1
IT <sub>PHL</sub> -T <sub>PLH</sub> I	Pulse Width Distortion	$R_L = 350\Omega$ , $C_L = 15pF$ (Fig. 20)		All			35	ns
t <sub>r</sub>	Output Rise Time (10-90%)	$R_L = 350\Omega, C_L = 15pF^{(5)}$ (F	ig. 20)	Single Ch		50		ns
				Dual Ch		17		1
t <sub>f</sub>	Output Fall Time (90-10%)	$R_L = 350\Omega, C_L = 15pF^{(6)}$ (F	ig. 20)	Single Ch		12		ns
				Dual Ch		5		1
t <sub>ELH</sub>	Enable Propagation Delay Time to Output High Level	$I_F$ = 7.5mA, V <sub>EH</sub> = 3.5V, R <sub>L</sub> = 350Ω, C <sub>L</sub> = 15pF <sup>(7)</sup> (Fig. 21)		HCPL0600 HCPL0601 HCPL0611		20		ns
t <sub>EHL</sub>	Enable Propagation Delay Time to Output Low Level	I <sub>F</sub> = 7.5mA, V <sub>EH</sub> = 3.5V, R <sub>L</sub> = 350Ω, C <sub>L</sub> = 15 pF <sup>(8)</sup> (Fig. 21)		HCPL0600 HCPL0601 HCPL0611		20		ns
ICM <sub>H</sub> I	Common Mode Transient Immunity	$R_{L} = 350\Omega, T_{A} = 25^{\circ}C,$ $I_{F} = 0mA,$	IV <sub>CM</sub> I = 10V	HCPL0600 HCPL0637	5,000			V/µs
	(at Output High Level)	V <sub>OH</sub> (Min.) = 2.0 V <sup>(9)</sup> (Fig. 22, 23)	$ V_{CM}  = 50V$	HCPL0601 HCPL0638	10,000			
			V <sub>CM</sub>   = 1,000V	HCPL0611	15,000			
				HCPL0639	25,000			
ICMLI	Common Mode Transient Immunity	$R_L = 350\Omega, T_A = 25^{\circ}C,$ $I_F = 7.5mA,$ (10)	$ V_{CM}  = 10V$	HCPL0600 HCPL0637	5,000			V/µs
	(at Output Low Level)	V <sub>OL</sub> (Max.) = 0.8 V <sup>(10)</sup> (Fig. 22, 23)	$ V_{CM}  = 50V$	HCPL0601 HCPL0638	10,000			
			V <sub>CM</sub>   = 1,000V	HCPL0611	15,000			1
				HCPL0639	25,000			1

Symbol	DC Characteristics	Test Conditions	Min.	Тур.*	Max.	Unit
I <sub>OH</sub>	High Level Output Current	$V_{CC} = 5.5 \text{V}, V_{O} = 5.5 \text{ V}, I_{F} = 250 \mu\text{A}, \\ V_{E} = 2.0 \text{V}^{(2)}$			100	μA
V <sub>OL</sub>	Low Level Output Voltage	$V_{CC} = 5.5V, I_F = 5mA, V_E = 2.0V,$ $I_{OL} = 13mA^{(2)}$			0.6	V
I <sub>FT</sub>	Input Threshold Current	$V_{CC} = 5.5$ V, $V_{O} = 0.6$ V, $V_{E} = 2.0$ V, $I_{OL} = 13$ mA			5	mA

Isolation Characteristics (T<sub>A</sub> = -40°C to +85°C unless otherwise specified.)

Symbol	Characteristics	Test Conditions	Min.	Тур.*	Max.	Unit
I <sub>I-O</sub>	Input-Output Insulation Leakage Current				1.0*	μA
V <sub>ISO</sub>	Withstand Insulation Test Voltage	$\begin{array}{l} {R_{H}} < 50\%,  {T_{A}} = 25^{\circ}C, \\ {I_{I-O}} \le 2\mu A,  t = 1   min.^{(11)} \end{array}$	3750			V <sub>RMS</sub>
R <sub>I-O</sub>	Resistance (Input to Output)	$V_{I-O} = 500V^{(11)}$		10 <sup>12</sup>		Ω
C <sub>I-O</sub>	Capacitance (Input to Output)	$f = 1 MHz^{(11)}$		0.6		pF

\*All typical values are at V<sub>CC</sub> = 5 V,  $T_A = 25^{\circ}C$ 

#### Notes:

- The V<sub>CC</sub> supply to each optoisolator must be bypassed by a 0.1µF capacitor or larger. This can be either a ceramic
  or solid tantalum capacitor with good high frequency characteristic and should be connected as close as possible
  to the package V<sub>CC</sub> and GND pins of each device.
- 2. Enable Input No pull up resistor required as the device has an internal pull up resistor.
- t<sub>PLH</sub> Propagation delay is measured from the 3.75mA level on the HIGH to LOW transition of the input current pulse to the 1.5V level on the LOW to HIGH transition of the output voltage pulse.
- t<sub>PHL</sub> Propagation delay is measured from the 3.75mA level on the LOW to HIGH transition of the input current pulse to the 1.5V level on the HIGH to LOW transition of the output voltage pulse.
- 5.  $t_r$  Rise time is measured from the 90% to the 10% levels on the LOW to HIGH transition of the output pulse.
- 6. t<sub>f</sub> Fall time is measured from the 10% to the 90% levels on the HIGH to LOW transition of the output pulse.
- t<sub>ELH</sub> Enable input propagation delay is measured from the 1.5V level on the HIGH to LOW transition of the input voltage pulse to the 1.5V level on the LOW to HIGH transition of the output voltage pulse.
- 8. t<sub>EHL</sub> Enable input propagation delay is measured from the 1.5V level on the LOW to HIGH transition of the input voltage pulse to the 1.5V level on the HIGH to LOW transition of the output voltage pulse.
- CM<sub>H</sub> The maximum tolerable rate of rise of the common mode voltage to ensure the output will remain in the high state (i.e., V<sub>OUT</sub> > 2.0V). Measured in volts per microsecond (V/µs).
- CM<sub>L</sub> The maximum tolerable rate of fall of the common mode voltage to ensure the output will remain in the low output state (i.e., V<sub>OUT</sub> < 0.8V). Measured in volts per microsecond (V/μs).</li>
- 11. Device considered a two-terminal device: Pins 1, 2, 3 and 4 shorted together, and Pins 5, 6, 7 and 8 shorted together.

#### Typical Performance Curves (HCPL0600, HCPL0601 and HCPL0611 only)










Fig. 3 Input Threshold Current vs. Temperature















7





8















HCPL06XX — High Speed-10 MBit/s Logic Gate Optocouplers

## **Ordering Information**


Option	Order Entry Identifier	Description
No Suffix	HCPL0600	Shipped in tubes (50 units per tube)
V*	HCPL0600V	IEC60747-5-2 approval
R2	HCPL0600R2	Tape and Reel (2500 units per reel)
R2V*	HCPL0600R2V	IEC60747-5-2 approval, Tape and Reel (2500 units per reel)


\*Available for HCPL0600, HCPL0601, HCPL0611 only.

## **Marking Information**




Definiti	ons			
1	Fairchild logo			
2	Device number			
3	VDE mark indicates IEC60747-5-2 approval (Note: Only appears on parts ordered with VDE option – See order entry table)			
4	One digit year code, e.g., '3'			
5	Two digit work week ranging from '01' to '53'			
6	Assembly package code			





Profile Freature	Pb-Free Assembly Profile
Temperature Min. (Tsmin)	150°C
Temperature Max. (Tsmax)	200°C
Time (t <sub>S</sub> ) from (Tsmin to Tsmax)	60–120 seconds
Ramp-up Rate (t <sub>L</sub> to t <sub>P</sub> )	3°C/second max.
Liquidous Temperature (T <sub>L</sub> )	217°C
Time $(t_L)$ Maintained Above $(T_L)$	60–150 seconds
Peak Body Package Temperature	260°C +0°C / –5°C
Time (t <sub>P</sub> ) within 5°C of 260°C	30 seconds
Ramp-down Rate ( $T_P$ to $T_L$ )	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: HCPL0638 HCPL0638R2