

NOTES: UNLESS OTHERWISE SPECIFIED

1.





THIS IS A ROHS COMPLIANT COMPONENT/PRODUCT.
ALL ENGINEERING CHANGES MUST HAVE PRIOR APPROVAL BY THE DESIGN CENTER.


- PLASTIC: THERMOSET PLASTIC MATERIAL WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
- 3. SOLDERABILITY: CONFORMS TO ANSI/J-STD-002, IPC/EIA J-STD-003A.
- 4. OPERATING TEMPERATURE: 0°C TO +70°C
- 5. STORAGE TEMPERATURE: -20°C TO +125°C
- 6. JEDEC MOISTURE: LEVEL 1.
- 7. DIMENSIONS ARE IN INCHES, TOLERANCES ARE: $.XX = \pm .01$ $.XXX = \pm .005$

ELECTRICAL CHARACTERISTICS AT +25°C UNLESS OTHERWISE SPECIFIED (FOR REFERENCE ONLY. USED FOR CUSTOMER INFORMATION.)

(FOR REPERCIOE ONE). USED FOR OBSTOMER IN GRAMMION.)						
PARAMETER	SPECIFICATIONS					
OPERATING TEMP	0°C - 70°C					
TURNS RATIO	1.00 ± 2%					
POLARITY	PER SCHEMATIC					
TURNS RATIO (F=10 KHZ)	$(1-3)$: $(16-14)$ = 1CT : 1CT $\pm 2\%$ $(6-8)$: $(11-9)$ = 1CT : 2CT $\pm 2\%$ $(16-15)$: $(15-14)$ = 1:1 $\pm 2\%$ WITH PINS $(1-3)$ SHORTED $(11-10)$: $(10-9)$ = 1:1 $\pm 2\%$ WITH PINS $(6-8)$ SHORTED					
COUPLING CAPACITANCE	(1-3)-(16-14) = 8.0 pF MAX. (6-8)-(11- 9) = 12.0 pF MAX. (V=20mV, F=100 KHz)					
LEAKAGE INDUCTANCE	(1-3)-(16-14) = 0.3 uH MAX. (6-8)-(11-9) = 0.20 uH MAX. (V=20mV, F=100 KHz)					
LP	(1-3) = 98 uH MIN. (11-9) = 70 uH MIN. 15 - (16-14) = 42 uH MIN. (V=20mV, $F=10$ KHz)					
BETWEEN CHANNEL ISOLATION	1500 VAC MIN @ 60 SECONDS					







@ Copyright, 2010. Pulse Electronics Corp. All rights reserved. Drawing specifications subject to change without notice. (02/10/11)

PULSE CONFIDENTIAL	PRODUCT DESCRIPTION	PS DRAWING	SHEET:	DWG. NO./ PART NO.	REV.
PROPRIETARY	XFMR,SIN,10D,1:2,SM,TU	PS-2400.001-A	1	23Z467SMNL	M11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

PE-65745T 23Z467SMNLT 23Z467SMNL PE-65745NL PE-65745NLT