



504.1687

INTERLOCKED SOCKET

16A 3P+N+E 6h 346-415V 50Hz 60Hz II 2GD
130X260MM_PAR Screw terminals With
mechanical interlock

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	ADVANCE-GRP[GD] Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	INTERLOCKED SOCKET	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	INTERLOCKED SOCKET		
Mounting version	SURFACE MOUNTING		
Rated current	16A	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Poles	3P+N+E	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Hour position	6h		
Rated voltage (range)	250-400V	EN 60309-4 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Switched socket-outlets and connectors, with or without interlock
Rated voltage	346-415V		
Working frequency	60Hz	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Working frequency	50Hz	EN 60309-2/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Colour	RED		
Material	GRP Glass Reinforced Polyester		
Protection degree	Splash proof	EN 60309-4/A1 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. - Switched socket-outlets and connectors, with or without interlock
Protection degree IP	IP66	EN 60079-0 (2012)	[European Standard] Explosive atmospheres. General requirements.
Protection degree IK	IK10	IEC 60079-0 (2011)	[International Standard] Electrical Apparatus for Explosive Gas Atmospheres - Part 0: General Requirements.
Terminals	Screw terminals		
Flange	130X260MM_PAR	EN 60079-31 (2014)	[European Standard] Explosive atmospheres. Equipment dust ignition

Cable outlet	1xM25		protection by enclosure "t"
Working temperature	-40°C/+60°C	IEC 60079-31 (2013)	[International Standard] Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"
GLOW WIRE	GW 960°C	EN 60079-0/A11 (2013)	[European Standard] Explosive atmospheres. General requirements.
Self-extinguishing UL94	V0	EN 60079-1 (2014)	[European Standard] Electrical apparatus for explosive gas atmospheres - Part 1: Flameproof enclosures 'd'
Group and categories EX	II 2GD	EN 60079-7 (2015)	[European Standard] Explosive atmospheres. Equipment protection by increased safety "e"
Ambient temperature Ta min	-35 °C		
Ambient temperature Ta max	60 °C	IEC 60079-1 (2014)	[International Standard] Explosive atmospheres - Part 1: Equipment protection by flameproof enclosures "d".
Options	With mechanical interlock	IEC 60079-7 (2015)	[International Standard] Explosive atmospheres - Part 7: Equipment protection by increased safety "e".
Padlock	ø5mm	DIRECTIVE ATEX 2014/34/UE	[European Directives] Atmosphere Explosive