



Datasheet

Mount Non-Latching Relay

RS Stock number <u>476-573</u>

Dimensions: (mm)



Specification

- · Extremely low cost
- 1 from A and 1 from C configurations
- Subminiature, standard PCB layout
- Sealed IP67 & flux proof types available
- · Lead free and cadmium free
- 2.5KV dielectric strength (between coil contacts)
- Flammability class according to UL94, V-O
- CTI250
- VDE 0631/0700
- Environmental protection product available
- · RoHS and WEEE compliant



ENGLISH

Contact Arrangement	1A	1C	
Initial Contact	100mΩ		
Resistance Max.	(at 1A 6VDC)		
Contact Material	AgSnO ₂ , AgNi		
Contact Bathan (Box Load)	10A 277VAC	7A 250VAC	
Contact Rating (Res. Load)		10A 277VAC	
Max. switching voltage	277VAC/30VDC		
Max. switching current	15A	10A	
Max. switching power	2770VA 210W		
Mechanical life		1 x 10 ⁷ ops	
Electrical life		1 x 10°ops	

Initial Insulation Resistance			100MΩ ,500VDC	
Dielectric	Between coil and contacts		2000VAC/2500VAC, 1min	
Strength	Between open contacts		750VAC, 1min	
Operate time (at nomi. Volt.)			Max. 10ms	
Release time (at nomi. Volt.)			Max. 5ms	
Temperature rise (at nomi. Volt.)			Max. 60°C	
Shock Resistance		Functional	98 m/s²(10g)	
		Destructive	980 m/s²(100g)	
Vibration Resistance			1.5mm, 10 to 55Hz	
Humidity			35% to 85%RH	
Ambient temperature			-40°C to +105°C	
Termination			PCB	
Unit weight			Approx. 10g	
Construction			Sealed IP67 & Flux proof	

0.36W

Nominal Voltage VDC	Pick-up Voltage VDC	Drop-out Voltage VDC	Max. allowable Voltage VDC(at 25°C)	Coil Resistance Ω
3	2.25	0.3	3.9	25 ± 10%
5	3.75	0.5	6.5	70 ± 10%
6	4.50	0.6	7.8	100 ± 10%
9	6.75	0.9	11.7	225 ± 10%
12	9.00	1.2	15.6	400 ± 10%
18	13.5	1.8	23.4	900 ± 10%
24	18.0	2.4	31.2	1600 ± 10%
48	36.0	4.8	62.4	6400 ± 10%