


- PNP
- Normally open (NO)
- 2.00 mm
- Flush (shielded)
- Connector, M12x1-S04



**General attributes**

Approvals / Conformity

CE  
cULus  
EAC  
IEC 60947-5-2  
IP67  
Yes  
immune to magnetic DC and AC fields  
Yes  
No  
II  
Yes  
740 a

Basic standard

Enclosure Type per IEC 60529  
Function indicator  
Magnetic field immune  
Polarity reversal protected  
Power indicator  
Protection Class  
Short circuit protected  
MTTF (40°C)

**Electrical attributes**

Connection type  
Eff. operating current I<sub>e</sub>  
Eff. operating voltage U<sub>e</sub> DC  
Electrical version  
Load capacitance max. (at U<sub>e</sub>)  
Magnetic field strength  
Max. no-load cur. I<sub>o</sub> undamped  
Minimum operating current I<sub>m</sub>  
No-load current I<sub>o</sub> damped max.  
Operating voltage U<sub>B</sub> max. DC [V]  
Operating voltage U<sub>B</sub> min. DC [V]  
Rated insulation voltage U<sub>i</sub>  
Rated short circuit current  
Ripple max. (% of U<sub>e</sub>)

Connector  
200 mA  
24.0 V  
DC, direct current  
1.000 µF  
100 kA/m  
15.0 mA  
0 mA  
20.0 mA  
30.0 V  
10.0 V  
250 VAC  
100 A  
10 %

Switching freq. f max. (at U<sub>e</sub>)  
Switching function  
Switching output  
Voltage drop static max.

1000 Hz  
Normally open (NO)  
PNP  
2.5 V

**Mechanical attributes**

Ambient temperature T<sub>a</sub> max.  
Ambient temperature T<sub>a</sub> min.  
Assured operating distance S<sub>a</sub>  
Connector type  
Depth  
Diameter d1  
Eff. operating distance S<sub>r</sub>  
Housing material  
Mech. installation condition  
Mounting length  
Rated operating distance S<sub>n</sub> [mm]  
Sensing face material  
Surface protection  
Tightening torque

70 °C  
-25 °C  
1.60 mm  
M12x1-S04  
61.0 mm  
M12x1  
2.00 mm  
CuZn  
Flush (shielded)  
40.0 mm  
2.00 mm  
LCP  
PTFE coating  
10 Nm

**Remarks**

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.

