
## BES 516-324-E4-C-03 **BES00MZ**






- PNP Normally open (NO)
- 1.50 mm
- Flush (shielded)
  Cable, PVC, 3.00 m

## General attributes Approvals / Conformity

Basic standard Enclosure Type per IEC 60529 Function indicator Polarity reversal protected Power indicator Protection Class Short circuit protected MTTF

## Electrical attributes

Connection type Eff. operating current le Eff. operating voltage Ue DC Electrical version Load capacitance max. (at Ue) Max. no-load cur. lo undamped Minimum operating current Im No-load current lo damped max. Operating voltage UB max. DC [V] Operating voltage UB min. DC [V] Rated insulation voltage Ui Rated short circuit current Ripple max. (% of Ue) Switching freq. f max. (at Ue) Switching function Switching output



CE cULus EAC IEC 60947-5-2 IP68 according to BWN PR 20 Yes Yes No Ш Yes 830 a

Cable 200 mA 24.0 V DC, direct current 0.500 µF 3.0 mÁ 0 mA 9.0 mA 30.0 V 10.0 V 250 VAC 100 A 15 % 2500 Hz Normally open (NO) PNP





Voltage drop static max.

2.5 V

LISTED IND. CONT. EQ. 81U2

a class 2 source of supply

Mechanical attributes Ambient temperature Ta max. 70 °C -25 °C 1.20 mm Ambient temperature Ta min. Assured operating distance Sa Cable diameter D max. 3.0 mm Cable jacket material PVC 3.00 m 0.14 mm<sup>2</sup> Cable length Conductor cross-section Depth 30.0 mm Diameter d1 M08x1 Eff. operating distance Sr 1.50 mm Housing material Stainless steel Mech. installation condition Flush (shielded) Mounting length 29.0 mm Number of conductors 3 Rated operating distance Sn [mm] Sensing face material 1.50 mm PBT Tightening torque 8 Nm

Remarks

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.



Internet Balluff Germany Balluff USA Balluff China

www.balluff.com +49 (0) 7158 173-0, 173-370 1-800-543-8390 +86 (0) 21-50 644131

For definitions of terms, see main catalog Subject to change