




DH Series Double Headed Ties

| Application Tool | Registration Numbers |
|-----------------------|----------------------|
| MK3SP | 1 |
| MK3PNSP2, MK7P | 2 |
| MK7 | 3 |
| MK7HT | 4 |
| MK20 | 5 |
| MK6 | 6 |
| MK9P, MK6PN | 7 |
| MK9 | 8 |
| MK9HT | 9 |
| MK21 | 10 |

For more information please turn to page 410.



Technical Table

| Article-No. | Type | Length (L) | Width (W) | Ø per loop max. | Min. Tensile Strength (N) | Min. Tensile Strength (N) 2nd loop | Material | Colour | Application Tool |
|-------------|---------------|------------|-----------|-----------------|---------------------------|------------------------------------|----------|--------------|------------------|
| 117-05002 | T50RDH | 210 | 4.7 | 19.0 | 225 | 180 | PA66 | Natural (NA) | 1-10 |
| 117-05000 | T50RDH | 210 | 4.7 | 19.0 | 225 | 180 | PA66 | Black (BK) | 1-10 |
| 117-05060 | T50RDH | 210 | 4.7 | 19.0 | 225 | 180 | PA66W | Black (BK) | 1-10 |
| 117-05050 | T50RDH | 210 | 4.7 | 19.0 | 225 | 180 | PA66HS | Black (BK) | 1-10 |
| 117-00004 | T50RDH | 210 | 4.7 | 19.0 | 225 | 180 | PA46 | Grey (GY) | 1-10 |
| 117-05302 | T50IDH | 305 | 4.7 | 38.0 | 225 | 180 | PA66 | Natural (NA) | 1-10 |
| 117-05362 | T50IDH | 305 | 4.7 | 38.0 | 225 | 180 | PA66 | Black (BK) | 1-10 |
| 117-05360 | T50IDH | 305 | 4.7 | 38.0 | 225 | 180 | PA66W | Black (BK) | 1-10 |
| 117-05402 | T50LDH | 395 | 4.7 | 50.0 | 225 | 180 | PA66 | Natural (NA) | 1-10 |
| 117-05400 | T50LDH | 395 | 4.7 | 50.0 | 225 | 180 | PA66 | Black (BK) | 1-10 |
| 117-05460 | T50LDH | 395 | 4.7 | 50.0 | 225 | 180 | PA66W | Black (BK) | 1-10 |
| 117-00008 | T50LDH | 395 | 4.7 | 50.0 | 225 | 180 | PA66HS | Black (BK) | 1-10 |

All dimensions in mm. Subject to technical changes.



Please Note for Product Specific Approvals please refer to the Appendix