

Surface Mount PTC OZCJ Series

HF 60 0ZCJ Series – 1206 Chip

RoHS 2 Compliant

Product Features

- 1206 Chip Size, Fast Trip Time, Low DCR Resistance
- AEC-Q Compliant
- Meets Bel automotive qualification*
- * Largely based on internal AEC-Q test plan

Operating (Hold Current) Range

50mA - 2A

Maximum Voltage

6 - 60V (per table)

Temperature Range

-40°C to 85°C

Agency Approval

TUV (Std. EN/IEC 60738-1-1 and EN/IEC 60730-1, Cert. R50102117) UL Recognized Component (Std. UL1434, File E305051)



AEC-Q Compliant

Electrical Characteristics (23°C)

		Hold	Trip	Rated	Maximum	Typical	Max Tim	e to Trip	Resistance	Tolerance	Agency A	pprovals
	Part Number	Current	Current	Voltage	Current	Power	Current	Time	Rmin	R1max		Å₽
		Ін, А	It, A	Vmax, Vdc	Imax, A	Pd, W	А	Sec	Ohms	Ohms	C THE US	TÜV
Z	0ZCJ0005FF2E	0.05	0.15	60	10	0.4	0.25	1.50	3.600	50.00	Y	Y
A	0ZCJ0010FF2E	0.10	0.25	60	10	0.4	0.50	1.00	1.600	15.000	Y	Y
В	0ZCJ0012FF2E	0.12	0.39	48	10	0.5	1.00	0.20	1.400	6.500	Y	Υ
С	0ZCJ0016FF2E	0.16	0.45	48	10	0.5	1.00	0.30	1.100	5.000	Y	Y
D	0ZCJ0020FF2E	0.20	0.40	30	10	0.4	8.00	0.10	0.600	2.500	Y	Y
E	0ZCJ0025FF2E	0.25	0.50	16	100	0.6	8.00	0.08	0.550	2.300	Y	Y
	0ZCJ0025AF2E	0.25	0.50	24	40	0.6	8.00	0.08	0.550	2.300	Y	Y
F	0ZCJ0035FF2G	0.35	0.75	16	40	0.4	8.00	0.10	0.300	1.200	Y	Y
	0ZCJ0035AF2E	0.35	0.75	30	40	0.6	8.00	0.10	0.300	1.200	Y	Y
G	0ZCJ0050FF2G	0.50	1.00	8	100	0.4	8.00	0.10	0.150	0.700	Y	Y
0	0ZCJ0050AF2E	0.50	1.00	24	100	0.6	8.00	0.10	0.150	0.750	Y	Y
н	0ZCJ0075FF2E	0.75	1.50	8	100	0.6	8.00	0.20	0.090	0.290	Y	Y
	0ZCJ0075AF2E	0.75	1.50	16	100	0.6	8.00	0.20	0.090	0.290	Y	Y
1	0ZCJ0100FF2E	1.00	1.80	6	100	0.6	8.00	0.30	0.055	0.210	Y	Y
	0ZCJ0110FF2E	1.10	2.20	8	100	0.8	8.00	0.30	0.040	0.180	Y	Y
ting	0ZCJ0110AF2C	1.10	2.20	16	100	0.8	8.00	0.30	0.040	0.180	Y	Y
K	0ZCJ0150FF2C	1.50	3.00	8	100	0.8	8.00	1.00	0.040	0.120	Y	Y
L	0ZCJ0200FF2C	2.00	3.50	6	100	0.8	8.00	1.50	0.018	0.080	Y	Y

New Rating

IH Hold Current- The maximum current at which the device will not trip in still air at 23°C.

IT Trip current- The minimum current at which the device will trip in still air at 23°C.

Vmax Maximum voltage device can withstand at its rated current without suffering damage.

Imax Maximum fault current device can withstand at rated voltage (Vmax) without damage.

Pd Typical power dissipated by device when in tripped state in 23°C still air environment.

Rmin Minimum device resistance at 23°C in initial un-soldered state.

R1max Maximum device resistance at 23°C, 1 hour after initial device trip, or after being soldered to PCB in end application.





Specifications subject to change without notice



PTC's – Basic Theory of Operation / "Tripped" Resistance Explanation

A Bel PTC consists of a block of polymeric material containing conductive carbon granules which is sandwiched between two conductive metal plates. When this polymer block reaches approximately 125C, either due to current passing through it via conductive chains of carbon particles or due to an external heat source; it swells volumetrically. This expansion breaks apart a majority of the chains of carbon granules that run randomly between the two conductive plates. This behavior results in a sharp increase in resistance across the two plates which all but eliminates current flow through the device, allowing just enough residual current flow to maintain the block's internal temperature at 125C. Once this "tripped" state current is cut off, the polymer brick cools and shrinks to its original size, thereby allowing its broken carbon chains to reestablish themselves and permit the part to return to its low resistance state. Once cooled to room ambient, the PTC will once again exhibit a resistance less than its "R1max" rating.

At currents below the device IHOLD rating, AND at temperatures below 100C, the PTC maintains a resistance value below its R1 MAX rating.

The catalog data for each device specifies a "Typical Power" value. This is the power required to exactly match the heat lost by the tripped device to its ambient surroundings at 23C. By Ohm's Law, power can be stated as: $W = E^2/R$. Thus the approximate resistance of a "Tripped" PTC can be determined by: $R = E^2/W$, where "E" is the voltage appearing across the PTC (usually the supply's open circuit voltage), and "W" is the Typical Power value for the particular PTC.


Since the PPTC acts to maintain a constant internal temperature, its apparent resistance will change based upon applied voltage and, to a lesser degree, ambient conditions. Consider the following example.... A PTC with a Typical Power of 1 watt protecting a circuit using a 60V supply will demonstrate an apparent,

tripped resistance "R" of: R = $60^2/1 = 3,600$ ohms

This same tripped device when used to protect a 12V circuit would now present an apparent resistance of: $R = 12^2/1 = 144$ ohms

The value for Typical Power is "typical" because any physical factors that affect heat loss (such as ambient temperature or air convection) will somewhat alter the level of power that the PTC needs to maintain its internal temperature. In short, PTCs do not exhibit a constant, quantifiable tripped resistance value.

Average Time Current Characteristic Curve at 23°C



The Average Time Current Characteristic Curve and Temperature Rerating Curve are affected by a number of variables and these curves are provided for guidance only.



Specifications subject to change without notice

Bel Fuse Inc. 206 Van Vorst Street Jersey City, NJ 07302 USA +1 201.432.0463 Bel.US.CS@belf.com belfuse.com/circuit-protection

© 2019 Bel Fuse, Inc.

Type 0ZCJ Series

Pad Layout

The dimensions in the table below provide the recommended pad layout.

Termination Pad Materials

.


.

3/4

Matte Tin – Plated Copper

I T						
w	F	5	5	6	V	V
ļļ	Norr	ninal	Norr	ninal	Nom	ninal
	mm	Inch	mm	Inch	mm	Inch
	2.00	0.079	1.00	0.039	1.90	0.075
S+						

Mechanical Dimensions and Marking




All dimensions in mm.							
		Dime	Marking Code				
Part Number	С		[)			
	Min	Max	Min	Max	"b", IH code"		
0ZCJ0005FF2E	0.45	0.85	0.10	0.75	С		
0ZCJ0010FF2E	0.45	0.85	0.10	0.75	D		
0ZCJ0012FF2E	0.45	0.85	0.10	0.75	Y		
0ZCJ0016FF2E	0.45	0.75	0.10	0.75	Z		
0ZCJ0020FF2E	0.45	0.75	0.10	0.75	F		
0ZCJ0025FF2E	0.45	0.75	0.10	0.75	G		
0ZCJ0025AF2E	0.45	0.75	0.10	0.75	g		
0ZCJ0035FF2G	0.30	0.75	0.10	0.75	J		
0ZCJ0035AF2E	0.90	1.30	0.25	0.75	j		
0ZCJ0050FF2G	0.25	0.55	0.10	0.75	М		
0ZCJ0050AF2E	0.80	1.20	0.25	0.75	m		
0ZCJ0075FF2E	0.45	1.25	0.25	0.75	Р		
0ZCJ0075AF2E	0.45	1.25	0.25	0.75	р		
0ZCJ0100FF2E	0.45	1.00	0.25	0.75	1		
0ZCJ0110FF2E	0.45	1.00	0.25	0.75	R		
0ZCJ0110AF2C	0.80	1.40	0.25	0.75	r		
0ZCJ0150FF2C	0.80	1.40	0.25	0.75	S		
0ZCJ0200FF2C	0.85	1.60	0.25	0.75	2		

Temperature Derating Table

	Temperature Derating									
I Hold Value	-40	-20	0	23	30	40	50	60	70	85
0005 and 0010	152%	136%	120%	100%	92%	81%	71%	60%	48%	30%
0020 thru 0200	145%	131%	116%	100%	94%	86%	77%	69%	60%	48%

Thermal Derating Curve



Cautionary Notes

- Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.
- These Polymer PTC (PPTC) devices are intended for protection against occasional overcurrent/overtemperature fault conditions and may not be suitable for use in applications where repeated and/or prolonged fault conditions are anticipated.
- 3. Avoid contact of PTC device with chemical solvent. Prolonged contact may adversely impact the PTC performance.
- 4. These PTC devices may not be suitable for use in circuits with a large inductance, as the PTC trip can generate circuit voltage spikes above the PTC rated voltage.
- 5. These devices may be used in both DC and AC circuits provided that peak-to-peak line voltage when carrying AC does not exceed the PTC's Vmax rating. As PTCs are essentially thermal devices, the RMS value of AC current carried by a PTC will produce tripping parameters and times-to-trip similar to those of a DC voltage of the same magnitude.
- If potting is mandated, avoid rigid potting compounds as they will encase the PTC and prevent it from volumetrically expanding to properly respond to a trip event.
- 7. MSL: 2a (According to IPC J-Std-020).



Specifications subject to change without notice

Bel Fuse Inc. 206 Van Vorst Street Jersey City, NJ 07302 USA +1 201.432.0463 Bel.US.CS@belf.com belfuse.com/circuit-protection

Type 0ZCJ Series

Environmental Specifications

Temperature cycling	JESD22 Method JA-104			
Biased humidity	MIL-STD-202 Method 103			
Operational life	MIL-STD-202 Method 108			
Resistance to solvents	MIL-STD-202 Method 215			
Mechanical shock	MIL-STD-202 Method 213			
Vibration	MIL-STD-202 Method 204			
Resistance to soldering heat	MIL-STD-202 Method 210			
Thermal shock	MIL-STD-202 Method 107			
Solderability	ANSI/J-STD-002			
Board flex(SMD)	AEC-Q200-005			
Terminal strength	AEC-Q200-006			

Solder Reflow and Rework Recommendations

Profile Feature	Pb-Free Assembly	
Average Ramp-Up Rate (Tsmax to Tp)	3°C/second max	TpCritical Zone
Preheat : Temperature Min (Tsmin) Temperature Max (Tsmax) Time (tsmin to tsmax) Time maintained above: Temperature(TL) Time (tL)	150°C 200°C 60-180 seconds 217°C 60-150 seconds	T _L T _L T _T T _T
Peak/Classification Temperature(Tp) :	260°C	F Preheat
Time within 5°C of actual Peak : Temperature (tp)	20-40 seconds	25 t 25°C to Peak
Ramp-Down Rate :	6°C/second max.	Time >
Time 25°C to Peak Temperature :	8 minutes max	

Solder Reflow

Due to "lead free / RoHS 2 " construction of these PTC devices , the required Temperature and Dwell Time in the " Soldering " zone of the reflow profile are greater than those used for non-RoHS devices.

1. Recommended reflow methods; IR, vapor phase oven, hot air oven.

2. Not Recommended For Wave Solder / Direct Immersion.

3. Recommended paste thickness range – 0.20 - 0.25 mm.

4. Devices are compatible with standard industry cleaning solvents and methods.

5. MSL: 2a (According to IPC J-Std-020).

Caution

If reflow temperature / dwell times exceed the recommended profile, the electrical performance of the PTC may be affected. Rework: MIL-STD-202G Method 210F, Test Condition A.

Standard Packaging

Part Number	Tape/Reel Qty	4000, 3000 or 2000
0ZCJ0005FF2E Thru 0ZCJ0025AF2E	3,000	fuses in 7 inches dia. Reel, 8mm wide tape, 4mm pitch, per
0ZCJ0035FF2G	4,000	EIA-481(equivalent
0ZCJ0035AF2E	3,000	IEC-286 part 3).
0ZCJ0050FF2G	4,000	
0ZCJ0050AF2E Thru 0ZCJ0110FF2E	3,000	
0ZCJ0110AF2C Thru 0ZCJ0200FF2C	2,000	

P/N Explanation and Ordering Information

	OZCJ		X X XX
PTC series			
0ZCJ,1206 Size			
I HOLD Rating			
Refer to Part Number and IH Rating i	n Electrical Characterist	tics Table on P.	.1.
Electrical Characteristics			_
F = Standard Design	rance DCD sort sta		
A to Z (except F) = Special, customer	spec, DCH sort, etc.		
Mechanical Features —			
F = Standard Design			
A to Z (except F) = Special, custome	r spec, lead forming, et	с.	
Tape & Reel Qty			
See standard packaging			



Specifications subject to change without notice

Bel Fuse Inc. 206 Van Vorst Street Jersey City, NJ 07302 USA +1 201.432.0463 Bel.US.CS@belf.com belfuse.com/circuit-protection

© 2019 Bel Fuse, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

 OZCJ0012FF2E
 OZCJ0200FF2C
 OZCJ0020FF2E
 OZCJ0025AF2E
 OZCJ0035AF2E
 OZCJ0005FF2E

 OZCJ0050AF2E
 OZCJ0010FF2E
 OZCJ000FF2E
 OZCJ0025FF2E
 OZCJ0035FF2G
 OZCJ0075FF2E
 OZCJ0010FF2E

 OZCJ0150FF2C
 OZCJ0110FF2E
 OZCJ0075AF2E
 OZCJ0050FF2G
 OZCJ0110AF2C
 OZCJ0010FF2E