

8M × 8 BANKS × 16 BIT DDR2 SDRAM

Table of Contents-

1.		GENERAL	DESCRIPTION	⊿
2.		FEATURE	S	⊿
3.			NFORMATION	
4.			AMETERS	
5.			NFIGURATION	
3. -			SCRIPTION	
7.			AGRAM	
3.			NAL DESCRIPTION	
	8.1		and Initialization Sequence	
	8.2		ister and Extended Mode Registers Operation	
		8.2.1	Mode Register Set Command (MRS)	
		8.2.2	Extend Mode Register Set Commands (EMRS)	
		8.2.2.1	Extend Mode Register Set Command (1), EMR (1)	
		8.2.2.2		
		8.2.2.3	3	
		8.2.2.4	Extend Mode Register Set Command (3), EMR (3)	
		8.2.3	Off-Chip Driver (OCD) Impedance Adjustment	
		8.2.3.1	Extended Mode Register for OCD Impedance Adjustment	
		8.2.3.2	1	
		8.2.3.3		
		8.2.4	On-Die Termination (ODT)	
		8.2.5	ODT related timings	
		8.2.5.1	MRS command to ODT update delay	
	8.3		Function	
		8.3.1	Bank Activate Command	
		8.3.2	Read Command	
		8.3.3	Write Command	
		8.3.4	Burst Read with Auto-precharge Command	
		8.3.5	Burst Write with Auto-precharge Command	
		8.3.6	Precharge All Command	
		8.3.7	Self Refresh Entry Command	
		8.3.8	Self Refresh Exit Command	
		8.3.9	Refresh Command	
		8.3.10	No-Operation Command	
		8.3.11	Device Deselect Command	
	8.4	Read and	Write access modes	23
		8.4.1	Posted CAS	
		8.4.1.1	Examples of posted CAS operation	
		8.4.2	Burst mode operation	
		8.4.3	Burst read mode operation	
		8.4.4	Burst write mode operation	
		8.4.5	Write data mask	
	8.5		rupt	
	8.6	Precharge	operation	27

Publication Release Date: Dec. 02, 2020

W971GG6NB

		winbond
	8.6.1	Burst read operation followed by precharge
	8.6.2	Burst write operation followed by precharge
8	7 Auto-prec	harge operation

		8.6.1	Burst read operation followed by precharge	27
		8.6.2	Burst write operation followed by precharge	27
	8.7	Auto-prec	harge operation	27
		8.7.1	Burst read with Auto-precharge	28
		8.7.2	Burst write with Auto-precharge	
	8.8	Refresh C	peration	
	8.9		wn Mode	
		8.9.1	Power Down Entry	
		8.9.2	Power Down Exit	
	8.10		k frequency change during precharge power down	
9.	0.10	•	ON MODE	
э.	9.1		I Truth Table	
	9.2		In the trable	
	9.3		k (DM) Truth Table	
	9.4		Fruth Table	
	9.5		Stated Diagram	
	9.5		-	
10.	40.4		CAL CHARACTERISTICS	
	10.1		Maximum Ratings	
	10.2		Temperature Condition	
	10.3		ended DC Operating Conditions	
	10.4		Electrical Characteristics	
	10.5	•	Logic Level	
	10.6	•	Logic Level	
	10.7 10.8	-	ceand Output Buffer Characteristics	
	10.8	_	cteristics	
	10.9		Measurement Test Parameters	
	10.10		Characteristics	
	10.11	10.11.1	AC Characteristics and Operating Condition for -18/18I/18J speed grade	
		-	AC Characteristics and Operating Condition for -25/25I/25J/-3 speed grades	
	40.40	10.11.2	Input Test Conditions	
	10.12 10.13		·	
	10.13		erential Input/Output AC Logic Levels	
	10.14		Overshoot / Undershoot Specification	
		10.14.1	AC Overshoot / Undershoot Specification for Address and Control Pins:	
		10.14.2	AC Overshoot / Undershoot Specification for Clock, Data, Strobe and Mask Pins:	
11.			/AVEFORMS	
	11.1		I Input Timing	
	11.2		ng for Active/Standby Mode	
	11.3		ng for Power Down Mode	
	11.4		ng mode switch at entering power down mode	
	11.5		ng mode switch at exiting power down mode	
	11.6		ut (read) timing	
	11.7		d operation: RL=5 (AL=2, CL=3, BL=4)	
	11.8	•	t (write) timing	
	11.9		e operation: RL=5 (AL=2, CL=3, WL=4, BL=4)	
	11.10		mless burst read operation: RL = 5 (AL = 2, and CL = 3, BL = 4)	
	11.11 11.12		mless burst write operation: RL = 5 (WL = 4, BL = 4)st read interrupt timing: RL =3 (CL=3, AL=0, BL=8)	
	11.12		st read interrupt timing: RL=3 (CL=3, AL=0, BL=8)st write interrupt timing: RL=3 (CL=3, AL=0, WL=2, BL=8)	
	11.13		e operation with Data Mask: WL=3, AL=0, WL=2, BL=6)e	
	11.14	. ۷۷11	0 operation with Data Mack. WE-0, AL-0, DL-7/	1 C

Publication Release Date: Dec. 02, 2020

W971GG6NB

		ala windond alasa	7
	11.15	Burst read operation followed by precharge: RL=4 (AL=1, CL=3, BL=4, tRTP ≤ 2clks)	.77
	11.16	Burst read operation followed by precharge: RL=4 (AL=1, CL=3, BL=8, tRTP ≤ 2clks)	.77
	11.17	Burst read operation followed by precharge: RL=5 (AL=2, CL=3, BL=4, tRTP ≤ 2clks)	.78
	11.18	Burst read operation followed by precharge: RL=6 (AL=2, CL=4, BL=4, tRTP ≤ 2clks)	.78
	11.19	Burst read operation followed by precharge: RL=4 (AL=0, CL=4, BL=8, tRTP > 2clks)	.79
	11.20	Burst write operation followed by precharge: WL = (RL-1) = 3	.79
	11.21	Burst write operation followed by precharge: WL = (RL-1) = 4	.80
	11.22	Burst read operation with Auto-precharge: RL=4 (AL=1, CL=3, BL=8, tRTP ≤ 2clks)	.80
	11.23	Burst read operation with Auto-precharge: RL=4 (AL=1, CL=3, BL=4, tRTP > 2clks)	.81
	11.24 (AL=2,	Burst read with Auto-precharge followed by an activation to the same bank (tRC Limit): RL=5 CL=3, internal tRCD=3, BL=4, tRTP ≤ 2clks)	
	11.25 (AL=2,	Burst read with Auto-precharge followed by an activation to the same bank (tRP Limit): RL=5 CL=3, internal tRCD=3, BL=4, tRTP ≤ 2clks)	
	11.26	Burst write with Auto-precharge (tRC Limit): WL=2, WR=2, BL=4, tRP=3	
	11.27	Burst write with Auto-precharge (WR + tRP Limit): WL=4, WR=2, BL=4, tRP=3	.83
	11.28	Self Refresh Timing	.83
	11.29	Basic Power Down Entry and Exit Timing	.84
	11.30	Precharged Power Down Entry and Exit Timing	.84
	11.31	Clock frequency change in precharge Power Down mode	.85
12.		PACKAGE SPECIFICATION	
13		REVISION HISTORY	87



1. GENERAL DESCRIPTION

The W971GG6NB is a 1G bits DDR2 SDRAM, organized as 8,388,608 words \times 8 banks \times 16 bits. This device achieves high speed transfer rates up to 1066 Mbps (DDR2-1066) for various applications. W971GG6NB is sorted into the following grade parts: -18, 18I, 18J, -25, 25I, 25J and -3.

The -18, 18I and 18J grade parts are compliant to the DDR2-1066 (6-6-6) specification (The 18I industrial grade which is guaranteed to support -40°C \leq TCASE \leq 95°C, the 18J industrial plus grade which is guaranteed to support -40°C \leq TCASE \leq 105°C).

The -25, 25I and 25J grade parts are compliant to the DDR2-800 (5-5-5) or DDR2-800 (6-6-6) specification (The 25I industrial grade which is guaranteed to support -40°C \leq TCASE \leq 95°C, the 25J industrial plus grade which is guaranteed to support -40°C \leq TCASE \leq 105°C).

The -3 grade parts is compliant to the DDR2-667 (5-5-5) specification.

All of the control and address inputs are synchronized with a pair of externally supplied differential clocks. Inputs are latched at the cross point of differential clocks (CLK rising and $\overline{\text{CLK}}$ falling). All I/Os are synchronized with a single ended DQS or differential DQS- $\overline{\text{DQS}}$ pair in a source synchronous fashion.

2. FEATURES

- Power Supply: VDD, VDDQ = 1.8 V ± 0.1 V
- Double Data Rate architecture: two data transfers per clock cycle
- CAS Latency: 3, 4, 5, 6 and 7
- Burst Length: 4 and 8
- Bi-directional, differential data strobes (DQS and DQS) are transmitted / received with data
- Edge-aligned with Read data and center-aligned with Write data
- DLL aligns DQ and DQS transitions with clock
- Differential clock inputs (CLK and CLK)
- Data masks (DM) for write data
- Commands entered on each positive CLK edge, data and data mask are referenced to both edges of DQS
- Posted CAS programmable additive latency supported to make command and data bus efficiency
- Read Latency = Additive Latency plus CAS Latency (RL = AL + CL)
- Off-Chip-Driver impedance adjustment (OCD) and On-Die-Termination (ODT) for better signal quality
- Auto-precharge operation for read and write bursts
- · Auto Refresh and Self Refresh modes
- Precharged Power Down and Active Power Down
- Write Data Mask
- Write Latency = Read Latency 1 (WL = RL 1)
- Interface: SSTL 18
- Packaged in VFBGA 84 Ball (8x12.5 mm² with thickness of 1.0 mm) (Window BGA Type), using Lead free materials with RoHS compliant

Publication Release Date: Dec. 02, 2020



3. ORDER INFORMATION

PART NUMBER	SPEED GRADE	OPERATING TEMPERATURE
W971GG6NB-18	DDR2-1066 (6-6-6)	0°C ≤ Tcase ≤ 85°C
W971GG6NB18I	DDR2-1066 (6-6-6)	-40°C ≤ TCASE ≤ 95°C
W971GG6NB18J	DDR2-1066 (6-6-6)	-40°C ≤ TCASE ≤ 105°C
W971GG6NB-25	DDR2-800 (5-5-5) or DDR2-800 (6-6-6)	0°C ≤ TCASE ≤ 85°C
W971GG6NB25I	DDR2-800 (5-5-5) or DDR2-800 (6-6-6)	-40°C ≤ TCASE ≤ 95°C
W971GG6NB25J	DDR2-800 (5-5-5) or DDR2-800 (6-6-6)	-40°C ≤ TCASE ≤ 105°C
W971GG6NB-3	DDR2-667 (5-5-5)	0°C ≤ TCASE ≤ 85°C

4. KEY PARAMETERS

	SPE	ED GRADE			DDR2-1066	DDR2-800	DDR2-667
SYM.	Bin(C	L-tRCD-tRP)		6-6-6	5-5-5/6-6-6	5-5-5
	Part Nur	nber Extens		-18/18I/18J	-25/25I/25J	-3	
		Min.	1.875 nS	_	_		
		@CL = 7	Max.	7.5 nS	_	_	
			@CL = 6	Min.	1.875 nS	2.5 nS	_
			@CL = 6	Max.	7.5 nS	8 nS	_
tCK(avg)	Average clock period	@CL = 5	Min.	2.5 nS	2.5 nS	3 nS	
ick(avg)	Average clock period		@CL = 5	Max.	7.5 nS	8 nS	8 nS 3.75 nS 8 nS 5 nS 8 nS 15 nS -*2 7.8 µS*1
			@CL = 4	Min.	3 nS	3.75 nS	
			₩ OL = 4	Max.	7.5 nS	8 nS	
			@CL = 3	Min.	_ 5 nS 8	5 nS	
	@ CL = 3			Max.	ı	8 nS	8 nS
tRCD	Active to Read/Write Cor	mmand Dela	y Time	Min.	11.25 nS	12.5 nS	15 nS
	-40°C ≤ TC		ASE ≤ 85°C	Max.	7.8 µS* ^{2, 3}	7.8 µS* ^{2, 3}	
tREFI	Average periodic	0°C ≤ TCA	0°C ≤ TCASE ≤ 85°C		7.8 µS*1	7.8 μS* ¹	7.8 µS*1
INLIT	refresh Interval	85°C < TC	ASE ≤ 95°C	Max.	3.9 µS* ⁴	3.9 µS*4	3.9 µS* ⁴
	95°C <		ASE ≤ 105°C	Max.	3.9 µS*4	3.9 µS*4	3.9 µS* ⁴
tRP	Precharge to Active Com	nmand Perio	b	Min.	11.25 nS	12.5 nS	15 nS
tRC	Active to Ref/Active Com	mand Period	t	Min.	51.25 nS	52.5 nS	55 nS
tRAS	Active to Precharge Com	nmand Perio	b	Min.	40 nS	40 nS	40 nS
IDD0	Operating one bank active	/e-precharge	current	Max.	60 mA	55 mA	50 mA
IDD1	Operating one bank activ	e-read-prech	narge current	Max.	70 mA	65 mA	60 mA
IDD4R	IDD4R Operating burst read current			Max.	110 mA	105 mA	100 mA
IDD4W	Operating burst write cur	rent		Max.	120 mA	110 mA	100 mA
IDD5B	Burst refresh current			Max.	85 mA	80 mA	75 mA
IDD6	Self refresh current (TCA	SE ≤ 85°C)		Max.	8 mA	8 mA	8 mA
IDD7	Operating bank interleav	e read curre	nt	Max.	150 mA	140 mA	130 mA

Notes:

- 1. All speed grades support 0°C ≤ TCASE ≤ 85°C with full JEDEC AC and DC specifications.
- 2. For -18, -25 and -3 speed grades, -40°C \leq TCASE < 0°C is not available.
- 3. 18I and 25I speed grades support -40°C ≤ TCASE ≤ 85°C with full JEDEC AC and DC specifications.
- 4. For -18, 18I, -25, 25I and -3 speed grades, TCASE is able to extend to 95°C. For 18J and 25J speed grades, TCASE is able to extend to 105°C. They are with doubling Auto Refresh commands in frequency to a 32 mS period (tREFI = 3.9 μS) and to enter to Self Refresh mode at this high temperature range via A7 "1" on EMR (2).

Publication Release Date: Dec. 02, 2020



5. BALL CONFIGURATION

VDD			5	6	7	8	9
	NC	VSS	Α		VSSQ	UDQS	VDDQ
DQ14	VSSQ	UDM	В		UDQS	VSSQ	DQ15
VDDQ	DQ9	VDDQ	С		VDDQ	DQ8	VDDQ
DQ12	VSSQ	DQ11	D		DQ10	VSSQ	DQ13
VDD	NC	VSS	Е		VSSQ	LDQS	VDDQ
DQ6	VSSQ	LDM	F		LDQS	VSSQ	DQ7
VDDQ	DQ1	VDDQ	G		VDDQ	DQ0	VDDQ
DQ4	VSSQ	DQ3	Н		DQ2	VSSQ	DQ5
VDDL	VREF	VSS	J		VSSDL	CLK	VDD
	CKE	WE	K		RAS	CLK	ODT
BA2	BA0	BA1	L		CAS	CS	
	A10/AP	A1	М		A2	A0	VDD
VSS	А3	A5	N		A6	A4	
	A7	A9	Р		A11	A8	VSS
VDD	A12	NC	R		NC	NC	

W971GG6NB




6. BALL DESCRIPTION

Address and Auto-precharge bit for Read/Write commands to select on location out of the memory array in the respective bank. Row address: A0-A12. Column address: A0-A9. (A10 is used for Auto-precharge) BA0-BA2 Bank Select BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. GS 6C4.PT.A141.H19, F1.F9.06.6C2.D7.03, DQ0-DQ15 Data Input / Output Bi-directional data bus. DD16.PS.B1.B9 DD7 DD7 DD7 DD7 DD7 DD7 DD7 DD7 DD7 DD	BALL NUMBER	SYMBOL	FUNCTION	DESCRIPTION
Column address: A0-A9. (A10 is used for Auto-precharge) L2,L3,L1 BA0-BA2 Bank Select BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank an ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which bank and ACTIVE, READ, WRITE of PRECHARGE command is being applied. BA0-BA2 define to which the being applied. BA0-BA2 define to which the serior and the serior an	M8,M3,M7,N2,N8,N3 ,N7,P2,P8,P3,M2,P7		Address	Provide the row address for active commands, and the column address and Auto-precharge bit for Read/Write commands to select one location out of the memory array in the respective bank.
Bank Select	,R2			
PRECHARGE command is being applied. REG. 2P.7.03, D1,09,B1,B9 DODT On Die Termination Control DOT (registered HIGH) enables termination resistance internal to the DR2 SDRAM. DOT (registered HIGH) enables termination resistance internal to the DR2 SDRAM. LOQS, LDQS LOQS LOQS LOQS LOQS LOQUE LOW Data Strobe EACH COMPANY LOQUE LOW Data Strobe DODO-DQT, LDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. B7,A8 DDQS, UDQS UP Data Strobe UP Data Strobe UP Data Strobe for Lower Byte: Output with read data, input with write date on DQO-DQT, LDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. B8,A8 CS Chip Select Chip Select All commands are masked when CS is registered HIGH. CS provides for external rank selection on systems with multiple ranks CS is considered part of the command code. K7,L7,K3 RAS, CAS, WE Command Inputs RAS, CAS and WE (along with CS) define the command being entered. DM is an input mask signal for write data. Input data is masked when DM is sampled no both edges of DQS, Although DM pins are input only, the DM loading matches the DQ and DQS loading. LR CKE Coke Clock Enable CLK and CLK are differential clock inputs. All address and control input signals are sampled on both edges of DQS, Although DM pins are input only, the DM loading matches the DQ and DQS loading. CLK and CLK are differential clock inputs. All address and control input signals are sampled on the deges of DQS. Although DM pins are input only the DM loading matches the DQ and DQS loading. CLK and CLK are differential clock inputs. All address and control input signals are sampled on the other crossing of the positive edge of CLK and DQS. CRES is a sampled on the both positive edge of CLK and CLK (both directions of crossing). CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuity on the DDR2 SDRAM. CKE (registered LOW ASSI) DQS (registered LOW deacti				Column address: A0–A9. (A10 is used for Auto-precharge)
F1 F9 CB C2 D7 D3	L2,L3,L1	BA0-BA2	Bank Select	BA0-BA2 define to which bank an ACTIVE, READ, WRITE or PRECHARGE command is being applied.
F7.E8 LDQS, LDQS LOW Data Strobe LOW Data Strobe LOW Data Strobe for Lower Byte: Output with read data, input with write data for source synchronous operation. Edge-aligned with read data for source synchronous operation. Edge-aligned with read data center-aligned with write data. LDQS corresponds to the data or DQO-DQ7. LDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. B7,A8 LB CS Chip Select Chip Select Chip Select Chip Select Chip Select Chip Select R7,L7,K3 RAS, CAS, WE Command Inputs RAS, CAS and WE (along with CS) define the command code. R7,L7,K3 RAS, CAS, WE CUM, LDM Input Data Mask CLK, CLK Differential Clock Inputs CLK and CLK are differential clock inputs. All address and control input signals are sampled on both edges of DQS. Although DM priss an input only, the DM loading matches the DQ and DQS loading. CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLK and negative edge of CLK. Output (read) data is referenced to the crossings of CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLK and negative edge of CLK and CLK (both directions of crossing). CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. J2 VREF Reference Voltage VREF (Reference Voltage) VREF (Reference Voltage) Power Supply: 1.8V ± 0.1V. CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. A9,C1,C3,C7,C9,E9, Q1,C3,G7,C9,E9, C1,C3,G7,C9,E9, C	,F1,F9,C8,C2,D7,D3,	DQ0-DQ15	Data Input / Output	Bi-directional data bus.
F7.E8 LDQS, LDQS LDQS LOW Data Strobe for source synchronous operation. Edge-aligned with riead data center-aligned with write data. LDQS corresponds to the data or DQO-DQ7. LDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. B7.A8 LDQS, UDQS UP Data Strobe UP Data Strobe for Upper Byte: Output with read data center-aligned with write data. UDQS corresponds to the data or DQB-DQ15. UDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when differential conduction of the command code. RAS, CAS and WE (along with differential code). RAS, CAS and WE (along with differential code). B3,F3 UDM, LDM Input Data Mask Input Data Mask LDM is an input mask signal for write data. Input data is masked when the command being entered. CLK, CLK Differential Clock Inputs CLK and CLK are differential clock inputs. All address and control input signals are sampled on both edges of DAS. Although DM pins an input only, the DM loading matches the DQ and DQS loading. CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLK and CLK (both directions of crossing). CKE (registered HIGH). Signal and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. VEF is reference voltage for inputs. All club Al	K9	ODT		ODT (registered HIGH) enables termination resistance internal to the DDR2 SDRAM.
B7.A8 B7	F7,E8	LDQS, LDQS	LOW Data Strobe	Data Strobe for Lower Byte: Output with read data, input with write data for source synchronous operation. Edge-aligned with read data, center-aligned with write data. LDQS corresponds to the data on
B7,A8 B7,B7 B7,A8 B7,A8 B7,B7 B7,A8 B7,A8 B7,A8 B7,A8 B7,A8 B7,B7 B7,A8 B7,B7 B7,A8 B7,B7 B7,A8 B7,A8 B7,B7 B7,A8 B7,B7 B7,A8 B7,B7 B7,A8 B7,A8 B7,B7 B7,A8 B7,A8 B7,A8 B7,B7 B7,A8 B7,B7 B7,A8 B7,A8 B7,B7 B7,A8 B7,A8 B7,CAS Command Inputs B7,A8 B7,A8 B7,A8 B7,A8 B7,CAS Command Inputs B7,A8 B7,A8 B7,A8 B7,A8 B7,CAS Command Inputs B7,A8 B7,CAS Command Inputs B7,A8 B7,CAS B7,A8 B7,CAS Command Inputs B7,A8 B7,A8 B7,A8 B7,A8 B7,A8 B7,B9 B7,		·		DQ0-DQ7. LDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command].
DQ8-DQ15. UDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command]. All commands are masked when CS is registered HIGH. CS provides for external rank selection on systems with multiple ranks CS is considered part of the command code. RAS, CAS, WE Command Inputs B3,F3 UDM, LDM Input Data Mask UDM, LDM Input Data Mask CLK, CLK Differential Clock Inputs A1 CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLF and negative edge of CLF. Output (read) data is referenced to the crossings of CLK and CLK (both directions of crossing). CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. VREF Reference Voltage VREF is reference voltage for inputs. A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSSQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. DLL Ground DLL Ground.	B7,A8	UDQS. UDQS	UP Data Strobe	Data Strobe for Upper Byte: Output with read data, input with write data for source synchronous operation. Edge-aligned with read data, center-aligned with write data. UDQS corresponds to the data on
L8				DQ8-DQ15. UDQS is only used when differential data strobe mode is enabled via the control bit at EMR (1)[A10 EMRS command].
RAS , CAS , CAS and WE (along with CS) define the command being entered. B3,F3 UDM, LDM Input Data Mask DM is an input mask signal for write data. Input data is masked when DM is sampled high coincident with that input data during a Write access. DM is sampled on both edges of DQS. Although DM pins are input only, the DM loading matches the DQ and DQS loading. CLK, CLK Differential Clock Inputs CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLK and negative edge of CLK and CLK (both directions of crossing). K2 CKE Clock Enable CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. J2 VREF Reference Voltage VREF is reference voltage for inputs. A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	L8	cs	Chip Select	All commands are masked when \overline{CS} is registered HIGH. \overline{CS} provides for external rank selection on systems with multiple ranks.
B3,F3 UDM, LDM Input Data Mask DM is sampled high coincident with that input data during a Write access. DM is sampled on both edges of DQS. Although DM pins are input only, the DM loading matches the DQ and DQS loading. CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLF and negative edge of CLF. Output (read) data is referenced to the crossings of CLK and CLF. (both directions of crossing). K2 CKE Clock Enable CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. J2 VREF Reference Voltage VREF is reference voltage for inputs. A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS Ground DQ Power Supply: 1.8V ± 0.1V. DQ Ground. Isolated on the device for improved noise immunity. A2,E2,R3,R7,R8 NC No Connection No connection. DLL Ground.	K7,L7,K3		Command Inputs	$\overline{\rm RAS}$, $\overline{\rm CAS}$ and $\overline{\rm WE}$ (along with $\overline{\rm CS}$) define the command being
J8,K8 CLK, CLK Differential Clock Inputs input signals are sampled on the crossing of the positive edge of CLK and negative edge of CLK. Output (read) data is referenced to the crossings of CLK and CLK (both directions of crossing). K2 CKE Clock Enable CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. J2 VREF Reference Voltage VREF is reference voltage for inputs. A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS Ground Ground. A9,C1,C3,C7,C9,E9, G1,G3,G7,G9 VDDQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	B3,F3	UDM, LDM	Input Data Mask	DM is an input mask signal for write data. Input data is masked when DM is sampled high coincident with that input data during a Write access. DM is sampled on both edges of DQS. Although DM pins are input only, the DM loading matches the DQ and DQS loading.
CKE Clock Enable CKE (registered HIGH) activates and CKE (registered LOW deactivates clocking circuitry on the DDR2 SDRAM. J2 VREF Reference Voltage VREF is reference voltage for inputs. A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS Ground Ground. A9,C1,C3,C7,C9,E9, G1,G3,G7,G9 VDDQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	J8,K8	CLK, CLK		CLK and CLK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CLK and negative edge of CLK. Output (read) data is referenced to the crossings of CLK and CLK (both directions of crossing).
A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS Ground Ground. A9,C1,C3,C7,C9,E9, G1,G3,G7,G9 VDDQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	K2	CKE	Clock Enable	CKE (registered HIGH) activates and CKE (registered LOW) deactivates clocking circuitry on the DDR2 SDRAM.
A1,E1,J9,M9,R1 VDD Power Supply Power Supply: 1.8V ± 0.1V. A3,E3,J3,N1,P9 VSS Ground Ground. A9,C1,C3,C7,C9,E9, G1,G3,G7,G9 VDDQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7, F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	J2	VREF	Reference Voltage	VREF is reference voltage for inputs.
A3,E3,J3,N1,P9 VSS Ground Ground. A9,C1,C3,C7,C9,E9,G1,G3,G7,G9 VDDQ DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7,F2,F8,H2,H8 NC No Connection No connection. J7 VSSDL DLL Ground DLL Ground.	A1,E1,J9,M9,R1	VDD	9	
A9,C1,C3,C7,C9,E9,G1,G3,G7,G9 DQ Power Supply DQ Power Supply: 1.8V ± 0.1V. A7,B2,B8,D2,D8,E7,F2,F8,H2,H8 DQ Ground DQ Ground. Isolated on the device for improved noise immunity. A2,E2,R3,R7,R8 NC No Connection No connection. DLL Ground.			,	,
A7,B2,B8,D2,D8,E7, F2,F8,H2,H8	A9,C1,C3,C7,C9,E9,			
J7 VSSDL DLL Ground DLL Ground.		Vssq	DQ Ground	DQ Ground. Isolated on the device for improved noise immunity.
	A2,E2,R3,R7,R8	NC	No Connection	No connection.
J1 VDDL DLL Power Supply DLL Power Supply: 1.8V ± 0.1V.	J7	VSSDL	DLL Ground	DLL Ground.
·	J1	VDDL	DLL Power Supply	DLL Power Supply: 1.8V ± 0.1V.

Publication Release Date: Dec. 02, 2020 Revision: A02



7. BLOCK DIAGRAM





8. FUNCTIONAL DESCRIPTION

8.1 Power-up and Initialization Sequence

DDR2 SDRAMs must be powered up and initialized in a predefined manner. Operational procedures other than those specified may result in undefined operation. The following sequence is required for Power-up and Initialization.

- 1. Apply power and attempt to maintain CKE below 0.2 × VDDQ and ODT^{*1} at a LOW state (all other inputs may be undefined.) Either one of the following sequence is required for Power-up.
 - A. The VDD voltage ramp time must be no greater than 200 mS from when VDD ramps from 300 mV to VDD min; and during the VDD voltage ramp, |VDD -VDDQ| ≤ 0.3 volts.
 - VDD, VDDL and VDDQ are driven from a single power converter output
 - VTT is limited to 0.95V max
 - VREF*2 tracks VDDQ/2
 - VDDQ ≥ VREF must be met at all times
 - B. Voltage levels at I/Os and outputs must be less than VDDQ during voltage ramp time to avoid DRAM latch-up. During the ramping of the supply voltages, VDD ≥ VDDL ≥ VDDQ must be maintained and is applicable to both AC and DC levels until the ramping of the supply voltages is complete.
 - Apply VDD/VDDL*3 before or at the same time as VDDQ
 - Apply VDDQ*4 before or at the same time as VTT
 - VREF^{*2} tracks VDDQ/2
 - VDDQ ≥ VREF must be met at all times.
 - Apply VTT
 - The VTT voltage ramp time from when VDDQ min is achieved on VDDQ to when VTT min is achieved on VTT must be no greater than 500 mS
- 2. Start Clock and maintain stable condition for 200 µS (min.).
- 3. After stable power and clock (CLK, CLK), apply NOP or Deselect and take CKE HIGH.
- 4. Wait minimum of 400 nS then issue precharge all command. NOP or Deselect applied during 400 nS period.
- 5. Issue an EMRS command to EMR (2). (To issue EMRS command to EMR (2), provide LOW to BA0, HIGH to BA1, LOW to BA2.)
- 6. Issue an EMRS command to EMR (3). (To issue EMRS command to EMR (3), provide HIGH to BA0 and BA1, LOW to BA2.)
- 7. Issue an EMRS command to EMR (1) to enable DLL. (To issue DLL Enable command, provide LOW to A0, HIGH to BA0 and LOW to BA1, LOW to BA2. And A9=A8=A7=LOW must be used when issuing this command.)
- 8. Issue a Mode Register Set command for DLL reset. (To issue DLL Reset command, provide HIGH to A8 and LOW to BA0 and BA1 and BA2.)
- 9. Issue a precharge all command.
- 10. Issue 2 or more Auto Refresh commands.
- 11. Issue a MRS command with LOW to A8 to initialize device operation. (i.e. to program operating parameters without resetting the DLL.)
- 12. At least 200 clocks after step 8, execute OCD Calibration (Off Chip Driver impedance adjustment). If OCD calibration is not used, EMRS to EMR (1) to set OCD Calibration Default (A9=A8=A7=HIGH) followed by EMRS to EMR (1) to exit OCD Calibration Mode (A9=A8=A7=LOW) must be issued with other operating parameters of EMR (1).
- 13. The DDR2 SDRAM is now ready for normal operation.

Publication Release Date: Dec. 02, 2020



Notes:

- 1. To guarantee ODT off, VREF must be valid and a LOW level must be applied to the ODT pin.
- 2. VREF must be within ± 300 mV with respect to VDDQ/2 during supply ramp time.
- 3. VDD/VDDL voltage ramp time must be no greater than 200 mS from when VDD ramps from 300 mV to VDD min.
- 4. The VDDQ voltage ramp time from when VDD min is achieved on VDD to when VDDQ min is achieved on VDDQ must be no greater than 500 mS.




Figure 1 – Initialization sequence after power-up

8.2 Mode Register and Extended Mode Registers Operation

For application flexibility, burst length, burst type, CAS Latency, DLL reset function, write recovery time (WR) are user defined variables and must be programmed with a Mode Register Set (MRS) command. Additionally, DLL disable function, driver impedance, additive CAS Latency, ODT (On Die Termination), single-ended strobe and OCD (off chip driver impedance adjustment) are also user defined variables and must be programmed with an Extended Mode Register Set (EMRS) command. Contents of the Mode Register (MR) or Extended Mode Registers EMR (1), EMR (2) and EMR (3) can be altered by reexecuting the MRS or EMRS Commands. Even if the user chooses to modify only a subset of the MR or EMR (1), EMR (2) and EMR (3) variables, all variables within the addressed register must be redefined when the MRS or EMRS commands are issued.

MRS, EMRS and Reset DLL do not affect array contents, which mean re-initialization including those can be executed at any time after power-up without affecting array contents.

8.2.1 Mode Register Set Command (MRS)

$$(\overline{CS} = "L", \overline{RAS} = "L", \overline{CAS} = "L", \overline{WE} = "L", BA0 = "L", BA1 = "L", BA2 = "L", A0 to A12 = Register Data)$$


The mode register stores the data for controlling the various operating modes of DDR2 SDRAM. It programs CAS Latency, burst length, burst sequence, test mode, DLL reset, Write Recovery (WR) and various vendor specific options to make DDR2 SDRAM useful for various applications. The default value in the Mode Register after power-up is not defined; therefore the Mode Register must be programmed during initialization for proper operation.

The DDR2 SDRAM should be in all bank precharge state with CKE already HIGH prior to writing into the mode register. The mode register set command cycle time (tMRD) is required to complete the write operation to the mode register. The mode register contents can be changed using the same command and clock cycle requirements during normal operation as long as all banks are in the precharge state.

Publication Release Date: Dec. 02, 2020

s winbond

The mode register is divided into various fields depending on functionality. Burst length is defined by A[2:0] with options of 4 and 8 bit burst lengths. The burst length decodes are compatible with DDR SDRAM. Burst address sequence type is defined by A3, CAS Latency is defined by A[6:4]. The DDR2 does not support half clock latency mode. A7 is used for test mode. A8 is used for DLL reset. A7 must be set to LOW for normal MRS operation. Write recovery time WR is defined by A[11:9]. Refer to the table for specific codes.



Note:

1. WR (write recovery for Auto-precharge) min is determined by tCK(avg) max and WR max is determined by tCK(avg) min. WR[cycles] = RU{ tWR[nS] / tCK(avg)[nS] }, where RU stands for round up. The mode register must be programmed to this value. This is also used with tRP to determine tDAL.

Figure 2 – Mode Register Set (MRS)

8.2.2 Extend Mode Register Set Commands (EMRS)

8.2.2.1 Extend Mode Register Set Command (1), EMR (1)

$$(\overline{CS} = "L", \overline{RAS} = "L", \overline{CAS} = "L", \overline{WE} = "L", BA0 = "H", BA1 = "L, BA2 = "L" A0 to A12 = Register data)$$


The extended mode register (1) stores the data for enabling or disabling the DLL, output driver strength, additive latency, ODT, \overline{DQS} disable, OCD program. The default value of the extended mode register (1) is not defined; therefore the extended mode register (1) must be programmed during initialization for proper operation. The DDR2 SDRAM should be in all bank precharge with CKE already high prior to writing into the extended mode register (1). The mode register set command cycle time (tMRD) must be satisfied to complete the write operation to the extended mode register (1). Extended mode register (1) contents can be changed using the same command and clock cycle requirements during normal operation as long as all banks are in the precharge state. A0 is used for DLL enable or disable. A1 is used for enabling a reduced strength output driver. A[5:3] determines the additive latency, A[9:7] are used for OCD control, A10 is used for \overline{DQS} disable. A2 and A6 are used for ODT setting.

Publication Release Date: Dec. 02, 2020



8.2.2.2 DLL Enable/Disable

The DLL must be enabled for normal operation. DLL enable is required during power-up initialization, and upon returning to normal operation after having the DLL disabled. The DLL is automatically disabled when entering Self Refresh operation and is automatically re-enabled and reset upon exit of Self Refresh operation. Any time the DLL is enabled (and subsequently reset), 200 clock cycles must occur before a Read command can be issued to allow time for the internal clock to be synchronized with the external clock. Failing to wait for synchronization to occur may result in a violation of the tAC or tDQSCK parameters.



Notes:

- 1. A11 default is "0" RDQS disabled.
- 2. Optional for DDR2-667, mandatory for DDR2-800 and DDR2-1066.
- 3. When Adjust mode is issued, AL from previously set value must be applied.
- 4. After setting to default, OCD calibration mode needs to be exited by setting A9-A7 to 000. Refer to the section 8.2.3 for detailed information.
- 5. Output disabled DQs, LDQS, LDQS, UDQS, UDQS. This feature is used in conjunction with DIMM IDD measurements when IDDQ is not desired to be included.

Figure 3 - EMR (1)

Publication Release Date: Dec. 02, 2020




8.2.2.3 Extend Mode Register Set Command (2), EMR (2)

$$(\overline{CS} = "L", \overline{RAS} = "L", \overline{CAS} = "L", \overline{WE} = "L", BA0 = "L", BA1 = "H", BA2 = "L" A0 to A12 = Register data)$$

The extended mode register (2) controls refresh related features. The default value of the extended mode register (2) is not defined; therefore the extended mode register (2) must be programmed during initialization for proper operation.

The DDR2 SDRAM should be in all bank precharge state with CKE already high prior to writing into the extended mode register (2). The mode register set command cycle time (tMRD) must be satisfied to complete the write operation to the extended mode register (2). Mode register contents can be changed using the same command and clock cycle requirements during normal operation as long as all banks are in the precharge state.



Notes:

- 1. The rest bits in EMR (2) is reserved for future use and all bits in EMR (2) except A7, BA0, BA1 and BA2 must be programmed to "0" when setting the extended mode register (2) during initialization.
- 2. When DRAM is operated at 85°C < TCASE ≤ 95°C or 105°C the extended Self Refresh rate must be enabled by setting bit A7 to "1" before the Self Refresh mode can be entered.

Figure 4 – EMR (2)


Publication Release Date: Dec. 02, 2020



8.2.2.4 Extend Mode Register Set Command (3), EMR (3)

$$(\overline{CS} = "L", \overline{RAS} = "L", \overline{CAS} = "L", \overline{WE} = "L", BA0 = "H", BA1 = "H", BA2 = "L", A0 to A12 = Register data)$$

No function is defined in extended mode register (3). The default value of the EMR (3) is not defined; therefore the EMR (3) must be programmed during initialization for proper operation.



Note:

1. All bits in EMR (3) except BA0 and BA1 are reserved for future use and must be set to "0" when programming the EMR (3).

Figure 5 – EMR (3)

Publication Release Date: Dec. 02, 2020



8.2.3 Off-Chip Driver (OCD) Impedance Adjustment

DDR2 SDRAM supports driver calibration feature and the flow chart in Figure 6 is an example of the sequence. Every calibration mode command should be followed by "OCD calibration mode exit" before any other command being issued. MRS should be set before entering OCD impedance adjustment and On Die Termination (ODT) should be carefully controlled depending on system environment.




Figure 6 - OCD Impedance Adjustment Flow Chart

Publication Release Date: Dec. 02, 2020



8.2.3.1 Extended Mode Register for OCD Impedance Adjustment

OCD impedance adjustment can be done using the following EMRS mode. In drive mode all outputs are driven out by DDR2 SDRAM. In Drive (1) mode, all DQ, DQS signals are driven HIGH and all $\overline{\rm DQS}$ signals are driven LOW. In Drive (0) mode, all DQ, DQS signals are driven LOW and all $\overline{\rm DQS}$ signals are driven HIGH. In adjust mode, BL = 4 of operation code data must be used. In case of OCD calibration default, output driver characteristics have a nominal impedance value of 18 Ohms during nominal temperature and voltage conditions. OCD applies only to normal full strength output drive setting defined by EMR (1) and if reduced strength is set, OCD default driver characteristics are not applicable. When OCD calibration adjust mode is used, OCD default output driver characteristics are not applicable. After OCD calibration is completed or driver strength is set to default, subsequent EMRS commands not intended to adjust OCD characteristics must specify A[9:7] as '000' in order to maintain the default or calibrated value.

A9	A8	A7	Operation
0	0	0	OCD calibration mode exit
0	0	1	Drive (1) DQ, DQS HIGH and DQS LOW
0	1	0	Drive (0) DQ, DQS LOW and DQS HIGH
1	0	0	Adjust mode
1	1	1	OCD calibration default

Table 1 – OCD Drive Mode Program

8.2.3.2 OCD Impedance Adjust

To adjust output driver impedance, controllers must issue the ADJUST EMRS command along with a 4 bit burst code to DDR2 SDRAM as in table 2. For this operation, Burst Length has to be set to BL = 4 via MRS command before activating OCD and controllers must drive the burst code to all DQs at the same time. DTo in table 2 means all DQ bits at bit time 0, DT1 at bit time 1, and so forth. The driver output impedance is adjusted for all DDR2 SDRAM DQs simultaneously and after OCD calibration, all DQs and DQS's of a given DDR2 SDRAM will be adjusted to the same driver strength setting. The maximum step count for adjustment is 16 and when the limit is reached, further increment or decrement code has no effect. The default setting may be any step within the 16 step range. When Adjust mode command is issued, AL from previously set value must be applied.

				Adjust mode i rogram		
4 bit	ourst code	inputs to a	all DQs	Operation		
D то	DT1	DT2	D тз	Pull-up driver strength	Pull-down driver strength	
0	0	0	0	NOP (No operation)	NOP (No operation)	
0	0	0	1	Increase by 1 step	NOP	
0	0	1	0	Decrease by 1 step	NOP	
0	1	0	0	NOP	Increase by 1 step	
1	0	0	0	NOP	Decrease by 1 step	
0	1	0	1	Increase by 1 step	Increase by 1 step	
0	1	1	0	Decrease by 1 step	Increase by 1 step	
1	1 0 0 1		1	Increase by 1 step	Decrease by 1 step	
1	0	1	0	Decrease by 1 step	Decrease by 1 step	
	Other Co	mbinations		Res	served	

Table 2 – OCD Adjust Mode Program

Publication Release Date: Dec. 02, 2020



For proper operation of adjust mode, WL = RL - 1 = AL + CL - 1 clocks and tDS/tDH should be met as shown in Figure 7. For input data pattern for adjustment, DT0 - DT3 is a fixed order and is not affected by burst type (i.e., sequential or interleave).




Figure 7 - OCD Adjust Mode

8.2.3.3 Drive Mode

Drive mode, both Drive (1) and Drive (0), is used for controllers to measure DDR2 SDRAM Driver impedance. In this mode, all outputs are driven out tolt after "enter drive mode" command and all output drivers are turned-off tolt after "OCD calibration mode exit" command as shown in Figure 8.




Figure 8 - OCD Drive Mode


Publication Release Date: Dec. 02, 2020



8.2.4 On-Die Termination (ODT)

On-Die Termination (ODT) is a new feature on DDR2 components that allows a DRAM to turn on/off termination resistance for each DQ, UDQS/ $\overline{\text{UDQS}}$, LDQS/ $\overline{\text{LDQS}}$, UDM and LDM signal via the ODT control pin. $\overline{\text{UDQS}}$ and $\overline{\text{LDQS}}$ are terminated only when enabled in the EMR (1) by address bit A10 = 0. The ODT feature is designed to improve signal integrity of the memory channel by allowing the DRAM controller to independently turn on/off termination resistance for any or all DRAM devices.

The ODT function can be used for all active and standby modes. ODT is turned off and not supported in Self Refresh mode. (Example timing waveforms refer to 11.2, 11.3 ODT Timing for Active/Standby/Power Down Mode and 11.4, 11.5 ODT timing mode switch at entering/exiting power down mode diagram in Chapter 11)



Switch (sw1, sw2, sw3) is enabled by ODT pin.

Selection among sw1, sw2, and sw3 is determined by "Rtt (nominal)" in EMR (1).

Termination included on all DQs, DM, DQS, DQS pins.

Figure 9 - Functional Representation of ODT


8.2.5 ODT related timings

8.2.5.1 MRS command to ODT update delay

During normal operation the value of the effective termination resistance can be changed with an EMRS command. The update of the Rtt setting is done between tMOD,min and tMOD,max, and CKE must remain HIGH for the entire duration of tMOD window for proper operation. The timings are shown in the following timing diagram.

Publication Release Date: Dec. 02, 2020

was winbond



However, to prevent any impedance glitch on the channel, the following conditions must be met.

- tAOFD must be met before issuing the EMRS command.
- ODT must remain LOW for the entire duration of tMOD window, until tMOD,max is met.

Now the ODT is ready for normal operation with the new setting, and the ODT signal may be raised again to turned on the ODT. Following timing diagram shows the proper Rtt update procedure.

Figure 10 - ODT update delay timing - tMOD




Figure 11 - ODT update delay timing - tMOD, as measured from outside

Publication Release Date: Dec. 02, 2020



8.3 Command Function

8.3.1 Bank Activate Command

(\overline{CS} ="L", \overline{RAS} ="L", \overline{CAS} ="H", \overline{WE} ="H", BA0, BA1, BA2=Bank, A0 to A12 be row address)

The Bank Activate command must be applied before any Read or Write operation can be executed. Immediately after the bank active command, the DDR2 SDRAM can accept a read or write command on the following clock cycle. If a Read/Write command is issued to a bank that has not satisfied the tRCDmin specification, then additive latency must be programmed into the device to delay when the Read/Write command is internally issued to the device. The additive latency value must be chosen to assure tRCDmin is satisfied. Additive latencies of 0, 1, 2, 3, 4, 5 and 6 are supported. Once a bank has been activated it must be precharged before another Bank Activate command can be applied to the same bank. The bank active and precharge times are defined as tRAS and tRP, respectively. The minimum time interval between successive Bank Activate commands to the same bank is determined by the RAS cycle time of the device (tRC). The minimum time interval between Bank Activate commands is tRRD.

In order to ensure that components with 8 internal memory banks do not exceed the instantaneous current supplying capability, certain restrictions on operation of the 8 banks must be observed. There are two rules. One for restricting the number of sequential ACT commands that can be issued and another for allowing more time for RAS precharge for a Precharge All command. The rules are as follows:

- Sequential Bank Activation Restriction: No more than 4 banks may be activated in a rolling tFAW window. Converting to clocks is done by dividing tFAW[nS] by tCK(avg)[ns], and rounding up to next integer value. As an example of the rolling window, if RU{ (tFAW / tCK(avg) } is 10 clocks, and an activate command is issued in clock N, no more than three further activate commands may be issued at or between clock N+1 and N+9.
- Precharge All Allowance: tRP for a Precharge All command is equal to tnRP + 1 x nCK, where tnRP
 = RU{ tRP / tCK(avg) } and tRP is the value for a single bank precharge.




Figure 12 - Bank activate command cycle: tRCD = 3, AL = 2, tRP = 3, tRRD = 2, tCCD = 2

Publication Release Date: Dec. 02, 2020



8.3.2 Read Command

($\overline{\text{CS}}$ ="L", $\overline{\text{RAS}}$ ="H", $\overline{\text{CAS}}$ ="L", $\overline{\text{WE}}$ ="H", BA0, BA1, BA2=Bank, A10="L", A0 to A9=Column Address)

The READ command is used to initiate a burst read access to an active row. The value on BA0, BA1, BA2 inputs selects the bank, and the A0 to A9 address inputs determine the starting column address. The address input A10 determines whether or not Auto-precharge is used. If Auto-precharge is selected, the row being accessed will be precharged at the end of the READ burst; if Auto-precharge is not selected, the row will remain open for subsequent accesses.

8.3.3 Write Command

($\overline{\text{CS}}$ ="L", $\overline{\text{RAS}}$ ="H", $\overline{\text{CAS}}$ ="L", $\overline{\text{WE}}$ ="L", BA0, BA1, BA2=Bank, A10="L", A0 to A9=Column Address)

The WRITE command is used to initiate a burst write access to an active row. The value on BA0, BA1, BA2 inputs selects the bank, and the A0 to A9 address inputs determine the starting column address. The address input A10 determines whether or not Auto-precharge is used. If Auto-precharge is selected, the row being accessed will be precharged at the end of the WRITE burst; if Auto-precharge is not selected, the row will remain open for subsequent accesses.

8.3.4 Burst Read with Auto-precharge Command

(\overline{CS} ="L", \overline{RAS} ="H", \overline{CAS} ="L", \overline{WE} ="H", BA0, BA1, BA2=Bank, A10="H", A0 to A9=Column Address)

If A10 is HIGH when a Read Command is issued, the Read with Auto-precharge function is engaged. The DDR2 SDRAM starts an Auto-precharge operation on the rising edge which is (AL + BL/2) cycles later than the read with AP command if transfer and transfer in the read with AP command if transfer in the read with AP command in in t

8.3.5 Burst Write with Auto-precharge Command

(CS="L", RAS="H", CAS="L", WE="L", BA0, BA1, BA2=Bank, A10="H", A0 to A9=Column Address)

If A10 is HIGH when a Write Command is issued, the Write with Auto-precharge function is engaged. The DDR2 SDRAM automatically begins precharge operation after the completion of the burst write plus write recovery time (WR) programmed in the mode register.

8.3.6 Precharge All Command

(CS="L", RAS="L", CAS="H", WE ="L", BA0, BA1, BA2=Don't Care, A10="H", A0 to A9 and A11 to A12=Don't Care)

The Precharge All command precharge all banks simultaneously. Then all banks are switched to the idle state.

8.3.7 Self Refresh Entry Command

($\overline{\text{CS}}$ ="L", $\overline{\text{RAS}}$ ="L", $\overline{\text{CAS}}$ ="L", $\overline{\text{WE}}$ ="H", CKE="L", BA0, BA1, BA2, A0 to A12=Don't Care)

The Self Refresh command can be used to retain data, even if the rest of the system is powered down. When in the Self Refresh mode, the DDR2 SDRAM retains data without external clocking. The DDR2 SDRAM device has a built-in timer to accommodate Self Refresh operation. ODT must be turned off before issuing Self Refresh command, by either driving ODT pin LOW or using an EMRS command. Once the command is registered, CKE must be held LOW to keep the device in Self Refresh mode. The DLL is automatically disabled upon entering Self Refresh and is automatically enabled upon exiting Self Refresh. When the DDR2 SDRAM has entered Self Refresh mode, all of the external signals except CKE, are "Don't Care".

The clock is internally disabled during self refresh operation to save power. The user may change the external clock frequency or halt the external clock one clock after Self Refresh entry is registered; however, the clock must be restarted and stable before the device can exit self refresh operation.

Publication Release Date: Dec. 02, 2020



8.3.8 Self Refresh Exit Command

(CKE="H", \overline{CS} ="H" or CKE="H", \overline{CS} ="L", \overline{RAS} ="H", \overline{CAS} ="H", \overline{WE} ="H", BA0, BA1, BA2, A0 to A12=Don't Care)

The procedure for exiting Self Refresh requires a sequence of commands. First, the clock must be stable prior to CKE going back HIGH. Once Self Refresh Exit is registered, a delay of at least tXSNR must be satisfied before a valid command can be issued to the device to allow for any internal refresh in progress. CKE must remain HIGH for the entire Self Refresh exit period tXSRD for proper operation except for self refresh re-entry.

Upon exit from Self Refresh, the DDR2 SDRAM can be put back into Self Refresh mode after waiting at least txsnr period and issuing one refresh command (refresh period of trech). NOP or Deselect commands must be registered on each positive clock edge during the Self Refresh exit interval txsnr. ODT should be turned off during txsrd.

The use of Self Refresh mode introduces the possibility that an internally timed refresh event can be missed when CKE is raised for exit from Self Refresh mode. Upon exit from Self Refresh, the DDR2 SDRAM requires a minimum of one extra auto refresh command before it is put back into Self Refresh mode.

8.3.9 Refresh Command

(CS="L", RAS="L", CAS="L", WE="H", CKE="H", BA0, BA1, BA2, A0 to A12=Don't Care)

Refresh is used during normal operation of the DDR2 SDRAM. This command is non persistent, so it must be issued each time a refresh is required.

The refresh addressing is generated by the internal refresh controller. This makes the address bits "Don't Care" during an Auto Refresh command. The DDR2 SDRAM requires Auto Refresh cycles at an average periodic interval of tREFI (max.).

When the refresh cycle has completed, all banks of the DDR2 SDRAM will be in the precharged (idle) state. A delay between the auto refresh command (REF) and the next activate command or subsequent auto refresh command must be greater than or equal to the auto refresh cycle time (tRFC).

To allow for improved efficiency in scheduling and switching between tasks, some flexibility in the absolute refresh interval is provided. A maximum of eight Refresh commands can be posted to any given DDR2 SDRAM, meaning that the maximum absolute interval between any Refresh command and the next Refresh command is 9 x treft.




Figure 13 - Refresh command

Publication Release Date: Dec. 02, 2020



8.3.10 No-Operation Command

 $(\overline{CS} = "L", \overline{RAS} = "H", \overline{CAS} = "H", \overline{WE} = "H", CKE, BAO, BA1, BA2, A0 to A12 = Don't Care)$

The No-Operation command simply performs no operation (same command as Device Deselect).

8.3.11 Device Deselect Command

 $(\overline{CS} = "H", \overline{RAS}, \overline{CAS}, \overline{WE}, CKE, BAO, BA1, BA2, A0 to A12 = Don't Care)$

The Device Deselect command disables the command decoder so that the \overline{RAS} , \overline{CAS} , \overline{WE} and Address inputs are ignored. This command is similar to the No-Operation command.

8.4 Read and Write access modes

The DDR2 SDRAM provides a fast column access operation. A single Read or Write Command will initiate a serial read or write operation on successive clock cycles. The boundary of the burst cycle is strictly restricted to specific segments of the page length.

The 8 Mbit x 16 I/O x 8 Bank chip has a page length of 1024 bits (defined by CA0 to CA9)*. The page length of 1024 is divided into 256 or 128 uniquely addressable boundary segments depending on burst length, 256 for 4 bit burst, 128 for 8 bit burst respectively. A 4-bit or 8-bit burst operation will occur entirely within one of the 256 or 128 groups beginning with the column address supplied to the device during the Read or Write Command (CA0 to CA9). The second, third and fourth access will also occur within this group segment. However, the burst order is a function of the starting address, and the burst sequence.

A new burst access must not interrupt the previous 4 bit burst operation in case of BL = 4 setting. However, in case of BL = 8 setting, two cases of interrupt by a new burst access are allowed, one reads interrupted by a read, the other writes interrupted by a write with 4 bit burst boundary respectively. The minimum \overline{CAS} to \overline{CAS} delay is defined by tCCD, and is a minimum of 2 clocks for read or write cycles.

Note: Page length is a function of I/O organization and column addressing 8M bits × 16 organization (CA0 to CA9); Page Length = 1024 bits

8.4.1 Posted CAS


Posted \overline{CAS} operation is supported to make command and data bus efficient for sustainable bandwidths in DDR2 SDRAM. In this operation, the DDR2 SDRAM allows a \overline{CAS} read or write command to be issued immediately after the \overline{RAS} bank activate command (or any time during the \overline{RAS} - \overline{CAS} -delay time, tRCD, period). The command is held for the time of the Additive Latency (AL) before it is issued inside the device. The Read Latency (RL) is controlled by the sum of AL and the CAS Latency (CL). Therefore if a user chooses to issue a Read/Write command before the tRCDmin, then AL (greater than 0) must be written into the EMR (1). The Write Latency (WL) is always defined as RL -1 (Read Latency -1) where Read Latency is defined as the sum of Additive Latency plus CAS Latency (RL = AL + CL). Read or Write operations using AL allow seamless bursts. (Example timing waveforms refer to 11.10 and 11.11 seamless burst read/write operation diagram in Chapter 11)

8.4.1.1 Examples of posted CAS operation

Examples of a read followed by a write to the same bank where AL = 2 and where AL = 0 are shown in Figures 14 and 15, respectively.


Publication Release Date: Dec. 02, 2020

reservinbond se



[AL = 2 and CL = 3, RL = (AL + CL) = 5, WL = (RL - 1) = 4, BL = 4]

Figure 14 – Example 1: Read followed by a write to the same bank, where AL = 2 and CL = 3, RL = (AL + CL) = 5, WL = (RL - 1) = 4, BL = 4



AL = 0 and CL = 3, RL = (AL + CL) = 3, WL = (RL - 1) = 2, BL = 4]

Figure 15 – Example 2: Read followed by a write to the same bank, where AL = 0 and CL = 3, RL = (AL + CL) = 3, WL = (RL - 1) = 2, BL = 4

8.4.2 Burst mode operation

Burst mode operation is used to provide a constant flow of data to memory locations (write cycle), or from memory locations (read cycle). The parameters that define how the burst mode will operate are burst sequence and burst length. The DDR2 SDRAM supports 4 bit and 8 bit burst modes only. For 8 bit burst mode, full interleave address ordering is supported, however, sequential address ordering is nibble based for ease of implementation. The burst length is programmable and defined by MR A[2:0]. The burst type, either sequential or interleaved, is programmable and defined by MR [A3]. Seamless burst read or write operations are supported.

Publication Release Date: Dec. 02, 2020



Unlike DDR1 devices, interruption of a burst read or writes cycle during BL = 4 mode operation is prohibited. However in case of BL = 8 mode, interruption of a burst read or write operation is limited to two cases, reads interrupted by a read, or writes interrupted by a write. (Example timing waveforms refer to 11.12 and 11.13 Burst read and write interrupt timing diagram in Chapter 11)

Therefore the Burst Stop command is not supported on DDR2 SDRAM devices.

Table 3 – Burst Length and Sequence

Burst Length	Starting Address (A2 A1 A0)	Sequential Addressing (decimal)	Interleave Addressing (decimal)
	x00	0, 1, 2, 3	0, 1, 2, 3
4	x01	1, 2, 3, 0	1, 0, 3, 2
4	x10	2, 3, 0, 1	2, 3, 0, 1
	x11	3, 0, 1, 2	3, 2, 1, 0
	000	0, 1, 2, 3, 4, 5, 6, 7	0, 1, 2, 3, 4, 5, 6, 7
	001	1, 2, 3, 0, 5, 6, 7, 4	1, 0, 3, 2, 5, 4, 7, 6
	010	2, 3, 0, 1, 6, 7, 4, 5	2, 3, 0, 1, 6, 7, 4, 5
8	011	3, 0, 1, 2, 7, 4, 5, 6	3, 2, 1, 0, 7, 6, 5, 4
0	100	4, 5, 6, 7, 0, 1, 2, 3	4, 5, 6, 7, 0, 1, 2, 3
	101	5, 6, 7, 4, 1, 2, 3, 0	5, 4, 7, 6, 1, 0, 3, 2
	110	6, 7, 4, 5, 2, 3, 0, 1	6, 7, 4, 5, 2, 3, 0, 1
	111	7, 4, 5, 6, 3, 0, 1, 2	7, 6, 5, 4, 3, 2, 1, 0

8.4.3 Burst read mode operation

Burst Read is initiated with a READ command. The address inputs determine the starting column address for the burst. The delay from the start of the command to when the data from the first cell appears on the outputs is equal to the value of the read latency (RL). The data strobe output (DQS) is driven LOW one clock cycle before valid data (DQ) is driven onto the data bus. The first bit of the burst is synchronized with the rising edge of the data strobe (DQS). Each subsequent data-out appears on the DQ pin in phase with the DQS signal in a source synchronous manner. The RL is equal to an additive latency (AL) plus CAS Latency (CL). The CL is defined by the Mode Register Set (MRS). The AL is defined by the Extended Mode Register EMR (1). (Example timing waveforms refer to 11.6 and 11.7 Data output (read) timing and Burst read operation diagram in Chapter 11)

8.4.4 Burst write mode operation

Burst Write is initiated with a WRITE command. The address inputs determine the starting column address for the burst. Write Latency (WL) is defined by a Read Latency (RL) minus one and is equal to (AL + CL -1); and is the number of clocks of delay that are required from the time the write command is registered to the clock edge associated to the first DQS strobe. A data strobe signal (DQS) should be driven LOW (preamble) nominally half clock prior to the WL. The first data bit of the burst cycle must be applied to the DQ pins at the first rising edge of the DQS following the preamble. The tDQSS specification must be satisfied for each positive DQS transition to its associated clock edge during write cycles. The subsequent burst bit data are issued on successive edges of the DQS until the burst length is completed, which is 4 or 8 bit burst. When the burst has finished, any additional data supplied to the DQ pins will be ignored. The DQ Signal is ignored after the burst write operation is complete. The time from the completion of the burst write to bank precharge is the write recovery time (WR). (Example timing waveforms refer to 11.8 and 11.9 Data input (write) timing and Burst write operation diagram in Chapter 11)

Publication Release Date: Dec. 02, 2020



8.4.5 Write data mask

One write data mask (DM) pin for each 8 data bits (DQ) will be supported on DDR2 SDRAM, consistent with the implementation on DDR1 SDRAM. It has identical timings on write operations as the data bits, and though used in a unidirectional manner, is internally loaded identically to data bits to insure matched system timing. DM is not used during read cycles. (Example timing waveform refer to 11.14 Write operation with Data Mask diagram in Chapter 11)

8.5 Burst Interrupt

Read or Write burst interruption is prohibited for burst length of 4 and only allowed for burst length of 8 under the following conditions:

- 1. Read burst of 8 can only be interrupted by another Read command. Read burst interruption by Write or Precharge Command is prohibited.
- 2. Write burst of 8 can only be interrupted by another Write command. Write burst interruption by Read or Precharge Command is prohibited.
- 3. Read burst interrupt must occur exactly two clocks after the previous Read command. Any other Read burst interrupt timings are prohibited.
- 4. Write burst interrupt must occur exactly two clocks after the previous Write command. Any other Write burst interrupt timings are prohibited.
- 5. Read or Write burst interruption is allowed to any bank inside the DDR2 SDRAM.
- 6. Read or Write burst with Auto-precharge enabled is not allowed to interrupt.
- 7. Read burst interruption is allowed by a Read with Auto-precharge command.
- 8. Write burst interruption is allowed by a Write with Auto-precharge command.
- 9. All command timings are referenced to burst length set in the mode register. They are not referenced to the actual burst. For example below:
 - Minimum Read to Precharge timing is AL + BL/2 where BL is the burst length set in the mode register and not the actual burst (which is shorter because of interrupt).
 - Minimum Write to Precharge timing is WL + BL/2 + tWR, where tWR starts with the rising clock after the un-interrupted burst end and not from the end of the actual burst end.

(Example timing waveforms refer to 11.12 and 11.13 Burst read and write interrupt timing diagram in Chapter 11)

Publication Release Date: Dec. 02, 2020



8.6 Precharge operation

The Precharge Command is used to precharge or close a bank that has been activated. The Precharge Command can be used to precharge each bank independently or all banks simultaneously. Three address bits A10, BA0 and BA1 and BA2 are used to define which bank to precharge when the command is issued.

A10	BA2	BA1	BA0	Precharge Bank(s)
LOW	LOW	LOW	LOW	Bank 0 only
LOW	LOW	LOW	HIGH	Bank 1 only
LOW	LOW	HIGH	LOW	Bank 2 only
LOW	LOW	HIGH	HIGH	Bank 3 only
LOW	HIGH	LOW	LOW	Bank 4 only
LOW	HIGH	LOW	HIGH	Bank 5 only
LOW	HIGH	HIGH	LOW	Bank 6 only
LOW	HIGH	HIGH	HIGH	Bank 7 only
HIGH	Don't Care	Don't Care	Don't Care	All Banks

Table 4 - Bank selection for precharge by address bits

8.6.1 Burst read operation followed by precharge

Minimum Read to Precharge command spacing to the same bank = AL + BL/2 + max(RTP, 2) - 2 clks

For the earliest possible precharge, the precharge command may be issued on the rising edge which is "Additive Latency (AL) + BL/2 + max(RTP, 2) - 2 clocks" after a Read command. A new bank active (command) may be issued to the same bank after the RAS precharge time (tRP). A precharge command cannot be issued until tRAS is satisfied.

The minimum Read to Precharge spacing has also to satisfy a minimum analog time from the rising clock edge that initiates the last 4-bit prefetch of a Read to Precharge command. This time is called tRTP (Read to Precharge). For BL = 4 this is the time from the actual read (AL after the Read command) to Precharge command. For BL = 8 this is the time from AL + 2 clocks after the Read to the Precharge command. (Example timing waveforms refer to 11.15 to 11.19 Burst read operation followed by precharge diagram in Chapter 11)

8.6.2 Burst write operation followed by precharge

Minimum Write to Precharge Command spacing to the same bank = WL + BL/2 clks + tWR

For write cycles, a delay must be satisfied from the completion of the last burst write cycle until the Precharge Command can be issued. This delay is known as a write recovery time (twr) referenced from the completion of the burst write to the precharge command. No Precharge command should be issued prior to the twr delay. (Example timing waveforms refer to 11.20 to 11.21 Burst write operation followed by precharge diagram in Chapter 11)

8.7 Auto-precharge operation

Before a new row in an active bank can be opened, the active bank must be precharged using either the Precharge command or the Auto-precharge function. When a Read or a Write command is given to the DDR2 SDRAM, the $\overline{\text{CAS}}$ timing accepts one extra address, column address A10, to allow the active bank to automatically begin precharge at the earliest possible moment during the burst read or write cycle. If A10 is LOW when the READ or WRITE command is issued, then normal Read or Write burst operation is executed and the bank remains active at the completion of the burst sequence. If A10 is HIGH when the Read or Write command is issued, then the Auto-precharge function is engaged. During Auto-precharge, a Read command will execute as normal with the exception that the active bank will begin to precharge on the rising edge which is CAS Latency (CL) clock cycles before the end of the read burst.

Publication Release Date: Dec. 02, 2020



Auto-precharge is also implemented during Write commands. The precharge operation engaged by the Auto-precharge command will not begin until the last data of the burst write sequence is properly stored in the memory array.

This feature allows the precharge operation to be partially or completely hidden during burst read cycles (dependent upon CAS Latency) thus improving system performance for random data access. The RAS lockout circuit internally delays the Precharge operation until the array restore operation has been completed (tras satisfied) so that the Auto-precharge command may be issued with any read or write command.

8.7.1 Burst read with Auto-precharge

If A10 is HIGH when a Read Command is issued, the Read with Auto-precharge function is engaged. The DDR2 SDRAM starts an Auto-precharge operation on the rising edge which is (AL + BL/2) cycles later from the Read with AP command if trans(min) and trans(min) are satisfied. (Example timing waveform refer to 11.22 Burst read operation with Auto-precharge diagram in Chapter 11)

If tRAS(min) is not satisfied at the edge, the start point of Auto-precharge operation will be delayed until tRAS(min) is satisfied.

If tRTP(min) is not satisfied at the edge, the start point of Auto-precharge operation will be delayed until tRTP(min) is satisfied.

In case the internal precharge is pushed out by tRTP, tRP starts at the point where tRTP ends (not at the next rising clock edge after this event). So for BL = 4 the minimum time from Read with Auto-precharge to the next Activate command becomes AL + RU{ (tRTP + tRP) / tCK(avg) } (Example timing waveform refer to 11.23 Burst read operation with Auto-precharge diagram in Chapter 11.), for BL = 8 the time from Read with Auto-precharge to the next Activate command is AL + 2 + RU{ (tRTP + tRP) / tCK(avg) }, where RU stands for "rounded up to the next integer". In any event internal precharge does not start earlier than two clocks after the last 4-bit prefetch.

A new bank active command may be issued to the same bank if the following two conditions are satisfied simultaneously.

- The RAS precharge time (tRP) has been satisfied from the clock at which the Auto-precharge begins.
- The RAS cycle time (tRC) from the previous bank activation has been satisfied.

(Example timing waveforms refer to 11.24 to 11.25 Burst read with Auto-precharge followed by an activation to the same bank (tRC Limit) and (tRP Limit) diagram in Chapter 11)

8.7.2 Burst write with Auto-precharge

If A10 is HIGH when a Write Command is issued, the Write with Auto-Precharge function is engaged. The DDR2 SDRAM automatically begins precharge operation after the completion of the burst write plus write recovery time (WR) programmed in the mode register. The bank undergoing Auto-precharge from the completion of the write burst may be reactivated if the following two conditions are satisfied.

- The data-in to bank activate delay time (WR + tRP) has been satisfied.
- The RAS cycle time (tRC) from the previous bank activation has been satisfied.

(Example timing waveforms refer to 11.26 to 11.27 Burst write with Auto-precharge (tRC Limit) and (WR + tRP Limit) diagram in Chapter 11)

Publication Release Date: Dec. 02, 2020



Table 5 - Precharge & Auto-precharge clarifications

From Command	To Command	Minimum Delay between "From Command" to "To Command"	Unit	Notes
Read	Precharge (to same Bank as Read)	AL + BL/2 + max(RTP, 2) - 2	clks	1, 2
Read	Precharge All	AL + BL/2 + max(RTP, 2) - 2	clks	1, 2
Read w/AP	Precharge (to same Bank as Read w/AP)	AL + BL/2 + max(RTP, 2) - 2	clks	1, 2
Read W/AP	Precharge All	AL + BL/2 + max(RTP, 2) - 2	clks	1, 2
\\/	Precharge (to same Bank as Write)	WL + BL/2 + tWR	clks	2
Write	Precharge All	WL + BL/2 + tWR	clks	2
Write w/AP	Precharge (to same Bank as Write w/AP)	WL + BL/2 + WR	clks	2
Wille W/AP	Precharge All	WL + BL/2 + WR	clks	2
Dunahauna	Precharge (to same Bank as Precharge)	1	clks	2
Precharge	Precharge All	1	clks	2
B 1 411	Precharge	1	clks	2
Precharge All	Precharge All	1	clks	2

Notes:

- 1. RTP[cycles] = RU{ tRTP[nS] / tCK(avg)[nS] }, where RU stands for round up.
- 2. For a given bank, the precharge period should be counted from the latest precharge command, either one bank precharge or precharge all, issued to that bank. The precharge period is satisfied after tRPall (= tRP + 1 x tCK) depending on the latest precharge command issued to that bank.

8.8 Refresh Operation

DDR2 SDRAM requires a refresh of all rows in any rolling 64 ms interval. The necessary refresh can be generated in one of two ways: by explicit Auto Refresh commands or by an internally timed Self Refresh mode. Dividing the number of device rows into the rolling 64 ms interval defines the average refresh interval, tREFI, which is a guideline to controllers for distributed refresh timing.

When CS, RAS and CAS are held LOW and WE HIGH at the rising edge of the clock, the chip enters the Refresh mode (REF). All banks of the DDR2 SDRAM must be precharged and idle for a minimum of the Precharge time (tRP) before the Refresh command (REF) can be applied. An address counter, internal to the device, supplies the bank address during the refresh cycle. No control of the external address bus is required once this cycle has started. (Example timing waveform refer to 11.28 Self Refresh diagram in Chapter 11)

8.9 Power Down Mode

Power-down is synchronously entered when CKE is registered LOW, along with NOP or Deselect command. CKE is not allowed to go LOW while mode register or extended mode register command time, or read or write operation is in progress. CKE is allowed to go LOW while any other operation such as row activation, Precharge or Auto-precharge or Auto Refresh is in progress, but power down IDD specification will not be applied until finishing those operations.

The DLL should be in a locked state when power-down is entered. Otherwise DLL should be reset after exiting power-down mode for proper read operation.

Publication Release Date: Dec. 02, 2020



8.9.1 Power Down Entry

Two types of Power Down Mode can be performed on the device: Precharge Power Down Mode and Active Power Down Mode.

If power down occurs when all banks are idle, this mode is referred to as Precharge Power Down; if power down occurs when there is a row active in any bank, this mode is referred to as Active Power Down. Entering power down deactivates the input and output buffers, excluding CLK, $\overline{\text{CLK}}$, ODT and CKE. Also the DLL is disabled upon entering Precharge Power Down or slow exit Active Power Down, but the DLL is kept enabled during fast exit Active Power Down.

In power down mode, CKE LOW and a stable clock signal must be maintained at the inputs of the DDR2 SDRAM, and ODT should be in a valid state but all other input signals are "Don't Care". CKE LOW must be maintained until tCKE has been satisfied. Maximum power down duration is limited by the refresh requirements of the device, which allows a maximum of 9 x tREFI if maximum posting of REF is utilized immediately before entering power down. (Example timing waveforms refer to 11.29 Basic Power Down Entry and Exit diagram and 11.30 Precharged Power Down Entry and Exit diagram in Chapter 11)

8.9.2 Power Down Exit

The power-down state is synchronously exited when CKE is registered HIGH (along with a NOP or Deselect command). CKE high must be maintained until tcke has been satisfied. A valid, executable command can be applied with power-down exit latency, txp, txard, or txards, after CKE goes HIGH. Power-down exit latency is defined at AC Characteristics table of this data sheet.

8.10 Input clock frequency change during precharge power down

DDR2 SDRAM input clock frequency can be changed under following condition:

DDR2 SDRAM is in precharged power down mode. ODT must be turned off and CKE must be at logic LOW level. A minimum of 2 clocks must be waited after CKE goes LOW before clock frequency may change. SDRAM input clock frequency is allowed to change only within minimum and maximum operating frequency specified for the particular speed grade. During input clock frequency change, ODT and CKE must be held at stable LOW levels.

Once input clock frequency is changed, stable new clocks must be provided to DRAM before precharge power down may be exited and DLL must be RESET via MRS command after precharge power down exit. Depending on new clock frequency an additional MRS or EMRS command may need to be issued to appropriately set the WR, CL etc...

During DLL re-lock period, ODT must remain off. After the DLL lock time, the DRAM is ready to operate with new clock frequency. (Example timing waveform refer to 11.31 Clock frequency change in precharge Power Down mode diagram in Chapter 11)

Publication Release Date: Dec. 02, 2020



9. OPERATION MODE

9.1 Command Truth Table

	СК	E	BA2								
COMMAND	Previous Cycle	Current Cycle	BA1 BA0	A12 A11	A10	A9-A0	CS	RAS	CAS	WE	NOTES
Bank Activate	Н	Н	ВА	Ro	w Addre	ess	L	L	Н	Н	1,2
Single Bank Precharge	Н	Н	ВА	Х	L	Х	L	L	Н	L	1,2
Precharge All Banks	Н	Н	Х	Х	Н	Х	L	L	Н	L	1
Write	Н	Н	ВА	Column	L	Column	L	Н	L	L	1,2,3
Write with Auto- precharge	Н	Н	ВА	Column	Н	Column	L	Н	L	L	1,2,3
Read	Н	Н	ВА	Column	L	Column	L	Н	L	Н	1,2,3
Read with Auto- precharge	Н	Н	ВА	Column	Н	Column	L	Н	L	Н	1,2,3
(Extended) Mode Register Set	Н	Н	ВА	OP Code			L	L	L	L	1,2
No Operation	Н	Х	Х	Х	Х	Х	L	Н	Н	Н	1
Device Deselect	Н	Х	Х	Х	Х	Х	Н	Х	Х	Х	1
Refresh	Н	Н	Х	Х	Х	Х	L	L	L	Н	1
Self Refresh Entry	Н	L	Х	Х	Х	Х	L	L	L	Н	1,4
Self Refresh				V	Х		Н	Х	Х	Х	4.4.5
Exit	L	Н	X	X		X	L	Н	Н	Н	1,4,5
Power Down	ш			V		Х	Н	Х	Х	Х	1.6
Mode Entry	Н	L	Х	Х	X	Α	L	Н	Н	Н	1,6
Power Down	L	Н	Х	Х	Х	Х	Н	Х	Х	Х	1,6
Mode Exit	L	П	^	^	^	^	L	Н	Н	Н	۵,۱

Notes:

- 1. All DDR2 SDRAM commands are defined by states of \overline{CS} , \overline{RAS} , \overline{CAS} , \overline{WE} and CKE at the rising edge of the clock.
- 2. Bank addresses BA [2:0] determine which bank is to be operated upon. For (E)MRS BA selects an (Extended) Mode Register.
- 3. Burst reads or writes at BL = 4 can not be terminated or interrupted. See "Burst Interrupt" in section 8.5 for details.
- 4. VREF must be maintained during Self Refresh operation.
- 5. Self Refresh Exit is asynchronous.
- 6. The Power Down does not perform any refresh operations. The duration of Power Down Mode is therefore limited by the refresh requirements outlined in section 8.8.

Publication Release Date: Dec. 02, 2020



9.2 Clock Enable (CKE) Truth Table for Synchronous Transitions

CURRENT	СК	E	COMMAND (N) 3			
STATE ²	Previous Cycle ¹ Current Cycle ¹ (N-1) (N)		RAS, CAS, WE, CS	ACTION (N) ³	NOTES	
Power Down	L	L	X	Maintain Power Down	11, 13, 15	
Fower Down	L	Н	DESELECT or NOP	Power Down Exit	4, 8, 11, 13	
Self Refresh	L	L	X	Maintain Power Down	11, 15, 16	
Sell Reliesii	L	Н	DESELECT or NOP	Self Refresh Exit	4, 5, 9, 16	
Bank(s) Active	Н	L	DESELECT or NOP	Active Power Down Entry	4, 8, 10, 11, 13	
All Banks Idle	Н	L	DESELECT or NOP	Precharge Power Down Entry	4, 8, 10, 11, 13	
All balles fule	Н	L	REFRESH	Self Refresh Entry	6, 9, 11, 13	
	Н	Н	Refer to the Comr	7		

Notes:

- 1. CKE (N) is the logic state of CKE at clock edge N; CKE (N-1) was the state of CKE at the previous clock edge.
- 2. Current state is the state of the DDR2 SDRAM immediately prior to clock edge N.
- 3. COMMAND (N) is the command registered at clock edge N, and ACTION (N) is a result of COMMAND (N).
- 4. All states and sequences not shown are illegal or reserved unless explicitly described elsewhere in this document.
- 5. On Self Refresh Exit DESELECT or NOP commands must be issued on every clock edge occurring during the tXSNR period. Read commands may be issued only after tXSRD (200 clocks) is satisfied.
- 6. Self Refresh mode can only be entered from the All Banks Idle state.
- 7. Must be a legal command as defined in the Command Truth Table.
- 8. Valid commands for Power Down Entry and Exit are NOP and DESELECT only.
- 9. Valid commands for Self Refresh Exit are NOP and DESELECT only.
- 10. Power Down and Self Refresh can not be entered while Read or Write operations, (Extended) Mode Register Set operations or Precharge operations are in progress. See section 8.9 "Power Down Mode" and section 8.3.7/8.3.8 "Self Refresh Entry Command/Self Refresh Exit Command" for a detailed list of restrictions.
- 11. tCKEmin of 3 clocks means CKE must be registered on three consecutive positive clock edges. CKE must remain at the valid input level the entire time it takes to achieve the 3 clocks of registration. Thus, after any CKE transition, CKE may not transition from its valid level during the time period of tIS + 2 x tCK + tIH.
- 12. The state of ODT does not affect the states described in this table. The ODT function is not available during Self Refresh. See section 8.2.4.
- 13. The Power Down does not perform any refresh operations. The duration of Power Down Mode is therefore limited by the refresh requirements outlined in section 8.8.
- 14. CKE must be maintained HIGH while the SDRAM is in OCD calibration mode.
- 15. "X" means "don't care (including floating around VREF)" in Self Refresh and Power Down. However ODT must be driven high or low in Power Down if the ODT function is enabled (Bit A2 or A6 set to "1" in EMR (1)).
- 16. VREF must be maintained during Self Refresh operation.

9.3 Data Mask (DM) Truth Table

FUNCTION	DM	DQS	NOTE
Write enable	L	Valid	1
Write inhibit	Н	X	1

Note:

1. Used to mask write data, provided coincident with the corresponding data.

Publication Release Date: Dec. 02, 2020

W971GG6NB



9.4 Function Truth Table

CURRENT STATE	cs	RAS	CAS	WE	ADDRESS	COMMAND	ACTION	NOTES
	Н	Х	Х	Χ	Х	DSL	NOP or Power down	
	L	Н	Н	Н	Х	NOP	NOP or Power down	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
Idle	L	L	Н	Н	BA, RA	ACT	Row activating	
	L	L	Н	L	BA, A10	PRE/PREA	Precharge/ Precharge all banks	
	L	L	L	Н	Х	REF/SELF	Auto Refresh or Self Refresh	2
	L	L	L	L	Op-Code	MRS/EMRS	Mode/Extended register accessing	2
	Н	Х	Х	Х	Х	DSL	NOP	
	L	Н	Н	Н	Х	NOP	NOP	
	L	Н	L	Н	BA, CA, A10	READ/READA	Begin read	
Banks	L	Н	L	L	BA, CA, A10	WRIT/WRITA	Begin write	
Active	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	Precharge/ Precharge all banks	
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Х	X	DSL	Continue burst to end	
	L	Н	Н	Η	Х	NOP	Continue burst to end	
	L	Н	L	Η	BA, CA, A10	READ/READA	Burst interrupt	1,3
Read	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
Reau	L	L	Н	Ι	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Ι	X	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Χ	Χ	DSL	Continue burst to end	
	L	Н	Н	Н	Х	NOP	Continue burst to end	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
	L	Н	L	L	BA, CA, A10	WRIT/WRITA	Burst interrupt	1,3
Write	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Н	X	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	

Publication Release Date: Dec. 02, 2020



Function Truth Table, continued

CURRENT STATE	cs	RAS	CAS	WE	ADDRESS	COMMAND	ACTION	NOTES
	Н	Х	Х	Х	Х	DSL	Continue burst to end	
	L	Н	Н	Н	Х	NOP	Continue burst to end	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
Read with Auto-	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
precharge	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	Ш	L	L	Ι	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Χ	Х	DSL	Continue burst to end	
	L	Н	Н	Н	Х	NOP	Continue burst to end	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
Write with Auto-	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
precharge	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Χ	Χ	Х	DSL	NOP-> Idle after tRP	
	L	Н	Н	Н	Х	NOP	NOP-> Idle after tRP	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
Precharge	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
rrecharge	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	NOP-> Idle after tRP	1
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Χ	Х	DSL	NOP-> Row active after tRCD	
	L	Н	Н	Н	Х	NOP	NOP-> Row active after tRCD	
Row Activating	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	

Publication Release Date: Dec. 02, 2020



Function Truth Table, continued

CURRENT STATE	cs	RAS	CAS	WE	ADDRESS	COMMAND	ACTION	NOTES
	Н	Х	Х	Х	Х	DSL	NOP-> Bank active after tWR	
	L	Н	Н	Н	Х	NOP	NOP-> Bank active after tWR	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
Write	L	Н	L	L	BA, CA, A10	WRIT/WRITA	New write	
Recovering	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Х	Х	DSL	NOP-> Precharge after tWR	
	L	Н	Н	Н	Х	NOP	NOP-> Precharge after tWR	
10/11/4-2	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	1
Write Recovering	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	1
with Auto- precharge	L	L	Н	Н	BA, RA	ACT	ILLEGAL	1
precharge	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	1
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Х	Х	DSL	NOP-> Idle after tRC	
	L	Н	Н	Н	Х	NOP	NOP-> Idle after tRC	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	
Dofroching	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	
Refreshing	L	L	Н	Н	BA, RA	ACT	ILLEGAL	
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	
	Н	Х	Х	Х	Х	DSL	NOP-> Idle after tMRD	
	L	Н	Н	Н	Х	NOP	NOP-> Idle after tMRD	
	L	Н	L	Н	BA, CA, A10	READ/READA	ILLEGAL	
Mode Register Accessing	L	Н	L	L	BA, CA, A10	WRIT/WRITA	ILLEGAL	
	L	L	Н	Н	BA, RA	ACT	ILLEGAL	
	L	L	Н	L	BA, A10	PRE/PREA	ILLEGAL	
	L	L	L	Н	Х	REF/SELF	ILLEGAL	
	L	L	L	L	Op-Code	MRS/EMRS	ILLEGAL	

Notes:


- 1. This command may be issued for other banks, depending on the state of the banks.
- 2. All banks must be in "IDLE".
- 3. Read or Write burst interruption is prohibited for burst length of 4 and only allowed for burst length of 8. Burst read/write can only be interrupted by another read/write with 4 bit burst boundary. Any other case of read/write interrupt is not allowed.

Remark: H = High level, L = Low level, X = High or Low level (Don't Care), V = Valid data.

Publication Release Date: Dec. 02, 2020



9.5 Simplified Stated Diagram





10. ELECTRICAL CHARACTERISTICS

10.1 Absolute Maximum Ratings

PARAMETER	SYMBOL	RATING	UNIT	NOTES
Voltage on VDD pin relative to VSS	VDD	-1.0 ~ 2.3	V	1, 2
Voltage on VDDQ pin relative to VSS	VDDQ	-0.5 ~ 2.3	V	1, 2
Voltage on VDDL pin relative to VSS	VDDL	-0.5 ~ 2.3	V	1, 2
Voltage on any pin relative to VSS	VIN, VOUT	-0.5 ~ 2.3	V	1, 2
Storage Temperature	TSTG	-55 ~ 150	°C	1, 3

Notes:

- Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a
 stress rating only and functional operation of the device at these or any other conditions above those indicated in the
 operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended
 periods may affect reliability.
- 2. When VDD and VDDQ and VDDL are less than 500mV; VREF may be equal to or less than 300mV.
- 3. Storage temperature is the case surface temperature on the center/top side of the DRAM.

10.2 Operating Temperature Condition

PARAMETER	SYM.	MIN.	MAX.	UNIT	NOTES
Commercial Operating Temperature Range (for -18/-25/-3)	TCASE	0	85	°C	1, 2, 3
Industrial Operating Temperature Range (for 18I/25I)	TCASE	-40	95	°C	1, 2, 3, 4
Industrial Plus Operating Temperature Range (for 18J/25J)	TCASE	-40	105	°C	1, 2, 3, 4

Notes:

- 1. Operating case temperature is the case surface temperature on the center/top side of the DRAM.
- 2. Supporting 0°C ≤ TCASE ≤ 85°C with full JEDEC AC and DC specifications.
- 3. Supporting 0°C ≤ TCASE ≤ 85°C and being able to extend to 95°C or 105°C with doubling Auto Refresh commands in frequency to a 32 mS period (tREFI = 3.9 µS) and to enter to Self Refresh mode at this high temperature range via A7 "1" on EMR (2).
- 4. During operation, the DRAM case temperature must be maintained between -40°C ≤ TCASE ≤ 95°C for Industrial grade parts or -40°C ≤ TCASE ≤ 105°C for Industrial plus grade parts under all specification parameters.
- 5. All parts list in ordering information table (section 3) will not guarantee to meet functional and AC specification if the operation temperature range out of range mentioned in above table.

10.3 Recommended DC Operating Conditions

	<u>-</u>					
SYM.	PARAMETER	MIN.	TYP.	MAX.	UNIT	NOTES
VDD	Supply Voltage	1.7	1.8	1.9	V	1
VDDL	Supply Voltage for DLL	1.7	1.8	1.9	V	5
VDDQ	Supply Voltage for Output	1.7	1.8	1.9	V	1, 5
VREF	Input Reference Voltage	0.49 x VDDQ	0.5 x VDDQ	0.51 x VDDQ	V	2, 3
VTT	Termination Voltage (System)	VREF - 0.04	VREF	VREF + 0.04	V	4

Notes:

- There is no specific device VDD supply voltage requirement for SSTL_18 compliance. However under all conditions VDDQ must than or equal to VDD.
- 2. The value of VREF may be selected by the user to provide optimum noise margin in the system. Typically the value of VREF is expected to be about 0.5 x VDDQ of the transmitting device and VREF is expected to track variations in VDDQ.
- 3. Peak to peak AC noise on VREF may not exceed ± 2 % VREF(dc).
- 4. VTT of transmitting device must track VREF of receiving device.
- 5. VDDQ tracks with VDD, VDDL tracks with VDD. AC parameters are measured with VDD, VDDQ and VDDDL tied together.
- 6. All parts list in ordering information table (section 3) will not guarantee to meet functional and AC specification if the DC operation conditions out of range mentioned in above table.

Publication Release Date: Dec. 02, 2020



10.4 ODT DC Electrical Characteristics

PARAMETER/CONDITION	SYM.	MIN.	NOM.	MAX.	UNIT	NOTES
Rtt effective impedance value for EMRS(A6,A2)=0,1; 75 Ω	Rtt1(eff)	60	75	90	Ω	1
Rtt effective impedance value for EMRS(A6,A2)=1,0; 150 Ω	Rtt2(eff)	120	150	180	Ω	1
Rtt effective impedance value for EMRS(A6,A2)=1,1; 50 Ω	Rtt3(eff)	40	50	60	Ω	1, 2
Deviation of VM with respect to VDDQ/2	ΔVΜ	-6		+6	%	1

Notes:

- 1. Test condition for Rtt measurements.
- 2. Optional for DDR2-667, mandatory for DDR2-800 and DDR2-1066.

Measurement Definition for Rtt(eff):

Apply VIH (ac) and VIL (ac) to test pin separately, then measure current I(VIH (ac)) and I(VIL (ac)) respectively. VIH (ac), VIL (ac), and VDDQ values defined in SSTL_18.

$$Rtt(eff) = (VIH(ac) - VIL(ac)) / (I(VIHac) - I(VILac))$$

Measurement Definition for ΔVM:

Measure voltage (VM) at test pin (midpoint) with no load.

$$\Delta VM = ((2 \times Vm / VDDQ) - 1) \times 100\%$$

10.5 Input DC Logic Level

PARAMETER	SYM.	MIN.	MAX.	UNIT
DC input logic HIGH	VIH(dc)	VREF + 0.125	VDDQ + 0.3	V
DC input logic LOW	VIL(dc)	-0.3	VREF - 0.125	V

10.6 Input AC Logic Level

PARAMETER SYM.		-18/18	-18/18I/18J		-25/25I/25J/-3		
PARAMETER	STIVI.	MIN.	MAX.	MIN.	MAX.	UNIT	
AC input logic HIGH	VIH (ac)	VREF + 0.200	-	VREF + 0.200	VDDQ + VPEAK ¹	V	
AC input logic LOW	VIL (ac)	_	VREF - 0.200	VSSQ - VPEAK1	VREF - 0.200	V	

Note:

Publication Release Date: Dec. 02, 2020

^{1.} Refer to the page 67 sections 10.14.1 and 10.14.2 AC Overshoot/Undershoot specification table for VPEAK value: maximum peak amplitude allowed for Overshoot/Undershoot.



10.7 Capacitance

SYM.	PARAMETER	MIN.	MAX.	UNIT
ССК	Input Capacitance , CLK and CLK	1.0	1.5	pF
CDCK	Input Capacitance delta , CLK and $\overline{\text{CLK}}$	_	0.25	pF
CI	input Capacitance, all other input-only pins	1.0	1.75	pF
CDI	Input Capacitance delta, all other input-only pins	-	0.25	pF
CIO	Input/output Capacitance, DQ, LDM, UDM, LDQS, LDQS, UDQS, UDQS	2.5	3.5	pF
CDIO	Input/output Capacitance delta, DQ, LDM, UDM, LDQS, LDQS, UDQS, UDQS	-	0.5	pF

10.8 Leakage and Output Buffer Characteristics

SYM.	PARAMETER	MIN.	MAX.	UNIT	NOTES
liL	Input Leakage Current (0V ≤ VIN ≤ VDD)	-2	2	μA	1
IOL	Output Leakage Current (Output disabled, 0V ≤ VOUT ≤ VDDQ)	-5	5	μA	2
VOTR	Output Timing Measurement Reference Level	0.5 x VDDQ	ı	V	3
IOH(dc)	Output Minimum Source DC Current	-13.4	-	mA	4, 6
IOL(dc)	Output Minimum Sink DC Current	13.4	-	mA	5, 6

Notes:

- 1. All other pins not under test = 0 V.
- 2. DQ, LDQS, LDQS, UDQS, UDQS are disabled and ODT is turned off.
- 3. The VDDQ of the device under test is referenced.
- 4. VDDQ = 1.7 V; VOUT = 1.42 V. (VOUT VDDQ)/IOH must be less than 21 Ω for values of VOUT between VDDQ and VDDQ 0.28V.
- 5. VDDQ = 1.7 V; VOUT = 0.28V. VOUT/IOL must be less than 21 Ω for values of VOUT between 0 V and 0.28V.
- 6. The values of IOH(dc) and IOL(dc) are based on the conditions given in Notes 4 and 5. They are used to test drive current capability to ensure VIHmin plus a noise margin and VILmax minus a noise margin are delivered to an SSTL_18 receiver.

Publication Release Date: Dec. 02, 2020



10.9 DC Characteristics

0.44			-18/18I/18J	-25/25I/25J	-3		
SYM.	CONDITIONS		MAX.	MAX.	MAX.	UNIT	NOTES
IDD0	Operating Current - One Bank Active tCK = tCK(IDD), tRC = tRC(IDD), tRAS = t CKE is HIGH, CS is HIGH between va Address and control inputs are SWITC Databus inputs are SWITCHING.	60	55	50	mA	1,2,3,4,5,6	
IDD1	Operating Current - One Bank Active Precharge IOUT = 0 mA; BL = 4, CL = CL(IDD), AL = 0; tCK = tCK(IDD), tRC = tRC(IDD), tRAS = tRCD = tRCD(IDD); CKE is HIGH, CS is HIGH between validation and control inputs are SWITCD Data bus inputs are SWITCHING.	70	65	60	mA	1,2,3,4,5,6	
IDD2P	Precharge Power-Down Current All banks idle; tCK = tCK(IDD); CKE is LOW; Other control and address inputs are S Data Bus inputs are FLOATING. (TCAS	8	8	8	mA	1,2,3,4,5,6, 7	
IDD2N	Precharge Standby Current All banks idle; tCK = tCK(IDD); CKE is HIGH, CS is HIGH; Other control and address inputs are SWITCHING;		40	35	32	mA	1,2,3,4,5,6
IDD2Q	Data bus inputs are SWITCHING. Precharge Quiet Standby Current All banks idle; tCK = tCK(IDD); CKE is HIGH, CS is HIGH; Other control and address inputs are S Data bus inputs are FLOATING.	TABLE;	35	33	30	mA	1,2,3,4,5,6
IDD3PF	Active Power-Down Current All banks open; tCK = tCK(IDD);	Fast PDN Exit MRS(12) = 0	30	30	30	mA	1,2,3,4,5,6
IDD3PS	CKE is LOW; Other control and address inputs are STABLE; Data bus inputs are FLOATING. (TCASE ≤ 85°C)		17	17	17	mA	1,2,3,4,5,6, 7
IDD3N	Active Standby Current All banks open; tCK = tCK(IDD); tRAS = tRASmax(IDD), tR CKE is HIGH, CS is HIGH between to the control and address inputs are S Data bus inputs are SWITCHING.	valid commands;	50	47	45	mA	1,2,3,4,5,6

Publication Release Date: Dec. 02, 2020

see winbond

IDD4R	Operating Burst Read Current All banks open, Continuous burst reads, IOUT = 0 mA; BL = 4, CL = CL(IDD), AL = 0; tCK = tCK(IDD); tRAS = tRASmax(IDD), tRP = tRP(IDD); CKE is HIGH, CS is HIGH between valid commands; Address inputs are SWITCHING; Data Bus inputs are SWITCHING.	110	105	100	mA	1,2,3,4,5,6
IDD4W	Operating Burst Write Current All banks open, Continuous burst writes; BL = 4, CL = CL(IDD), AL = 0; tCK = tCK(IDD); tRAS = tRASmax(IDD), tRP = tRP(IDD); CKE is HIGH, CS is HIGH between valid commands; Address inputs are SWITCHING; Data Bus inputs are SWITCHING.	120	110	100	mA	1,2,3,4,5,6
IDD5B	Burst Refresh Current tCK = tCK(IDD); Refresh command every tRFC(IDD) interval; CKE is HIGH, \overline{CS} is HIGH between valid commands; Other control and address inputs are SWITCHING; Data bus inputs are SWITCHING.	85	80	75	mA	1,2,3,4,5,6
IDD6	Self Refresh Current CKE ≤ 0.2 V, external clock off, CLK and CLK at 0 V; Other control and address inputs are FLOATING; Data bus inputs are FLOATING. (TCASE ≤ 85°C)	8	8	8	mA	1,2,3,4,5,6, 7
IDD7	Operating Bank Interleave Read Current All bank interleaving reads, IOUT = 0mA; BL = 4, CL = CL(IDD), AL = tRCD(IDD) - 1 x tCK(IDD); tCK = tCK(IDD), tRC = tRC(IDD), tRRD = tRRD(IDD), tFAW = tFAW(IDD), tRCD = tRCD(IDD); CKE is HIGH, CS is HIGH between valid commands; Address bus inputs are STABLE during deselects; Data Bus inputs are SWITCHING.	150	140	130	mA	1,2,3,4,5,6

Notes:

- 1. $VDD = 1.8 \text{ V} \pm 0.1 \text{ V}$; $VDDQ = 1.8 \text{ V} \pm 0.1 \text{ V}$.
- 2. IDD specifications are tested after the device is properly initialized.
- 3. Input slew rate is specified by AC Parametric Test Condition.
- 4. IDD parameters are specified with ODT disabled.
- 5. Data Bus consists of DQ, LDM, UDM, LDQS, LDQS, UDQS and UDQS.
- 6. Definitions for IDD

 $LOW = Vin \le VIL (ac) (max)$

HIGH = Vin ≥ VIH (ac) (min)

STABLE = inputs stable at a HIGH or LOW level

FLOATING = inputs at VREF = VDDQ/2

SWITCHING = inputs changing between HIGH and LOW every other clock cycle (once per two clocks) for address and control signals, and inputs changing between HIGH and LOW every other data transfer (once per clock) for DQ signals not including masks or strobes.

7. The following IDD values must be derated (IDD limits increase), when TCASE ≥ 85°C IDD2P must be derated by 20%; IDD3P(slow) must be derated by 30% and IDD6 must be derated by 80%. (IDD6 will increase by this amount if TCASE < 85°C and the 2X refresh option is still enabled)

Publication Release Date: Dec. 02, 2020

W971GG6NB



10.10 IDD Measurement Test Parameters

SPEED GRADE	DDR2-1066 (-18/18I/18J)	DDR2-800 (-25/25I/25J)	DDR2-667 (-3)	UNIT
Bin(CL-tRCD-tRP)	6-6-6	5-5-5/6-6-6	5-5-5	
CL(IDD)	6	5/6	5	tCK
tCK(IDD)	1.875	2.5	3	nS
tRCD(IDD)	11.25	12.5	15	nS
tRP(IDD)	11.25	12.5	15	nS
tRC(IDD)	51.25	52.5	55	nS
tRASmin(IDD)	40	40	40	nS
tRASmax(IDD)	70000	70000	70000	nS
tRRD(IDD)-2KB	10	10	10	nS
tFAW(IDD)-2KB	45	45	50	nS
tRFC(IDD)	127.5	127.5	127.5	nS

- 42 -

Publication Release Date: Dec. 02, 2020



10.11 AC Characteristics

10.11.1 AC Characteristics and Operating Condition for -18/18I/18J speed grade

Notes: 1-3 and 45-47 apply to the entire table

	SPI	EED GRADE	DDR2-1066	(-18/18I/18J)			
SYM.	Bin(CL-tRCD-tRP)		6-6	6-6	UNIT ²⁵	NOTES	
	P.A	ARAMETER	MIN.	MAX.	1		
tRCD	Active to Read/Write C	ommand Delay Time	11.25	=	nS	23	
tRP	Precharge to Active Co	mmand Period	11.25	=	nS	23	
tRC	Active to Ref/Active Co	mmand Period	51.25	-	nS	23	
tRAS	Active to Precharge Co	mmand Period	40	70000	nS	4,23	
tRFC	Auto Refresh to Active/	Auto Refresh command period	127.5	-	nS	5	
		-40°C ≤ TCASE ≤ 85°C*	_	7.8	μS	5	
+DEE!	Average periodic	0°C ≤ TCASE ≤ 85°C	_	7.8	μS	5	
tREFI	refresh Interval	85°C < TCASE ≤ 95°C	_	3.9	μS	5,6	
		95°C < TCASE ≤ 105°C*	_	3.9	μS	5,6	
tCCD	CAS to CAS comm	AS to CAS command delay		=	nCK		
		tCK(avg) @ CL=4	3	7.5	nS	30,31	
t01(()	Access alsolves sind	tCK(avg) @ CL=5	2.5	7.5	nS	30,31	
tCK(avg)	Average clock period	tCK(avg) @ CL=6	1.875	7.5	nS	30,31	
		tCK(avg) @ CL=7	1.875	7.5	nS	30,31	
tCH(avg)	Average clock high pul	se width	0.45	0.55	tCK(avg)	30,31	
tCL(avg)	Average clock low puls	e width	0.45	0.55	tCK(avg)	30,31	
tAC	DQ output access time	from CLK/ CLK	-350	350	pS	35	
tDQSCK	DQS output access tim	e from CLK / CLK	-325	325	pS	35	
tDQSQ	DQS-DQ skew for DQS	S & associated DQ signals	ı	175	pS	13	
tCKE	CKE minimum high and	d low pulse width	3	_	nCK	7	
tRRD	Active to active comma	nd period for 2KB page size	10	_	nS	8,23	
tFAW	Four Activate Window f	or 2KB page size	45		nS	23	
tWR	Write recovery time		15	_	nS	23	
tDAL	Auto-precharge write re	ecovery + precharge time	WR + tnRP	-	nCK	24	
tWTR	Internal Write to Read	command delay	7.5	-	nS	9,23	
tRTP	Internal Read to Precha	arge command delay	7.5	-	nS	4,23	
tIS (base)	Address and control inp	out setup time	125		pS	10,26, 40,42,43	
tIH (base)	Address and control inp	out hold time	200	-	pS	11,26, 40,42,43	
tIS (ref)	Address and control inp	out setup time	325	-	pS	10,26, 40,42,43	
tIH (ref)	Address and control inp	out hold time	325	-	pS	11,26, 40,42,43	
tIPW	Address and control in	out pulse width for each input	0.6	_	tCK(avg)		
tDQSS	DQS latching rising train	nsitions to associated clock edges	-0.25	0.25	tCK(avg)	28	
tDSS	DQS falling edge to CL	K setup time	0.2	_	tCK(avg)	28	
tDSH	DQS falling edge hold to	time from CLK	0.2	_	tCK(avg)	28	
tDQSH	DQS input high pulse v	vidth	0.35	-	tCK(avg)		
tDQSL	DQS input low pulse wi	dth	0.35	-	tCK(avg)		

^{* -40°}C ≤ TCASE ≤ 85°C is for 18I and 18J grade parts only. 95°C < TCASE ≤ 105°C is for 18J grade parts only.

Publication Release Date: Dec. 02, 2020



AC Characteristics and Operating Condition for -18/18I/18J speed grade, continued

Notes: 1-3 and 45-47 apply to the entire table

	SPEED GRADE	DDR2-1066	(-18/18I/18J)		
SYM.	Bin(CL-tRCD-tRP)	6-0	6-6	UNITS ²⁵	NOTES
	PARAMETER	MIN.	MAX.		
tWPRE	Write preamble	0.35	-	tCK(avg)	
tWPST	Write postamble	0.4	0.6	tCK(avg)	12
tRPRE	Read preamble	0.9	1.1	tCK(avg)	14,36
tRPST	Read postamble	0.4	0.6	tCK(avg)	14,37
tDS(base)	DQ and DM input setup time	0	=	pS	16,27,29, 41,42,44
tDH(base)	DQ and DM input hold time	75	=	pS	17,27,29, 41,42,44
tDS(ref)	DQ and DM input setup time	200	-	pS	16,27,29, 41,42,44
tDH(ref)	DQ and DM input hold time	200	-	pS	17,27,29, 41,42,44
tDIPW	DQ and DM input pulse width for each input	0.35	-	tCK(avg)	
tHZ	Data-out high-impedance time from CLK/ CLK	-	tAC,max	pS	15,35
tLZ(DQS)	DQS/ DQS -low-impedance time from CLK/ CLK	tAC,min	tAC,max	pS	15,35
tLZ(DQ)	DQ low-impedance time from CLK/ CLK	2 x tAC,min	tAC,max	pS	15,35
tHP	Clock half pulse width	Min. (tCH(abs), tCL(abs))	_	pS	32
tQHS	Data hold skew factor	_	250	pS	33
tQH	DQ/DQS output hold time from DQS	tHP - tQHS	_	pS	34
txsnr	Exit Self Refresh to a non-Read command	tRFC + 10	_	nS	23
tXSRD	Exit Self Refresh to a Read command	200	_	nCK	
tXP	Exit precharge power down to any command	3	_	nCK	
tXARD	Exit active power down to Read command	3	-	nCK	18
tXARDS	Exit active power down to Read command (slow exit, lower power)	10 - AL	-	nCK	18,19
taond	ODT turn-on delay	2	2	nCK	20
tAON	ODT turn-on	tAC,min	tAC,max + 2.575	nS	20,35
tAONPD	ODT turn-on (Power Down mode)	tAC,min + 2	3 x tCK(avg) + tAC,max+1	nS	
tAOFD	ODT turn-off delay	2.5	2.5	nCK	21,39
tAOF	ODT turn-off	tAC,min	tAC,max + 0.6	nS	21,38,39
tAOFPD	ODT turn-off (Power Down mode)	tAC,min + 2	2.5 x tCK(avg) + tAC,max + 1	nS	
tanpd	ODT to power down Entry Latency	4	-	nCK	
tAXPD	ODT Power Down Exit Latency	11		nCK	
tMRD	Mode Register Set command cycle time	2	_	nCK	
tMOD	MRS command to ODT update delay	0	12	nS	23
tOIT	OCD Drive mode output delay	0	12	nS	23
tDELAY	Minimum time clocks remain ON after CKE asynchronously drops LOW	tIS+tCK(avg)+tIH	_	nS	22

Publication Release Date: Dec. 02, 2020



10.11.2 AC Characteristics and Operating Condition for -25/25I/25J/-3 speed grades

Notes: 1-3 and 45-47 apply to the entire table

CVM	SPEE	DDR2- (-25/25l/		DDR2- (-3)	UNITS ²⁵	NOTES	
SYM.	Bin(CL	-tRCD-tRP)	5-5-5/6	-6-6	5-5-	-5	UNITS	NOTES
	PARA	AMETER	MIN.	MAX.	MIN.	MAX.		
tRCD	Active to Read/Write Co	ommand Delay Time	12.5	_	15	_	nS	23
tRP	Precharge to Active Con	mmand Period	12.5	_	15	_	nS	23
tRC	Active to Ref/Active Cor	mmand Period	52.5	-	55	_	nS	23
tRAS	Active to Precharge Con	mmand Period	40	70000	40	70000	nS	4,23
tRFC	Auto Refresh to Active/aperiod	Auto Refresh command	127.5	-	127.5	-	nS	5
		-40°C ≤ TCASE ≤ 85°C*	-	7.8	-	_	μS	5
tREFI	Average periodic	0°C ≤ TCASE ≤ 85°C	П	7.8	_	7.8	μS	5
refresh Interval	refresh Interval	85°C < TCASE ≤ 95°C	II	3.9	=	3.9	μS	5,6
		95°C < TCASE ≤ 105°C*	-	3.9	-	-	μS	5,6
tCCD	CAS to CAS comma	and delay	2	-	2	-	nCK	
		tCK(avg) @ CL=3	5	8	5	8	nS	30,31
tCK(ava)	Average clock period	tCK(avg) @ CL=4	3.75	8	3.75	8	nS	30,31
tor(avg)	Average clock period	tCK(avg) @ CL=5	2.5	8	3	8	nS	30,31
		tCK(avg) @ CL=6	2.5	8	-	-	nS	30,31
tCH(avg)	Average clock high puls		0.45	0.55	0.45	0.55	tCK(avg)	30,31
tCL(avg)	Average clock low pulse	e width	0.45	0.55	0.45	0.55	tCK(avg)	30,31
tAC	DQ output access time	from CLK/ CLK	-400	400	-450	450	pS	35
tDQSCK	DQS output access time	e from CLK / CLK	-350	350	-400	400	pS	35
tDQSQ	DQS-DQ skew for DQS	& associated DQ signals	_	200	-	240	pS	13
tCKE	CKE minimum high and	l low pulse width	3	-	3	_	nCK	7
tRRD	Active to active comma	nd period for 2KB page size	10	-	10	_	nS	8,23
tFAW	Four Activate Window for	or 2KB page size	45	-	50	-	nS	23
tWR	Write recovery time		15	-	15	_	nS	23
tDAL	Auto-precharge write re	covery + precharge time	WR + tnRP	-	WR + tnRP	-	nCK	24
tWTR	Internal Write to Read of	command delay	7.5	-	7.5	-	nS	9,23
tRTP	Internal Read to Precha	arge command delay	7.5	-	7.5	_	nS	4,23
tIS (base)	Address and control inp	out setup time	175	_	200	-	pS	10,26, 40,42,43
tIH (base)	Address and control inp	out hold time	250	_	275	-	pS	11,26, 40,42,43
tIS (ref)	Address and control inp	out setup time	375	-	400	-	pS	10,26, 40,42,43
tIH (ref)	Address and control inp	out hold time	375	_	400	-	pS	11,26, 40,42,43
tIPW	Address and control inpinput	0.6	-	0.6	ı	tCK(avg)		
tDQSS	DQS latching rising tran edges	sitions to associated clock	-0.25	0.25	-0.25	0.25	tCK(avg)	28
tDSS	DQS falling edge to CLI	K setup time	0.2	-	0.2	-	tCK(avg)	28
tDSH	DQS falling edge hold to	ime from CLK	0.2	_	0.2		tCK(avg)	28
tDQSH	DQS input high pulse w	idth	0.35	_	0.35	ĺ	tCK(avg)	
tDQSL	DQS input low pulse wie	dth	0.35	_	0.35	_	tCK(avg)	

^{* -40°}C \leq TCASE \leq 85°C is for 25I and 25J grade parts only. 95°C < TCASE \leq 105°C is for 25J grade parts only.

Publication Release Date: Dec. 02, 2020



AC Characteristics and Operating Condition for -25/25I/25J/-3 speed grades, continued

Notes: 1-3 and 45-47 apply to the entire table

SYM.	SPEED GRADE		2-800 51/25J)	DDR:	2-667 3)	LINIT © 25	NOTES
STIVI.	Bin(CL-tRCD-tRP)	5-5-5	/6-6-6	5-	5-5	UNITS	NOTES
	PARAMETER	MIN.	MAX.	MIN.	MAX.		
tWPRE	Write preamble	0.35	-	0.35	-	tCK(avg)	
tWPST	Write postamble	0.4	0.6	0.4	0.6	tCK(avg)	12
tRPRE	Read preamble	0.9	1.1	0.9	1.1	tCK(avg)	14,36
tRPST	Read postamble	0.4	0.6	0.4	0.6	tCK(avg)	14,37
tDS(base)	DQ and DM input setup time	50	-	100	_	pS	16,27,29, 41,42,44
tDH(base)	DQ and DM input hold time	125	_	175	_	pS	17,27,29, 41,42,44
tDS(ref)	DQ and DM input setup time	250	-	300	-	pS	16,27,29, 41,42,44
tDH(ref)	DQ and DM input hold time	250	-	300	-	pS	17,27,29, 41,42,44
tDIPW	DQ and DM input pulse width for each input	0.35	=	0.35	=	tCK(avg)	
tHZ	Data-out high-impedance time from CLK/CLK	_	tAC,max	_	tAC,max	pS	15,35
tLZ(DQS)	DQS/DQS -low-impedance time from CLK/CLK	tAC,min	tAC,max	tAC,min	tAC,max	pS	15,35
tLZ(DQ)	DQ low-impedance time from CLK/ CLK	2 x tAC,min	tAC,max	2 x tAC,min	tAC,max	pS	15,35
tHP	Clock half pulse width	Min. (tCH(abs), tCL(abs))		Min. (tCH(abs), tCL(abs))		pS	32
tQHS	Data hold skew factor	_	300	-	340	pS	33
tQH	DQ/DQS output hold time from DQS	tHP - tQHS	-	tHP - tQHS	-	pS	34
txsnr	Exit Self Refresh to a non-Read command	tRFC + 10	-	tRFC + 10	-	nS	23
txsrd	Exit Self Refresh to a Read command	200	-	200	-	nCK	
tXP	Exit precharge power down to any command	2	-	2	-	nCK	
tXARD	Exit active power down to Read command	2	-	2	-	nCK	18
tXARDS	Exit active power down to Read command (slow exit, lower power)	8 - AL	-	7 - AL	-	nCK	18,19
tAOND	ODT turn-on delay	2	2	2	2	nCK	20
tAON	ODT turn-on	tAC,min	tAC,max + 0.7	tAC,min	tAC,max + 0.7	nS	20,35
tAONPD	ODT turn-on (Power Down mode)	tAC,min + 2	2 x tCK(avg) + tAC,max + 1	tAC,min + 2	2 x tCK(avg) + tAC,max + 1	nS	
tAOFD	ODT turn-off delay	2.5	2.5	2.5	2.5	nCK	21,39
tAOF	ODT turn-off	tAC,min	tAC,max + 0.6	tAC,min	tAC,max + 0.6	nS	21,38,39
tAOFPD	ODT turn-off (Power Down mode)	tAC,min + 2	2.5 x tCK(avg) + tAC,max + 1	tAC,min + 2	2.5 x tCK(avg) + tAC,max + 1	nS	
tANPD	ODT to power down Entry Latency	3	-	3	_	nCK	
tAXPD	ODT Power Down Exit Latency	8		8		nCK	
tMRD	Mode Register Set command cycle time	2	-	2	_	nCK	
tMOD	MRS command to ODT update delay	0	12	0	12	nS	23
tOIT	OCD Drive mode output delay	0	12	0	12	nS	23
tDELAY	Minimum time clocks remain ON after CKE asynchronously drops LOW	tIS+tCK(avg)+ tIH	_	tIS+tCK(avg)+ tIH	-	nS	22

Publication Release Date: Dec. 02, 2020



Notes:

- 1. All voltages are referenced to VSS.
- Tests for AC timing, IDD, and electrical AC and DC characteristics may be conducted at nominal reference/supply voltage levels, but the related specifications and device operation are guaranteed for the full voltage range specified. ODT is disabled for all measurements that are not ODT-specific.
- 3. AC timing reference load:




Figure 16 - AC timing reference load

- This is a minimum requirement. Minimum read to precharge timing is AL + BL / 2 provided that the tRTP and tRAS(min) have been satisfied.
- If refresh timing is violated, data corruption may occur and the data must be re-written with valid data before a valid READ can be executed.
- 6. This is an optional feature. For detailed information, please refer to "Operating Temperature Condition" section 10.2 in this data sheet.
- 7. tCKE min of 3 clocks means CKE must be registered on three consecutive positive clock edges. CKE must remain at the valid input level the entire time it takes to achieve the 3 clocks of registration. Thus, after any CKE transition, CKE may not transition from its valid level during the time period of tIS + 2 x tCK + tIH.
- 8. A minimum of two clocks (2 * nCK) is required irrespective of operating frequency.
- 9. tWTR is at least two clocks (2 * nCK) independent of operation frequency.
- 10. There are two sets of values listed for Command/Address input setup time: tIS(base) and tIS(ref). The tIS(ref) value (for reference only) is equivalent to the baseline value of tIS(base) at VREF when the slew rate is 1.0 V/nS. The baseline value tIS(base) is the JEDEC defined value, referenced from the input signal crossing at the VIH(ac) level for a rising signal and VIL(ac) for a falling signal applied to the device under test. See Figure 17. If the Command/Address slew rate is not equal to 1.0 V/nS, then the baseline values must be derated by adding the values from table of tIS/tIH derating values for DDR2-667, DDR2-800 and DDR2-1066 (page 55).




Figure 17 - Differential input waveform timing - tIS and tIH

Publication Release Date: Dec. 02, 2020



- 11. There are two sets of values listed for Command/Address input hold time: tlH(base) and tlH(ref). The tlH(ref) value (for reference only) is equivalent to the baseline value of tlH(base) at VREF when the slew rate is 1.0 V/nS. The baseline value tlH(base) is the JEDEC defined value, referenced from the input signal crossing at the VIL(dc) level for a rising signal and VIH(dc) for a falling signal applied to the device under test. See Figure 17. If the Command/Address slew rate is not equal to 1.0 V/nS, then the baseline values must be derated by adding the values from table tlS/tlH derating values for DDR2-667, DDR2-800 and DDR2-1066 (page 55).
- 12. The maximum limit for the tWPST parameter is not a device limit. The device operates with a greater value for this parameter, but system performance (bus turnaround) will degrades accordingly.
- 13. tDQSQ: Consists of data pin skew and output pattern effects, and p-channel to n-channel variation of the output drivers as well as output Slew Rate mismatch between DQS / DQS and associated DQ in any given cycle.
- 14. tRPST end point and tRPRE begin point are not referenced to a specific voltage level but specify when the device output is no longer driving (tRPST), or begins driving (tRPRE). Figure 18 shows a method to calculate these points when the device is no longer driving (tRPST), or begins driving (tRPRE) by measuring the signal at two different voltages. The actual voltage measurement points are not critical as long as the calculation is consistent.
- 15. tHZ and tLZ transitions occur in the same access time as valid data transitions. These parameters are referenced to a specific voltage level which specifies when the device output is no longer driving (tHZ), or begins driving (tLZ). Figure 18 shows a method to calculate the point when device is no longer driving (tHZ), or begins driving (tLZ) by measuring the signal at two different voltages. The actual voltage measurement points are not critical as long as the calculation is consistent. tLZ(DQ) refers to tLZ of the DQ's and tLZ(DQS) refers to tLZ of the (UDQS, LDQS, UDQS and UDQS) each treated as single-ended signal.




Figure 18 - Method for calculating transitions and endpoints

- 16. Input waveform timing tDS with differential data strobe enabled MR[bit10]=0. There are two sets of values listed for DQ and DM input setup time: tDS(base) and tDS(ref). The tDS(ref) value (for reference only) is equivalent to the baseline value tDS(base) at VREF when the slew rate is 2.0 V/nS, differentially. The baseline value tDS(base) is the JEDEC defined value, referenced from the input signal crossing at the VIH(ac) level to the differential data strobe crosspoint for a rising signal, and from the input signal crossing at the VIL(ac) level to the differential data strobe crosspoint for a falling signal applied to the device under test. DQS, DQS signals must be monotonic between VIL(dc)max and VIH(dc)min. See Figure 19. If the differential DQS slew rate is not equal to 2.0 V/nS, then the baseline values must be derated by adding the values from table of DDR2-667, DDR2-800 and DDR2-1066 tDS/tDH derating with differential data strobe (page 60).
- 17. Input waveform timing tDH with differential data strobe enabled MR[bit10]=0. There are two sets of values listed for DQ and DM input hold time: tDH(base) and tDH(ref). The tDH(ref) value (for reference only) is equivalent to the baseline value tDH(base) at VREF when the slew rate is 2.0 V/nS, differentially. The baseline value tDH(base) is the JEDEC defined value, referenced from the differential data strobe crosspoint to the input signal crossing at the VIH(dc) level for a falling signal and from the differential data strobe crosspoint to the input signal crossing at the VIL(dc) level for a rising signal applied to the device under test. DQS, DQS signals must be monotonic between VIL(dc)max and VIH(dc)min. See Figure 19. If the differential DQS slew rate is not equal to 2.0 V/nS, then the baseline values must be derated by adding the values from table of DDR2-667, DDR2-800 and DDR2-1066 tDS/tDH derating with differential data strobe (page 60).

Publication Release Date: Dec. 02, 2020

resear winbond




Figure 19 - Differential input waveform timing - tDS and tDH

- 18. User can choose which active power down exit timing to use via MRS (bit 12). tXARD is expected to be used for fast active power down exit timing. tXARDS is expected to be used for slow active power down exit timing.
- 19. AL = Additive Latency.
- 20. ODT turn on time min is when the device leaves high impedance and ODT resistance begins to turn on. ODT turn on time max is when the ODT resistance is fully on. Both are measure from tAOND, which is interpreted differently per speed bin. For DDR2-667/800/1066, tAOND is 2 clock cycles after the clock edge that registered a first ODT HIGH counting the actual input clock edges.
- 21. ODT turn off time min is when the device starts to turn off ODT resistance. ODT turn off time max is when the bus is in high impedance. Both are measured from tAOFD, which is interpreted as 0.5 x tCK(avg) [nS] after the second trailing clock edge counting from the clock edge that registered a first ODT LOW and by counting the actual input clock edges.

For DDR2-667/800: If tCK(avg) = 3 nS is assumed, tAOFD is 1.5 nS (= 0.5 x 3 nS) after the second trailing clock edge counting from the clock edge that registered a first ODT LOW and by counting the actual input clock edges.

For DDR2-1066: tAOFD is 0.9375 [nS] (= 0.5 x 1.875 [nS]) after the second trailing clock edge counting from the clock edge that registered a first ODT LOW and by counting the actual input clock edges.

- 22. The clock frequency is allowed to change during Self Refresh mode or precharge power-down mode. In case of clock frequency change during precharge power-down, a specific procedure is required as described in section 8.10.
- 23. For these parameters, the DDR2 SDRAM device is characterized and verified to support tnPARAM = RU{tPARAM / tCK(avg)}, which is in clock cycles, assuming all input clock jitter specifications are satisfied.

Examples:

The device will support tnRP = RU{tRP / tCK(avg)}, which is in clock cycles, if all input clock jitter specifications are met. This means:

For DDR2-667 5-5-5, of which tRP = 15nS, the device will support $tnRP = RU\{tRP / tCK(avg)\} = 5$, i.e. as long as the input clock jitter specifications are met, Precharge command at Tm and Active command at Tm+5 is valid even if (Tm+5 - Tm) is less than 15nS due to input clock jitter.

For DDR2-1066 6-6-6, of which tRP = 11.25 nS, the device will support tnRP = RU{tRP / tCK(avg)} = 6, i.e. as long as the input clock jitter specifications are met, Precharge command at Tm and Active command at Tm+6 is valid even if (Tm+6 - Tm) is less than 11.25 nS due to input clock jitter.

24. tDAL [nCK] = WR [nCK] + tnRP [nCK] = WR + RU {tRP [pS] / tCK(avg) [pS] }, where WR is the value programmed in the mode register set and RU stands for round up.

Example:

For DDR2-1066 6-6-6 at tCK(avg) = 1.875 nS with WR programmed to 8 nCK, tDAL = $8 + RU\{11.25 \text{ nS} / 1.875 \text{ nS}\}$ [nCK] = 8 + 6 [nCK] = 14 [nCK].

Publication Release Date: Dec. 02, 2020

W971GG6NB



25. New units, 'tCK(avg)' and 'nCK', are introduced in DDR2-667, DDR2-800 and DDR2-1066.

Unit 'tCK(avg)' represents the actual tCK(avg) of the input clock under operation.

Unit 'nCK' represents one clock cycle of the input clock, counting the actual clock edges.

Examples:

For DDR2-667/800: tXP = 2 [nCK] means; if Power Down exit is registered at Tm, an Active command may be registered at Tm+2, even if (Tm+2 - Tm) is 2 x tCK(avg) + tERR(2per),min.

For DDR2-1066: tXP = 3 [nCK] means; if Power Down exit is registered at Tm, an Active command may be registered at Tm+3, even if (Tm+3 - Tm) is 3 x tCK(avg) + tERR(3per),min.

- 26. These parameters are measured from a command/address signal (CKE, \overline{CS} , \overline{RAS} , \overline{CAS} , \overline{WE} , ODT, BA0, A0, A1, etc.) transition edge to its respective clock signal (CLK/ \overline{CLK}) crossing. The spec values are not affected by the amount of clock jitter applied (i.e. tJIT(per), tJIT(cc), etc.), as the setup and hold are relative to the clock signal crossing that latches the command/address. That is, these parameters should be met whether clock jitter is present or not.
- 27. If tDS or tDH is violated, data corruption may occur and the data must be re-written with valid data before a valid READ can be executed.
- 28. These parameters are measured from a data strobe signal ((L/U)DQS/DQS) crossing to its respective clock signal (CLK/CLK) crossing. The spec values are not affected by the amount of clock jitter applied (i.e. tJIT(per), tJIT(cc), etc.), as these are relative to the clock signal crossing. That is, these parameters should be met whether clock jitter is present or not.
- 29. These parameters are measured from a data signal ((L/U)DM, (L/U)DQ0, (L/U)DQ1, etc.) transition edge to its respective data strobe signal ((L/U)DQS/DQS) crossing.

Publication Release Date: Dec. 02, 2020



30. Input clock jitter spec parameter. These parameters and the ones in the table below are referred to as 'input clock jitter spec parameters'. The jitter specified is a random jitter meeting a Gaussian distribution.

Input clock-Jitter specifications parameters for DDR2-667, DDR2-800 and DDR2-1066

DADAMETED	CVMDOL	DDR	2-667	DDR	2-800	DDR2-1066		UNIT
PARAMETER	SYMBOL	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	UNII
Clock period jitter	tJIT(per)	-125	125	-100	100	-90	90	pS
Clock period jitter during DLL locking period	tJIT(per,lck)	-100	100	-80	80	-80	80	pS
Cycle to cycle clock period	tJIT(cc)	-250	250	-200	200	-180	180	pS
Cycle to cycle clock period jitter during DLL locking period	tJIT(cc,lck)	-200	200	-160	160	-160	160	pS
Cumulative error across 2 cycles	tERR(2per)	-175	175	-150	150	-132	132	pS
Cumulative error across 3 cycles	tERR(3per)	-225	225	-175	175	-157	157	pS
Cumulative error across 4 cycles	tERR(4per)	-250	250	-200	200	-175	175	pS
Cumulative error across 5 cycles	tERR(5per)	-250	250	-200	200	-188	188	pS
Cumulative error across n cycles, n = 6 10, inclusive	tERR(6-10per)	-350	350	-300	300	-250	250	pS
Cumulative error across n cycles, n = 11 50, inclusive	tERR(11-50per)	-450	450	-450	450	-425	425	pS
Duty cycle jitter	tJIT(duty)	-125	125	-100	100	-75	75	pS

Definitions:

- tCK(avg)

tCK(avg) is calculated as the average clock period across any consecutive 200 cycle window.

$$tCK(avg) = \left[\sum_{j=1}^{N} tCK_{j}\right]/N$$
where $N = 200$

- tCH(avg) and tCL(avg)

tCH(avg) is defined as the average HIGH pulse width, as calculated across any consecutive 200 HIGH pulses.

$$tCH(avg) = \left[\sum_{j=1}^{N} tCH_{j}\right] / (N \times tCK(avg))$$

$$where \qquad N = 200$$

tCL(avg) is defined as the average LOW pulse width, as calculated across any consecutive 200 LOW pulses.

$$tCL(avg) = \left[\sum_{j=1}^{N} tCL_{j}\right] / (N \times tCK(avg))$$

$$where \qquad N = 200$$

Publication Release Date: Dec. 02, 2020



- tJIT(duty)

tJIT(duty) is defined as the cumulative set of tCH jitter and tCL jitter. tCH jitter is the largest deviation of any single tCH from tCH(avg). tCL jitter is the largest deviation of any single tCL from tCL(avg).

tJIT(duty) = Min/max of {tJIT(CH), tJIT(CL)}

where,

tJIT(CH) = {tCHi- tCH(avg) where i=1 to 200}

tJIT(CL) = {tCLi- tCL(avg) where i=1 to 200}

- tJIT(per), tJIT(per,lck)

tJIT(per) is defined as the largest deviation of any single tCK from tCK(avg).

tJIT(per) = Min/max of {tCKi- tCK(avg) where i=1 to 200}

tJIT(per) defines the single period jitter when the DLL is already locked.

tJIT(per,lck) uses the same definition for single period jitter, during the DLL locking period only.

tJIT(per) and tJIT(per,lck) are not guaranteed through final production testing.

tJIT(cc), tJIT(cc,lck)

tJIT(cc) is defined as the difference in clock period between two consecutive clock cycles:

tJIT(cc) = Max of |tCKi+1 - tCKi|

tJIT(cc) defines the cycle to cycle jitter when the DLL is already locked.

tJIT(cc,lck) uses the same definition for cycle to cycle jitter, during the DLL locking period only.

tJIT(cc) and tJIT(cc,lck) are not guaranteed through final production testing.

tERR(2per), tERR (3per), tERR (4per), tERR (5per), tERR (6-10per) and tERR (11-50per)
 tERR is defined as the cumulative error across multiple consecutive cycles from tCK(avg).

$$tERR(nper) = \left[\sum_{j=1}^{i+n-1} tCK_{j}\right] - n \times tCK(avg)$$

$$\textit{Where} \begin{bmatrix} n=2 & \text{for} & \text{tERR}(2\text{per}) \\ n=3 & \text{for} & \text{tERR}(3\text{per}) \\ n=4 & \text{for} & \text{tERR}(4\text{per}) \\ n=5 & \text{for} & \text{tERR}(5\text{per}) \\ 6 \leq n \leq 10 & \text{for} & \text{tERR}(6-10\text{per}) \\ 11 \leq n \leq 50 & \text{for} & \text{tERR}(11-50\text{per}) \end{bmatrix}$$

Publication Release Date: Dec. 02, 2020



31. These parameters are specified per their average values, however it is understood that the following relationship between the average timing and the absolute instantaneous timing holds at all times. (Min and max of SPEC values are to be used for calculations in the table below.)

PARAMETER	SYMBOL	MIN	MAX	UNIT
Absolute clock period	tCK(abs)	tCK(avg),min + tJIT(per),min	tCK(avg),max + tJIT(per),max	pS
Absolute clock HIGH pulse width	tCH(abs)	tCH(avg),min x tCK(avg),min + tJIT(duty),min	tCH(avg),max x tCK(avg),max + tJIT(duty),max	pS
Absolute clock LOW pulse width	tCL(abs)	tCL(avg),min x tCK(avg),min + tJIT(duty),min	tCL(avg),max x tCK(avg),max + tJIT(duty),max	pS

Examples: 1) For DDR2-667, tCH(abs),min = (0.45 x 3000 pS) - 125 pS = 1225 pS

- 2) For DDR2-1066, tCH(abs),min = (0.45 x 1875 pS) 75 pS = 768.75 pS
- 32. tHP is the minimum of the absolute half period of the actual input clock. tHP is an input parameter but not an input specification parameter. It is used in conjunction with tQHS to derive the DRAM output timing tQH. The value to be used for tQH calculation is determined by the following equation:

tHP = Min (tCH(abs), tCL(abs)),

where,

tCH(abs) is the minimum of the actual instantaneous clock HIGH time;

tCL(abs) is the minimum of the actual instantaneous clock LOW time;

33. tQHS accounts for:

- 1) The pulse duration distortion of on-chip clock circuits, which represents how well the actual tHP at the input is transferred to the output: and
- 2) The worst case push-out of DQS on one transition followed by the worst case pull-in of DQ on the next transition, both of which are independent of each other, due to data pin skew, output pattern effects, and p-channel to n-channel variation of the output drivers
- 34. tQH = tHP tQHS, where:

tHP is the minimum of the absolute half period of the actual input clock; and

tQHS is the specification value under the max column.

{The less half-pulse width distortion present, the larger the tQH value is; and the larger the valid data eye will be.} Examples:

- 1) If the system provides tHP of 1315 pS into a DDR2-667 SDRAM, the DRAM provides tQH of 975 pS minimum.
- 2) If the system provides tHP of 1420 pS into a DDR2-667 SDRAM, the DRAM provides tQH of 1080 pS minimum.
- 3) If the system provides tHP of 825 pS into a DDR2-1066 SDRAM, the DRAM provides tQH of 575 pS minimum.
- 4) If the system provides tHP of 900 pS into a DDR2-1066 SDRAM, the DRAM provides tQH of 650 pS minimum.
- 35. When the device is operated with input clock jitter, this parameter needs to be derated by the actual tERR(6-10per) of the input clock. (output deratings are relative to the SDRAM input clock.)

Examples:

1) If the measured jitter into a DDR2-667 SDRAM has tERR(6-10per), min = -272 pS and tERR(6-10per), max = +293 pS, then tDQSCK, min(derated) = tDQSCK, min - tERR(6-10per), max = -400 pS -293 pS = -693 pS and tDQSCK, max(derated) = tDQSCK, max - tERR(6-10per), min = 400 pS +272 pS = +672 pS.

Similarly, tLZ(DQ) for DDR2-667 derates to tLZ(DQ),min(derated) = - 900 pS - 293 pS = - 1193 pS and tLZ(DQ),max(derated) = 450 pS + 272 pS = + 722 pS. (Caution on the min/max usage!)

2) If the measured jitter into a DDR2-1066 SDRAM has tERR(6-10per), min = -202 pS and tERR(6-10per), max = +223 pS, then tDQSCK, min(derated) = tDQSCK, min - tERR(6-10per), max = -300 pS -223 pS = -523 pS and tDQSCK, max(derated) = tDQSCK, max - tERR(6-10per), min = 300 pS +202 pS = +502 pS.

Similarly, tLZ(DQ) for DDR2-1066 derates to tLZ(DQ),min(derated) = - 700 pS - 223 pS = - 923 pS and tLZ(DQ),max(derated) = 350 pS + 202 pS = + 552 pS. (Caution on the min/max usage!)

Publication Release Date: Dec. 02, 2020



36. When the device is operated with input clock jitter, this parameter needs to be derated by the actual tJIT(per) of the input clock. (output deratings are relative to the SDRAM input clock.)

Examples

- 1) If the measured jitter into a DDR2-667 SDRAM has tJIT(per),min = 72 pS and tJIT(per),max = + 93 pS, then tRPRE,min(derated) = tRPRE,min + tJIT(per),min = 0.9 x tCK(avg) 72 pS = + 2178 pS and tRPRE,max(derated) = tRPRE,max + tJIT(per),max = 1.1 x tCK(avg) + 93 pS = + 2843 pS. (Caution on the min/max usage!)
- 2) If the measured jitter into a DDR2-1066 SDRAM has tJIT(per),min = 72 pS and tJIT(per),max = + 63 pS, then tRPRE,min(derated) = tRPRE,min + tJIT(per),min = 0.9 x tCK(avg) 72 pS = + 1615.5 pS and tRPRE,max(derated) = tRPRE,max + tJIT(per),max = 1.1 x tCK(avg) + 63 pS = + 2125.5 pS. (Caution on the min/max usage!)
- 37. When the device is operated with input clock jitter, this parameter needs to be derated by the actual tJIT(duty) of the input clock. (output deratings are relative to the SDRAM input clock.)

Examples:

- 1) If the measured jitter into a DDR2-800 SDRAM has tJIT(duty), min = -72 pS and tJIT(duty), max = +93 pS, then tRPST, min(derated) = tRPST, min(derated) = tRPST, min(derated) = tRPST, max + tJIT(duty), $max = 0.6 \times tCK(avg) + 93$ pS = +1593 pS. (Caution on the min/max usage!)
- 2) If the measured jitter into a DDR2-1066 SDRAM has tJIT(duty), min = -72 pS and tJIT(duty), max = +63 pS, then tRPST, min(derated) = tRPST, min + tJIT(duty), min = 0.4 x tCK(avg) 72 pS = +678 pS and tRPST, max(derated) = tRPST, max + tJIT(duty), max = 0.6 x tCK(avg) + 63 pS = +1188 pS. (Caution on the min/max usage!)
- 38. When the device is operated with input clock jitter, this parameter needs to be derated by { -tJIT(duty),max tERR(6-10per),max } and { tJIT(duty),min tERR(6-10per),min } of the actual input clock. (output deratings are relative to the SDRAM input clock.)

Examples:

- 1) If the measured jitter into a DDR2-667 SDRAM has tERR(6-10per),min = 272 pS, tERR(6-10per),max = + 293 pS, tJIT(duty),min = 106 pS and tJIT(duty),max = + 94 pS, then tAOF,min(derated) = tAOF,min + $\{$ tJIT(duty),max tERR(6-10per),max $\}$ = 450 pS + $\{$ 94 pS 293 pS $\}$ = 837 pS and tAOF,max(derated) = tAOF,max + $\{$ tJIT(duty),min tERR(6-10per),min $\}$ = 1050 pS + $\{$ 106 pS + 272 pS $\}$ = + 1428 pS. (Caution on the min/max usage!)
- 2) If the measured jitter into a DDR2-1066 SDRAM has tERR(6-10per), min = -202 pS, tERR(6-10per), max = +223 pS, tIJT(duty), min = -66 pS and tJIT(duty), max = +74 pS, then tAOF, min(derated) = tAOF, $min + {-tJIT(duty)}$, max tERR(6-10per), $max } = -350$ pS + { -74 pS -223 pS} = -647 pS and tAOF, max(derated) = tAOF, $max + {-tJIT(duty)}$, min tERR(6-10per), $min } = 950$ pS + { -66 pS + -202 pS } = + -1218 pS. (Caution on the min/max usage!)
- 39. For tAOFD of DDR2-667/800/1066, the 1/2 clock of nCK in the 2.5 x nCK assumes a tCH(avg), average input clock HIGH pulse width of 0.5 relative to tCK(avg). tAOF,min and tAOF,max should each be derated by the same amount as the actual amount of tCH(avg) offset present at the DRAM input with respect to 0.5.

Example

If an input clock has a worst case tCH(avg) of 0.45, the tAOF,min should be derated by subtracting 0.02 x tCK(avg) from it, whereas if an input clock has a worst case tCH(avg) of 0.55, the tAOF,max should be derated by adding 0.02 x tCK(avg) to it. Therefore, we have;

tAOF,min(derated) = tAC,min - [0.5 - Min(0.5, tCH(avg),min)] x tCK(avg)

tAOF,max(derated) = tAC,max + 0.6 + [Max(0.5, tCH(avg),max) - 0.5] x tCK(avg)

or

tAOF,min(derated) = Min(tAC,min, tAC,min - [0.5 - tCH(avg),min] x tCK(avg))

tAOF,max(derated) = 0.6 + Max(tAC,max, tAC,max + [tCH(avg),max - 0.5] x tCK(avg))

where tCH(avg),min and tCH(avg),max are the minimum and maximum of tCH(avg) actually measured at the DRAM input balls.

Note that these deratings are in addition to the tAOF derating per input clock jitter, i.e. tJIT(duty) and tERR(6-10per). However tAC values used in the equations shown above are from the timing parameter table and are not derated.

Thus the final derated values for tAOF are:

tAOF,min(derated_final) = tAOF,min(derated) + { - tJIT(duty),max - tERR(6-10per),max }

tAOF,max(derated_final) = tAOF,max(derated) + { - tJIT(duty),min - tERR(6-10per),min }

- 40. Timings are specified with command/address input slew rate of 1.0 V/nS.
- 41. Timings are specified with DQs and DM input slew rate of 1.0V/nS.
- 42. Timings are specified with CLK/ CLK differential slew rate of 2.0 V/nS. Timings are guaranteed for DQS signals with a differential slew rate of 2.0 V/nS in differential strobe mode.

Publication Release Date: Dec. 02, 2020



43. tIS and tIH (input setup and hold) derating.

tIS/tIH derating values for DDR2-667, DDR2-800 and DDR2-1066

	ΔtIS and ΔtIH Derating Values for DDR2-667, DDR2-800 and DDR2-1066										
Command/Address			CLK/ CLK	Differential	Slew Rate						
Slew Rate (V/nS)	2.0	V/nS	1.5	V/nS	1.0	Unit					
	ΔtIS	ΔtIH	ΔtIS	ΔtIH	ΔtIS	ΔtIH	Unit				
4.0	+150	+94	+180	+124	+210	+154	pS				
3.5	+143	+89	+173	+119	+203	+149	pS				
3.0	+133	+83	+163	+113	+193	+143	pS				
2.5	+120	+75	+150	+105	+180	+135	pS				
2.0	+100	+45	+130	+75	+160	+105	pS				
1.5	+67	+21	+97	+51	+127	+81	pS				
1.0	0	0	+30	+30	+60	+60	pS				
0.9	-5	-14	+25	+16	+55	+46	pS				
0.8	-13	-31	+17	-1	+47	+29	pS				
0.7	-22	-54	+8	-24	+38	+6	pS				
0.6	-34	-83	-4	-53	+26	-23	pS				
0.5	-60	-125	-30	-95	0	-65	pS				
0.4	-100	-188	-70	-158	-40	-128	pS				
0.3	-168	-292	-138	-262	-108	-232	pS				
0.25	-200	-375	-170	-345	-140	-315	pS				
0.2	-325	-500	-295	-470	-265	-440	pS				
0.15	-517	-708	-487	-678	-457	-648	pS				
0.1	-1000	-1125	-970	-1095	-940	-1065	pS				

For all input signals the total tIS (setup time) and tIH (hold time) required is calculated by adding the data sheet tIS(base) and tIH(base) value to the Δ tIS and Δ tIH derating value respectively. Example: tIS (total setup time) = tIS(base) + Δ tIS.

Setup (tIS) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of VREF(dc) and the first crossing of VIH(ac)min. Setup (tIS) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of VREF(dc) and the first crossing of VIL(ac)max. If the actual signal is always earlier than the nominal slew rate line between shaded 'VREF(dc) to AC region', use nominal slew rate for derating value. See Figure 20 Illustration of nominal slew rate for tIS.

If the actual signal is later than the nominal slew rate line anywhere between shaded 'VREF(dc) to AC region', the slew rate of a tangent line to the actual signal from the AC level to DC level is used for derating value. See Figure 21 Illustration of tangent line for tIS.

Hold (tlH) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of VIL(dc)max and the first crossing of VREF(dc). Hold (tlH) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of VIH(dc)min and the first crossing of VREF(dc). If the actual signal is always later than the nominal slew rate line between shaded 'DC to VREF(dc) region', use nominal slew rate for derating value. See Figure 22 Illustration of nominal slew rate for tlH.

If the actual signal is earlier than the nominal slew rate line anywhere between shaded 'DC to VREF(dc) region', the slew rate of a tangent line to the actual signal from the DC level to VREF(dc) level is used for derating value. See Figure 23 Illustration of tangent line for tIH.

Although for slow slew rates the total setup time might be negative (i.e. a valid input signal will not have reached VIH/IL(ac) at the time of the rising clock transition) a valid input signal is still required to complete the transition and reach VIH/IL(ac).

For slew rates in between the values listed in above tIS/tIH derating values for DDR2-667, DDR2-800 and DDR2-1066 table, the derating values may obtained by linear interpolation.

These values are typically not subject to production test. They are verified by design and characterization.

Publication Release Date: Dec. 02, 2020

sees winbond




Figure 20 - Illustration of nominal slew rate for tis

Publication Release Date: Dec. 02, 2020

reservinbond




Figure 21 - Illustration of tangent line for tis

Publication Release Date: Dec. 02, 2020

sassa winbond sa




Figure 22 - Illustration of nominal slew rate for tIH

Publication Release Date: Dec. 02, 2020

massas winbond sassi




Figure 23 - Illustration of tangent line for till

Publication Release Date: Dec. 02, 2020



44. Data setup and hold time derating.

DDR2-667, DDR2-800 and DDR2-1066 tDS/tDH derating with differential data strobe

DQ	ΔtDS, ΔtDH Derating Values for DDR2-667, DDR2-800 and DDR2-1066 (All units in 'pS'; the note applie the entire table)													applie	s to			
Slew	DQ3/DQ3 Differential Siew Rate																	
(V/nS)	4.0 \	V/nS	3.0 \	V/nS	2.0	V/nS	1.8	V/nS	1.6	V/nS	1.4	V/nS	1.2	V/nS	1.0	V/nS	0.8	V/nS
	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH	ΔtDS	ΔtDH
2.0	100	45	100	45	100	45	ı	-	-	-	-	-	-	-	-	-	-	-
1.5	67	21	67	21	67	21	79	33	-	-	-	-	-	-	-	-	-	-
1.0	0	0	0	0	0	0	12	12	24	24	-	-	-	-	-	-	-	-
0.9	-	-	-5	-14	-5	-14	7	-2	19	10	31	22	-	-	-	-	-	-
8.0	ı	1	-	1	-13	-31	-1	-19	11	-7	23	5	35	17	-	-	-	-
0.7	ı	1	-	ı	-	1	-10	-42	2	-30	14	-18	26	-6	38	6	-	-
0.6	-	-	-	-	-	-	-	-	-10	-59	2	-47	14	-35	26	-23	38	-11
0.5	-	-	-	-	-	-	1	-	-	-	-24	-89	-12	-77	0	-65	12	-53
0.4	-	-	-	-	-	-	-	-	-	-	-	-	-52	-140	-40	-128	-28	-116

For all input signals the total tDS (setup time) and tDH (hold time) required is calculated by adding the data sheet tDS(base) and tDH(base) value to the Δ tDS and Δ tDH derating value respectively. Example: tDS (total setup time) = tDS(base) + Δ tDS.

Setup (tDS) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of VREF(dc) and the first crossing of VIH(ac)min. Setup (tDS) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of VREF(dc) and the first crossing of VIL(ac)max. If the actual signal is always earlier than the nominal slew rate line between shaded 'VREF(dc) to AC region', use nominal slew rate for derating value. See Figure 24 Illustration of nominal slew rate for tDS (differential DQS, \overline{DQS}).

If the actual signal is later than the nominal slew rate line anywhere between shaded 'VREF(dc) to AC region', the slew rate of a tangent line to the actual signal from the AC level to DC level is used for derating value. See Figure 25 Illustration of tangent line for tDS (differential DQS, DQS).

Hold (tDH) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of VIL(dc)max and the first crossing of VREF(dc). Hold (tDH) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of VIH(dc)min and the first crossing of VREF(dc). If the actual signal is always later than the nominal slew rate line between shaded 'DC level to VREF(dc) region', use nominal slew rate for derating value. See Figure 26 Illustration of nominal slew rate for tDH (differential DQS, \overline{DQS}).

If the actual signal is earlier than the nominal slew rate line anywhere between shaded 'DC to VREF(dc) region', the slew rate of a tangent line to the actual signal from the DC level to VREF(dc) level is used for derating value. See Figure 27 Illustration of tangent line for tDH (differential DQS, \overline{DQS}).

Although for slow slew rates the total setup time might be negative (i.e. a valid input signal will not have reached VIH/IL(ac) at the time of the rising clock transition) a valid input signal is still required to complete the transition and reach VIH/IL(ac).

For slew rates in between the values listed in above DDR2-667, DDR2-800 and DDR2-1066 tDS/tDH derating with differential data strobe table, the derating values may be obtained by linear interpolation.


These values are typically not subject to production test. They are verified by design and characterization.

Publication Release Date: Dec. 02, 2020



- 45. Slew Rate Measurement Levels:
- a) Output slew rate for falling and rising edges is measured between VTT 250 mV and VTT + 250 mV for single ended signals.
 - For differential signals (e.g. DQS \overline{DQS}) output slew rate is measured between DQS \overline{DQS} = 500 mV and DQS \overline{DQS} = + 500 mV. Output slew rate is guaranteed by design, but is not necessarily tested on each device.
- b) Input slew rate for single ended signals is measured from VREF(dc) to VIH(ac),min for rising edges and from VREF(dc) to VIL(ac),max for falling edges.
 - For differential signals (e.g. CLK $\overline{\text{CLK}}$) slew rate for rising edges is measured from CLK $\overline{\text{CLK}}$ = 250 mV to CLK $\overline{\text{CLK}}$ = + 500 mV (+ 250 mV to 500 mV for falling edges).
- c) VID is the magnitude of the difference between the input voltage on CLK and the input voltage on $\overline{\text{CLK}}$, or between DQS and $\overline{\text{DQS}}$ for differential strobe.
- 46. DDR2 SDRAM output slew rate test load:

Output slew rate is characterized under the test conditions as shown in below figure.



Output slew rate test load

47. Differential data strobe:

DDR2 SDRAM pin timings are specified for either single ended mode or differential mode depending on the setting of the EMRS "Enable DQS" mode bit; timing advantages of differential mode are realized in system design. The method by which the DDR2 SDRAM pin timings are measured is mode dependent. In single ended mode, timing relationships are measured relative to the rising or falling edges of DQS crossing at VREF. In differential mode, these timing relationships are measured relative to the cross point of DQS and its complement, \overline{DQS} . This distinction in timing methods is guaranteed by design and characterization. Note that when differential data strobe mode is disabled via the EMRS, the complementary pin, \overline{DQS} , must be tied externally to VSS through a 20 Ω to 10 k Ω resistor to insure proper operation.

48. All parts list in ordering information table (section 3) will not guarantee to meet functional and AC specification if the tCK out of range mentioned in 10.11 AC Characteristics table.

Publication Release Date: Dec. 02, 2020

resear winbond as




Figure 24 – Illustration of nominal slew rate for tDS (differential DQS, DQS)

Publication Release Date: Dec. 02, 2020 Revision: A02

reservinbond




Figure 25 – Illustration of tangent line for tDS (differential DQS, DQS)

Publication Release Date: Dec. 02, 2020 Revision: A02

resear winbond as




Figure 26 – Illustration of nominal slew rate for tDH (differential DQS, DQS)

Publication Release Date: Dec. 02, 2020 Revision: A02

reses winbond se




Figure 27 – Illustration tangent line for tDH (differential DQS, DQS)

- 65 -

Publication Release Date: Dec. 02, 2020



10.12 AC Input Test Conditions

CONDITION	SYMBOL	VALUE	UNIT	NOTES
Input reference voltage	VREF	0.5 x VDDQ	V	1
Input signal maximum peak to peak swing	VSWING(MAX)	1.0	V	1
Input signal minimum slew rate	SLEW	1.0	V/nS	2, 3

Notes:

- 1. Input waveform timing is referenced to the input signal crossing through the VIH/IL(ac) level applied to the device under test.
- 2. The input signal minimum slew rate is to be maintained over the range from VREF to VIH(ac) min for rising edges and the range from VREF to VIL(ac) max for falling edges as shown in the below figure.
- 3. AC timings are referenced with input waveforms switching from VIL(ac) to VIH(ac) on the positive transitions and VIH(ac) to VIL(ac) on the negative transitions.

10.13 Differential Input/Output AC Logic Levels

PARAMETER	SYM.	MIN.	MAX.	UNIT	NOTES
AC differential input voltage	VID (ac)	0.5	VDDQ + 0.6	V	1
AC differential cross point input voltage	VIX (ac)	0.5 x VDDQ - 0.175	0.5 x VDDQ + 0.175	V	2
AC differential cross point output voltage	VOX (ac)	0.5 x VDDQ - 0.125	0.5 x VDDQ + 0.125	V	3

Notes:

- 1. VID (ac) specifies the input differential voltage |VTR -VCP | required for switching, where VTR is the true input signal (such as CLK, LDQS or UDQS) and VCP is the complementary input signal (such as CLK, LDQS or UDQS). The minimum value is equal to VIH (ac) VIL (ac).
- 2. The typical value of VIX (ac) is expected to be about 0.5 x VDDQ of the transmitting device and VIX (ac) is expected to track variations in VDDQ. VIX (ac) indicates the voltage at which differential input signals must cross.
- 3. The typical value of VOX (ac) is expected to be about 0.5 x VDDQ of the transmitting device and VOX (ac) is expected to track variations in VDDQ. VOX (ac) indicates the voltage at which differential output signals must cross.




Figure 28 - AC input test signal and Differential signal levels waveform

Publication Release Date: Dec. 02, 2020



10.14 AC Overshoot / Undershoot Specification

10.14.1 AC Overshoot / Undershoot Specification for Address and Control Pins:

Applies to A0-A12, BA0-BA2, CS, RAS, CAS, WE, CKE, ODT

PARAMETER	DDR2-1066	DDR2-800	DDR2-667	UNIT
Maximum peak amplitude allowed for overshoot area	0.5	0.5	0.5	V
Maximum peak amplitude allowed for undershoot area	0.5	0.5	0.5	V
Maximum overshoot area above VDD	0.5	0.66	0.8	V-nS
Maximum undershoot area below VSS	0.5	0.66	0.8	V-nS

10.14.2 AC Overshoot / Undershoot Specification for Clock, Data, Strobe and Mask Pins:

Applies to DQ, LDQS, LDQS, UDQS, UDQS, LDM, UDM, CLK, CLK

PARAMETER	DDR2-1066	DDR2-800	DDR2-667	UNIT
Maximum peak amplitude allowed for overshoot area	0.5	0.5	0.5	V
Maximum peak amplitude allowed for undershoot area	0.5	0.5	0.5	V
Maximum overshoot area above VDDQ	0.19	0.23	0.23	V-nS
Maximum undershoot area below VSSQ	0.19	0.23	0.23	V-nS





Figure 29 - AC overshoot and undershoot definition

Publication Release Date: Dec. 02, 2020




11. TIMING WAVEFORMS

11.1 Command Input Timing






11.2 ODT Timing for Active/Standby Mode




11.3 ODT Timing for Power Down Mode






11.4 ODT Timing mode switch at entering power down mode






11.5 ODT Timing mode switch at exiting power down mode






11.6 Data output (read) timing




11.7 Burst read operation: RL=5 (AL=2, CL=3, BL=4)






11.8 Data input (write) timing




11.9 Burst write operation: RL=5 (AL=2, CL=3, WL=4, BL=4)






11.10 Seamless burst read operation: RL = 5 (AL = 2, and CL = 3, BL = 4)



Note

The seamless burst read operation is supported by enabling a read command at every other clock for BL = 4 operation, and every 4 clock for BL = 8 operation. This operation is allowed regardless of same or different banks as long as the banks are activated.

11.11 Seamless burst write operation: RL = 5 (WL = 4, BL = 4)




Note:

The seamless burst write operation is supported by enabling a write command every other clock for BL = 4 operation, every four clocks for BL = 8 operation. This operation is allowed regardless of same or different banks as long as the banks are activated.


Publication Release Date: Dec. 02, 2020



11.12 Burst read interrupt timing: RL =3 (CL=3, AL=0, BL=8)




11.13 Burst write interrupt timing: RL=3 (CL=3, AL=0, WL=2, BL=8)



Publication Release Date: Dec. 02, 2020 Revision: A02




11.14 Write operation with Data Mask: WL=3, AL=0, BL=4)






11.15 Burst read operation followed by precharge: RL=4 (AL=1, CL=3, BL=4, tRTP ≤ 2clks)




11.16 Burst read operation followed by precharge: RL=4 (AL=1, CL=3, BL=8, tRTP ≤ 2clks)




Publication Release Date: Dec. 02, 2020



11.17 Burst read operation followed by precharge: RL=5 (AL=2, CL=3, BL=4, tRTP ≤ 2clks)




11.18 Burst read operation followed by precharge: RL=6 (AL=2, CL=4, BL=4, tRTP ≤ 2clks)




Publication Release Date: Dec. 02, 2020



11.19 Burst read operation followed by precharge: RL=4 (AL=0, CL=4, BL=8, tRTP > 2clks)




11.20 Burst write operation followed by precharge: WL = (RL-1) = 3




Publication Release Date: Dec. 02, 2020 Revision: A02



11.21 Burst write operation followed by precharge: WL = (RL-1) = 4




11.22 Burst read operation with Auto-precharge: RL=4 (AL=1, CL=3, BL=8, tRTP ≤ 2clks)




Publication Release Date: Dec. 02, 2020



11.23 Burst read operation with Auto-precharge: RL=4 (AL=1, CL=3, BL=4, tRTP > 2clks)




11.24 Burst read with Auto-precharge followed by an activation to the same bank (tRC Limit): RL=5 (AL=2, CL=3, internal tRCD=3, BL=4, tRTP ≤ 2clks)




Publication Release Date: Dec. 02, 2020



11.25 Burst read with Auto-precharge followed by an activation to the same bank (tRP Limit): RL=5 (AL=2, CL=3, internal tRCD=3, BL=4, tRTP ≤ 2clks)




11.26 Burst write with Auto-precharge (tRC Limit): WL=2, WR=2, BL=4, tRP=3




Publication Release Date: Dec. 02, 2020



11.27 Burst write with Auto-precharge (WR + tRP Limit): WL=4, WR=2, BL=4, tRP=3



11.28 Self Refresh Timing




Notes:

- 1. Device must be in the "All banks idle" state prior to entering Self Refresh mode.
- 2. ODT must be turned off tAOFD before entering Self Refresh mode, and can be turned on again when tXSRD timing is satisfied.
- 3. tXSRD is applied for a Read or a Read with Auto-precharge command. tXSNR is applied for any command except a Read or a Read with Auto-precharge command.


Publication Release Date: Dec. 02, 2020



11.29 Basic Power Down Entry and Exit Timing




11.30 Precharged Power Down Entry and Exit Timing



Publication Release Date: Dec. 02, 2020



11.31 Clock frequency change in precharge Power Down mode




Publication Release Date: Dec. 02, 2020 Revision: A02



12. PACKAGE SPECIFICATION

Package Outline VFBGA84 Ball (8x12.5 mm², Ball pitch: 0.8mm) - (Window BGA Type)



Publication Release Date: Dec. 02, 2020



13. REVISION HISTORY

VERSION	DATE	PAGE	DESCRIPTION
A01	Aug. 11, 2020	All	Initial formal datasheet
A02	Dec. 02, 2020	5, 42, 43, 45	Revise tRAS min. value from 45nS to 40nS
		43, 45	Revise tCH(avg) & tCL(avg) min./max. value from 0.48 tCK(avg)/0.52 tCK(avg) to 0.45 tCK(avg)/0.55 tCK(avg)