

# Wiha T-handle.

The classic for high torques.

## For Allen screws (metric).



### 334 Hex driver with T-handle.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.

Order-No.	●	↔	○	↔	↔	↔	↔	↔
00904 5	2	100	-	126	80	26		10
00905 2	2	200	-	226	80	26		10
00906 9	2.5	100	-	126	80	26		10
00907 6	2.5	200	-	226	80	26		10
00908 3	3	100	-	126	80	26		10
00909 0	3	150	-	176	80	26		10
00910 6	3	200	-	226	80	26		10
00911 3	3	350	5+	382	100	32		10
00912 0	4	100	-	126	80	26		10
00913 7	4	150	-	176	80	26		10
00914 4	4	200	-	226	80	26		10
00915 1	4	350	5+	382	100	32		10
00916 8	5	100	-	132	100	32		10
00917 5	5	150	-	182	100	32		10
00918 2	5	200	-	232	100	32		10
00919 9	5	350	-	382	100	32		10
00921 2	6	100	-	132	100	32		10
00922 9	6	150	-	182	100	32		10
00923 6	6	200	-	232	100	32		10
00924 3	6	350	-	382	100	32		10
00926 7	7	200	-	232	100	32		10
00928 1	8	100	-	132	100	32		10
00929 8	8	150	-	182	100	32		10
00930 4	8	200	-	232	100	32		10
00931 1	8	350	-	372	100	32		10
00933 5	10	100	-	138	120	38		10
00934 2	10	200	-	238	120	38		10
00937 3	12	200	-	238	120	38		5

+ Overlength with reinforced blade

## For hex nuts.



### 336 Hex nut driver with T-handle.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.  
Extra: Recess in shank to accommodate for long screws.

Order-No.	○	↔	↔	↔	↔	↔	↔
00965 6	5.5	125	157	100	32		10
00966 3	6	125	157	100	32		10
00967 0	6	200	232	100	32		10
00968 7	7	125	157	100	32		10
00969 4	7	200	232	100	32		10
00970 0	7	350	382	100	32		10
00971 7	8	125	157	100	32		10
00972 4	8	200	232	100	32		10
00973 1	8	350	382	100	32		10
00974 8	9	125	157	100	32		10
00975 5	9	200	232	100	32		10
00977 9	10	125	157	100	32		10
00978 6	10	200	232	100	32		10
00979 3	10	230	262	100	32		10
00980 9	10	350	382	100	32		10
00982 3	11	125	157	100	32		10
00983 0	11	230	262	100	32		5
00985 4	12	125	157	100	32		10
00986 1	12	230	262	100	32		5
00988 5	13	125	157	100	32		10
00989 2	13	230	262	100	32		10
00990 8	13	350	382	100	32		10
00991 5	14	125	157	100	32		5
00993 9	15	125	157	100	32		5
00994 6	16	125	157	100	32		5
00995 3	17	125	157	100	32		5

## For external square drive screws.



### 338 Square nut driver with T-handle.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.  
Extra: Recess in shank to accommodate for long screws.

Order-No.	□	↔	↔	↔	↔	↔
01005 8	6	125	157	100	32	10
01006 5	8	125	157	100	32	10
01007 2	10	125	157	100	32	10
01008 9	12	125	157	100	32	10

## For hexagon bolts and Allen screws (metric).



### 336 Zoll Hex nut driver with T-handle.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.  
Extra: Recess in shank to accommodate for long screws.

Order-No.	○	↔	↔	↔	↔	mm	↔
02819 0	3/16	150	182	100	32	4.76	10
02820 6	1/4	150	182	100	32	6.35	10
02821 3	5/16	150	182	100	32	7.94	10
02822 0	3/8	150	182	100	32	9.53	10
02823 7	7/16	150	182	100	32	11.11	10
02824 4	1/2	150	182	100	32	12.70	10



### 334 Zoll Hex driver with T-handle.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.

Order-No.	●	↔	↔	↔	↔	mm	↔
02802 2	3/32	150	182	80	26	2.38	10
02803 9	7/64	150	182	80	26	2.78	10
02804 6	1/8	150	182	80	26	3.18	10
02805 3	9/64	150	182	80	26	3.57	10
02806 0	5/32	150	182	80	26	3.97	10
02807 7	3/16	150	182	100	32	4.76	10
02808 4	7/32	150	182	100	32	5.56	10
02809 1	1/4	150	182	100	32	6.35	10
02810 7	5/16	150	182	100	32	7.94	10
02811 4	3/8	150	188	120	38	9.53	10



### 334 VB Hex driver set with T-handle.

In bench stand, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.  
Handle: Wiha T-handle.  
Application: For high torque transfer with minimal effort.  
Extra: Robust metal workbench holder to place on workbench or wall-mount.  
Tip diagrams printed to scale.

Order-No.	Series	↔
00953 3	334 VB	1
●	334	2x100 2.5x100 3x100 4x150 5x150 6x200 8x200

## Wiha Info



Wiha VDE T-handles can be found in the VDE range on page 231.