


**Triple-deck terminal blocks + ground protection**  
**Compression clamp**  
 **DIN 3**


**D 4/6.T3.P**

Spacing 6 mm (.238")



Standard 6 mm block + ground protection.



Color	Type	Part numbers
Grey V0	 <b>D 4/6.T3.P</b>	<b>0299 684.02</b>

**Characteristics**

**Wire size**

		IEC		UL	CSA
		NFC	DIN		
Compression clamp	Solid wire	0,2-4 mm <sup>2</sup>		24-10 AWG	24-10 AWG
	Stranded wire	0,22-4 mm <sup>2</sup>		24-10 AWG	24-10 AWG

**Voltage**

Rated	500 V	300 V	300 V
Pulse	6 kV		
Pollution degree	3		

**Current**

Rated / Short circuit	32A - 480A/1s	20 A	20 A
-----------------------	---------------	------	------

**Wire size**

Rated/gauge	4 mm <sup>2</sup> / A4	10 AWG	10 AWG
Wire stripping length	Recommended screwdriver	Recommended torque	Protection
9,5 mm .37"	4 mm .16"	0,5-0,8 Nm 4,4-7 lb.in	IP 20 NEMA 1

End stop	th. 12 mm	<b>BADH</b> V2	<b>0116 900.27</b>
End stop	th. 9,1 mm	<b>BAMH</b> V0	<b>0194 836.01</b>
End stop	th. 9,1 mm	<b>BAMH</b> V2	<b>0114 836.00</b>

Other end stops : see Accessories section


Rail	35 x 7,5 x 1	<b>PR3G2</b>	<b>0164 800.03</b>
Rail	35 x 7,5 x 1	<b>PR3Z2</b>	<b>0174 300.17</b>
Rail	35 x 7,5 x 1	<b>PR30</b> prepunched	<b>0173 220.05</b>
Rail	35 x 15 x 2,3	<b>PR4</b>	<b>0168 500.12</b>
Rail	35 x 15 x 1,5	<b>PR5</b> prepunched	<b>0101 598.26</b>

Other rails : see Accessories section

Other accessories : see Accessories section







**Notes**

Block for three phase motor supply



or for connection of 4 wire sensors.

**Accessories**

	<b>1</b> End section	
	<b>2</b> Circuit separator	white
	<b>3</b> Test socket	
	<b>4</b> Test plug	
	<b>5</b> Assembled jumper bar	32A
	<b>6</b> Comb type jumper bar	32A
	<b>7</b> IDC jumper	24A



**R** See section on markers marking method

Type	Part numbers
No end section needed : closed block	
<b>SCD</b> (3) V2	<b>0103 189.26</b>
<b>AL2</b> (2) (3)	DIA. 2,0 mm <b>0167 319.06</b>
<b>FC2</b> (1) (3)	DIA. 2,0 mm <b>0007 865.26</b>
<b>BJM62</b> (3)	2 poles <b>0173 217.26</b>
<b>BJM62</b> (3)	3 poles <b>0173 218.07</b>
<b>BJM62</b> (3)	4 poles <b>0173 219.00</b>
<b>BJM62</b> (3)	5 poles <b>0173 221.22</b>
<b>BJM62</b> (3)	6 poles <b>0174 112.16</b>
<b>BJM62</b> (3)	7 poles <b>0174 113.17</b>
<b>BJM62</b> (3)	8 poles <b>0174 114.10</b>
<b>BJM62</b> (3)	9 poles <b>0174 115.11</b>
<b>BJM62</b> (3)	10 poles <b>0173 226.27</b>
<b>PC61</b>	10 poles <b>0163 311.22</b>
<b>AD2,5</b> V2	<b>0114 205.20</b>

Ⓢ Note : RC65 blank (white, red, blue)  
 (1) For block equipped with AL2. (2) A circuit separator **SCD** is required with the use of these accessories.  
 (3) Only for upper deck.